

LOC	DIST	REVISIONS			
		REV	DESCRIPTION	DATE	DWN
CM	00	E2	REV PER ECO 11-015338	26JUL11	JR

D

C

B



A

D


C

B

A



RECOMMENDED MOUNTING HOLE PATTERN FOR 1.57[.062] THICK P.C. BOARD



- 1 MATERIAL HOUSING: THERMOPLASTIC POLYESTER, GLASS FILLED, UL94V-O. POST: COPPER ALLOY
- 2 FINISH HOUSING: NATURAL POST: BRIGHT TIN-LEAD (93/7) PLATE, 0.00380-0.00880[.000150-.000350] THK OVER NICKEL UNDERPLATE, 0.00130[.000050] MIN THK.
- 3 UL MARKING MAY NOT APPEAR ON THE 2 OR 3 POSITION SIZES. CSA MARKING MAY NOT APPEAR ON THE 2 POSITION SIZE.
- 4 POST SOLDERTAILS COMPLY WITH AMP SOLDERABILITY SPEC 109-11-2.
- 5 POST WITHSTANDS 13.34N [3 LB] MIN AXIAL FORCE IN EITHER DIRECTION WITHOUT DISLODGING.
- 6 APPLIES AT -A-
- 7 APPLIES WHEN THE HEADER IS STRAIGHT.
- 8 PLASTIC PROJECTIONS PERMITTED IN THIS ZONE.
- 9 COORDINATE DIMENSIONS APPLIES FROM THE CENTER OF THE ACTUAL FEATURE.
- 10 SOLDER SIDE OF BOARD IS SHOWN.
- 11 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 12 ALL POSITION SIZES HAVE THE BACKWALL NOTCHED ON BOTH ENDS AS SHOWN. THE 2 THRU 5 POSITION SIZES HAVE SOLID BACKWALLS. POSITION SIZES 6 AND ABOVE HAVE AN INTERRUPTED BACKWALL AT VARIOUS LOCATIONS (SEE TABLE FOR INTERRUPTION(S) LOCATIONS).
- 13 EDGE OF POLARIZING LOCK WALL TO BE IN LINE WITH CENTERLINE OF ADJACENT POST WITHIN ±0.13 [.005]
- 14 FINISH HOUSING: NATURAL POST: MATTE TIN PLATE 0.000150 MIN THICK OVER NICKEL.
- 15 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

13 SUPERSEDED

13 SUPERSEDED

13 SUPERSEDED

13 SUPERSEDED

FINISH	BACKWALL INTERRUPTION(S) BETWEEN POST	L	NO. OF POSITIONS	PART NO
14	4&5, 7&8, 11&12, 14&15	71.20 [2.803]	18	4-644613-8
14	4&5, 7&8, 10&11, 13&14	67.23 [2.647]	17	4-644613-7
14	4&5, 8&9, 12&13	63.27 [2.491]	16	4-644613-6
14	4&5, 8&9, 11&12	59.31 [2.335]	15	4-644613-5
14	4&5 7&8, 10&11	55.35 [2.179]	14	4-644613-4
14	4&5 7&8, 10&11	51.38 [2.023]	13	4-644613-3
14	4&5, 8&9	47.42 [1.867]	12	4-644613-2
14	4&5, 7&8	43.46 [1.711]	11	4-644613-1
14	3&4, 7&8	39.50 [1.555]	10	4-644613-0
14	3&4, 6&7	35.53 [1.399]	9	3-644613-9
14	4&5	31.57 [1.243]	8	3-644613-8
14	4&5	27.61 [1.087]	7	3-644613-7
14	3&4	23.65 [.931]	6	3-644613-6
14	NONE	19.69 [.775]	5	3-644613-5
14	NONE	15.72 [.619]	4	3-644613-4
14	NONE	11.76 [.463]	3	3-644613-3
14	NONE	7.80 [.307]	2	3-644613-2
2	4&5, 7&8, 11&12, 14&15	71.20 [2.803]	18	1-644613-8
2	4&5, 7&8, 10&11, 13&14	67.23 [2.647]	17	1-644613-7
2	4&5, 8&9, 12&13	63.27 [2.491]	16	1-644613-6
2	4&5, 8&9, 11&12	59.31 [2.335]	15	1-644613-5
2	4&5 7&8, 10&11	55.35 [2.179]	14	1-644613-4
2	4&5 7&8, 10&11	51.38 [2.023]	13	1-644613-3
2	4&5, 8&9	47.42 [1.867]	12	1-644613-2
2	4&5, 7&8	43.46 [1.711]	11	1-644613-1
2	3&4, 7&8	39.50 [1.555]	10	1-644613-0
2	3&4, 6&7	35.53 [1.399]	9	644613-9
2	4&5	31.57 [1.243]	8	644613-8
2	4&5	27.61 [1.087]	7	644613-7
2	3&4	23.65 [.931]	6	644613-6
2	NONE	19.69 [.775]	5	644613-5
2	NONE	15.72 [.619]	4	644613-4
2	NONE	11.76 [.463]	3	644613-3
2	NONE	7.80 [.307]	2	644613-2

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SMITH 2-12-93	 TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK R.SWING 2-12-93		
DIMENSIONS: mm [INCHES]		APVD D.CLARK 15-12-93	NAME MTA-156 HEADER ASSEMBLY, POLARIZED LOCK, RIGHT ANGLE FRONT BEND,.045 SQUARE POST, TIN-LEAD PLATED, WITHOUT RETENTION PEGS	
		PRODUCT SPEC		
		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO	
0 PLC ± -				
1 PLC ± -			WEIGHT	
2 PLC ± -				
3 PLC ± -			CUSTOMER DRAWING	
4 PLC ± -				
ANGLES ± -				
FINISH				
MATERIAL 		RESTRICTED TO		-
		SCALE		5:1
		SHEET		1 OF 1
		REV		E2