


Darlington Transistor



Features:

- Collector-Emitter sustaining voltage-
 $V_{CEO(sus)} = 80V$ (Min.) - BDX33B, BDX34B
 $= 100V$ (Minimum) - BDX33C, BDX34C
- Monolithic construction with Built-in Base-Emitter shunt resistor

Maximum Ratings

Characteristic	Symbol	BDX33B BDX34B	BDX33C BDX34C	Unit
Collector-Emitter Voltage	V _{CEO}	80	100	V
Collector-Base Voltage	V _{CBO}			
Emitter-Base Voltage	V _{EBO}	5		
Collector Current-Continuous -Peak	I _C I _{CM}	10 15		A
Base Current	I _B	0.25		
Total Power Dissipation at T _C = 25°C Derate above 25°C	P _D	70 0.56		W W/°C
Operating and Storage Junction Temperature Range	T _J , T _{STG}	-65 to +150		°C

Thermal Characteristics

Characteristic	Symbol	Max.	Unit
Thermal Resistance Junction to Case	$R_{\theta jc}$	1.78	$^\circ C/W$

Darlington Transistor



Electrical Characteristics:

($T_C = 25^\circ\text{C}$ unless otherwise noted)

Characteristic	Symbol	Min.	Max.	Unit
----------------	--------	------	------	------

OFF Characteristics


Collector-Emitter Sustaining Voltage (1) $I_C = 100\text{mA}$, $I_B = 0$ BDX33B, BDX34B BDX33C, BDX34C	$V_{CEO(sus)}$	80 100	-	V
Collector Cut off Current $V_{CE} = 40\text{V}$, $I_B = 0$ BDX33B, BDX34B $V_{CE} = 50\text{V}$, $I_B = 0$ BDX33C, BDX34C	I_{CEO}	-	0.5 0.5	mA
Collector-Base Cut off Current $V_{CB} = \text{Rated } V_{CB}$, $I_E = 0$	I_{CBO}	-	200	μA
Emitter-Base Cut off Current $V_{EB} = 5\text{V}$, $I_C = 0$	I_{EBO}	-	10	mA

ON Characteristics (1)

DC Current Gain $I_C = 3\text{A}$, $V_{CE} = 3\text{V}$ BDX33B/33C/34B/34C	h_{FE}	750	-	-
Collector-Emitter Saturation Voltage $I_C = 3\text{A}$, $I_B = 6\text{mA}$ BDX33B/33C/34B/34C	$V_{CE(sat)}$	-	2.5	V
Base-Emitter On Voltage $I_C = 3\text{A}$, $V_{CE} = 3\text{V}$ BDX33B/33C/34B/34C	$V_{BE(on)}$	-	2.5	

(1) Pulse Test: Pulse Width = $300\mu\text{s}$, Duty Cycle $\leq 2\%$


Figure - 1 Power Derating



Darlington Transistor




Figure - 2 Safe Operating Area



There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown safe operating area curves indicate I_C - V_{CE} limits of the transistor that must be observed for reliable operation i.e., the transistor must not be subjected to greater dissipation than the curves indicate.

The data of Figure - 2 is based on $T_{J(PK)} = 150^\circ\text{C}$; TC is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided $T_{J(PK)} < 150^\circ\text{C}$. At high case temperatures, thermal limitation will reduce the power that can handled to values less than the limitations imposed by second breakdown.



Dimensions	Min.	Max.
A	14.68	15.31
B	9.78	10.42
C	5.01	6.52
D	13.06	14.62
E	3.57	4.07
F	2.42	3.66
G	1.12	1.36
H	0.72	0.96
I	4.22	4.98
J	1.14	1.38
K	2.2	2.97
L	0.33	0.55
M	2.48	2.98
O	3.7	3.9

Dimensions : Millimetres

Pin Configuration:

1. Base
2. Collector
3. Emitter
4. Collector(Case)

Part Number Table

Description	Part Number
Darlington Transistor, TO-220	BDX33B
	BDX33C
	BDX34B
	BDX34C

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

