


Panasonic
ideas for life

HIGH ELECTRICAL & MECHANICAL NOISE IMMUNITY RELAY

JQ RELAYS



mm inch

FEATURES

- High electrical noise immunity
- High switching capacity in a compact package
- High sensitivity: 200 mW (1a), 400 mW (1c)
- High surge voltage: 8,000 V between contacts and coil
- UL, CSA, VDE, TÜV, SEMKO approved
- Class B coil insulation type available

SPECIFICATIONS

Contact

				Standard type		High capacity type		
Arrangement				1 Form A, 1 Form C				
Initial contact resistance, max. (By voltage drop 6 V DC 1 A)				100 mΩ				
Contact material				Silver alloy				
Rating (resistive)	Nominal switching capacity	1a		5 A 125 V AC		10 A 125 V AC		
				2 A 250 V AC		5 A 250 V AC		
				5 A 30 V DC		5 A 30 V DC		
		1c		5 A 125 V AC		10 A 125 V AC		
				2 A 250 V AC		5 A 250 V AC		
				3 A 30 V AC		5 A 30 V DC		
	1c		2 A 125 V AC		3 A 125 V AC			
			1 A 250 V AC		2 A 250 V AC			
			1 A 30 V DC		1 A 30 V DC			
	Max. switching power	1c		1a		625 VA, 150 W		1,250 VA, 150 W
N.O.				625 VA, 90 W		1,250 V AC, 150 W		
N.C.				250 VA, 30 W		500 V AC, 30 W		
Max. switching voltage				250 V AC, 110 V DC (0.3A)				
Max. switching current				N.O.: 5 A N.C.: 2 A		N.O.: 10 A N.C.: 3 A		
Min. switching capacity ^{#1}				100 mA, 5 V DC				
Expected mechanical life (at 180 cpm)(min. operations)				10 ⁷				

Expected electrical life (min. operations)

Type		Switching capacity	No. of operations	
Standard type	1a	5 A 125 V AC	5×10 ⁴	
		3 A 125 V AC	2×10 ⁵	
		2 A 250 V AC	2×10 ⁵	
		5 A 30 V DC	10 ⁵	
	1c	N.O.	5 A 125 V AC	5×10 ⁴
			2 A 250 V AC	2×10 ⁵
3 A 30 V DC			10 ⁵	
1c	N.C.	2 A 125 V AC	2×10 ⁵	
		1 A 250 V AC	2×10 ⁵	
		1 A 30 V DC	10 ⁵	
High capacity type	1a	10 A 125 V AC	5×10 ⁴	
		5 A 250 V AC	5×10 ⁴	
		5 A 30 V DC	10 ⁵	
	1c	N.O.	10 A 125 V AC	5×10 ⁴
			5 A 250 V AC	5×10 ⁴
			5 A 30 V DC	10 ⁵
1c	N.C.	3 A 125 V AC	2×10 ⁵	
		2 A 250 V AC	2×10 ⁵	
		1 A 30 V DC	10 ⁵	

Coil (at 20°C 68°F)

Nominal operating power	1a: 200 mW	1c: 400 mW
-------------------------	------------	------------

Characteristics

Max. operating speed		20 cpm
Initial insulation resistance ^{*1}		Min. 1,000 MΩ at 500 V DC
Initial breakdown voltage ^{*2}	Between open contacts	1a: 1,000 Vrms for 1 min. 1c: 750 Vrms for 1 min.
	Between contacts and coil	4,000 Vrms for 1 min.
Surge voltage between contact and coil ^{*3}		8,000 V
Operate time ^{*4} (at nominal voltage)		Approx. 5 ms
Release time ^{*4} (at nominal voltage)(without diode)		Approx. 2 ms
Temperature rise ^{*5}		Max. 45°C
Shock resistance	Functional ^{*6}	Min. 294 m/s ² {30 G}
	Destructive ^{*7}	Min. 980 m/s ² {100 G}
Vibration resistance	Functional ^{*8}	98 m/s ² {10 G}, 10 to 55 Hz at double amplitude of 1.6 mm
	Destructive	117.6 m/s ² {12 G}, 10 to 55 Hz at double amplitude of 2.0 mm
Conditions for operation, transport and storage ^{*9} (Not freezing and condensing at low temperature)	Ambient temp. ^{*10}	−40°C to +85°C −40°F to +185°F
	Humidity	5 to 85% R.H.
Unit weight		Approx. 7 g .25 oz

#1 This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

Remarks

* Specifications will vary with foreign standards certification ratings.

*1 Measurement at same location as "Initial breakdown voltage" section

*2 Detection current: 10 mA

*3 Wave is standard shock voltage of ±1.2 × 50μs according to JEC-212-1981

*4 Excluding contact bounce time

*5 Measured conditions

Standard type	Resistive, nominal voltage applied to the coil. Contact carrying current: 5 A, at 70°C 158°F
High capacity type	Resistive, nominal voltage applied to the coil. Contact carrying current: 10 A, at 70°C 158°F

*6 Half-wave pulse of sine wave: 11ms; detection time: 10μs

*7 Half-wave pulse of sine wave: 6ms

*8 Detection time: 10μs

*9 Refer to 6. Conditions for operation, transport and storage mentioned in AMBIENT ENVIRONMENT

*10 When using relays in a high ambient temperature, consider the pick-up voltage rise due to the high temperature (a rise of approx. 0.4% V for each 1°C 33.8°F with 20°C 68°F as a reference) and use a coil impressed voltage that is within the maximum allowable voltage range.

TYPICAL APPLICATIONS

- Air conditioners
- Refrigerators
- Microwave ovens
- Heaters

ORDERING INFORMATION

Ex. JQ 1a P — B — 12 V — F

Contact arrangement	Contact capacity	Coil insulation class	Coil voltage (DC)	Environmental support
1a: 1 Form A 1: 1 Form C	Nil: Standard P: High capacity	Nil: Class E coil insulation B: Class B coil insulation	5, 6, 9, 12, 18, 24, 48* V	F: RoHS Directive conforming type (AgSnO ₂ type) Nil: RoHS Directive non-conforming type (AgCdO type)

UL/CSA, VDE, SEMKO approved type is standard.


* Available only for 1 Form C type

TYPES AND COIL DATA at 20°C 68°F


	Part No.	Nominal voltage, V DC	Pick-up voltage, V DC (min.)	Drop-out voltage, V DC (min.)	Nominal operating current, mA	Nominal operating power, mW	Coil resistance, Ω (±10%)	Max. allowable voltage, V DC
1 Form A	Standard type	JQ1a-5V (-F)	5	3.75	40	200	125	180% of nominal voltage (at 20°C 68°F)
		JQ1a-6V (-F)	6	4.5	33.3		180	
		JQ1a-9V (-F)	9	6.75	22.2		405	
		JQ1a-12V (-F)	12	9	16.7		720	
		JQ1a-18V (-F)	18	13.5	11.1		1,620	
		JQ1a-24V (-F)	24	18	8.3		2,880	
	High capacity type	JQ1aP-5V (-F)	5	4	40	200	125	130% of nominal voltage (at 85°C 185°F)
		JQ1aP-6V (-F)	6	4.8	33.3		180	
		JQ1aP-9V (-F)	9	7.2	22.2		405	
		JQ1aP-12V (-F)	12	9.6	16.7		720	
		JQ1aP-18V (-F)	18	14.4	11.1		1,620	
		JQ1aP-24V (-F)	24	19.2	8.3		2,880	
1 Form C	Standard type	JQ1-5V (-F)	5	3.75	80	400	62.5	150% of nominal voltage (at 20°C 68°F)
		JQ1-6V (-F)	6	4.5	66.7		90	
		JQ1-9V (-F)	9	6.75	44.4		202.5	
		JQ1-12V (-F)	12	9	33.3		360	
		JQ1-18V (-F)	18	13.5	22.2		810	
		JQ1-24V (-F)	24	18	16.7		1,440	
	High capacity type	JQ1P-5V (-F)	5	4	80	400	62.5	110% of nominal voltage (at 85°C 185°F)
		JQ1P-6V (-F)	6	4.8	66.7		90	
		JQ1P-9V (-F)	9	7.2	44.4		202.5	
		JQ1P-12V (-F)	12	9.6	33.3		360	
		JQ1P-18V (-F)	18	14.4	22.2		810	
		JQ1P-24V (-F)	24	19.2	16.7		1,440	
		JQ1P-48V (-F)	48	38.4	8.3		5,760	



1 Form A




1 Form A




Schematic (Bottom view)


1 Form C




1 Form C



1 Form A



1FormC

Tolerance: $\pm 0.1 \pm .004$

Dimension :

Max. 1mm .039 inch

1 to 5mm .039 to .118 inch


Min. 5mm .118 inch

General tolerance


 $\pm 0.2 \pm .008$ $\pm 0.3 \pm .012$ $\pm 0.4 \pm .016$

REFERENCE DATA

Max. switching capacity (1 Form A type)




Max. switching capacity (1 Form C type)



Standard type


1-(1). Operate & release time (1 Form A type)

Tested sample: JQ1a-12V, 25 pcs.




1-(2). Operate & release time (1 Form C type)

Tested sample: JQ1-24V, 25 pcs.




2. Life curve

Ambient temperature: room temperature




3-(1). Coil temperature rise (1 Form A type)

Contact carrying current: 3 A, 5 A
Measured portion: Inside the coil




3-(2). Coil temperature rise (1 Form C type)

Contact carrying current: 3 A, 5 A
Measured portion: Inside the coil




4-(1). Ambient temperature characteristics (1 Form A type)

Tested sample: JQ1a-24V
Contact carrying current: 3 A, 5 A



4-(2). Ambient temperature characteristics (1 Form C type)

Tested sample: JQ1-24V
Contact carrying current: 3 A, 5 A




- ① Allowable ambient temperature against % coil voltage (max. inside the coil temperature set as 130°C 266°F) (Carrying current: 3 A)
- ② Allowable ambient temperature against % coil voltage (max. inside the coil temperature set as 130°C 266°F) (Carrying current: 5 A)
- ③ Allowable ambient temperature against % coil voltage (max. inside the coil temperature set as 115°C 239°F) (Carrying current: 3 A)
- ④ Allowable ambient temperature against % coil voltage (max. inside the coil temperature set as 115°C 239°F) (Carrying current: 5 A)
- ⑤ Pick-up voltage with a hot-start condition of 100%V on the coil (Carrying current: 5 A)
- ⑥ Pick-up voltage with a hot-start condition of 100%V on the coil (Carrying current: 3 A)
- ⑦ Pick-up voltage

High capacity type


1-(1). Operate & release time (1 Form A type)

Tested sample: JQ1aP-12V, 25 pcs.




1-(2). Operate & release time (1 Form C type)

Tested sample: JQ1P-12V, 25 pcs.




2. Life curve

Ambient temperature: room temperature




3-(1). Coil temperature rise (1 Form A type)

Contact carrying current: 5 A, 10 A
Measured portion: Inside the coil




3-(2). Coil temperature rise (1 Form C type)


Contact carrying current: 5 A, 10 A
Measured portion: Inside the coil



4-(1). Ambient temperature characteristics
(1 Form A type)
Tested sample: JQ1aP-24V
Contact carrying current: 5 A, 10 A



4-(2). Ambient temperature characteristics
(1 Form C type)
Tested sample: JQ1P-24V
Contact carrying current: 5 A, 10 A



- ① Allowable ambient temperature against % coil voltage (max. inside the coil temperature set as 130°C 266°F) (Carrying current: 5 A)
- ② Allowable ambient temperature against % coil voltage (max. inside the coil temperature set as 130°C 266°F) (Carrying current: 10 A)
- ③ Allowable ambient temperature against % coil voltage (max. inside the coil temperature set as 115°C 239°F) (Carrying current: 5 A)
- ④ Allowable ambient temperature against % coil voltage (max. inside the coil temperature set as 115°C 239°F) (Carrying current: 10 A)
- ⑤ Pick-up voltage with a hot-start condition of 100%V on the coil (Carrying current: 10 A)
- ⑥ Pick-up voltage with a hot-start condition of 100%V on the coil (Carrying current: 5 A)
- ⑦ Pick-up voltage

For Cautions for Use, see Relay Technical Information