



Product: [82240](#)

50 Ohm Wireless Transmission Coax, RG-58, 20 AWG Solid BC, 95% TC Braid, Flamarrest® Jkt, CMP

Product Description

50 Ohm Wireless Transmission Coax, RG-58, 20 AWG Solid Bare Copper Conductor, FEP Insulation, 95% Tinned Copper Braid Shield, Flamarrest® Jacket, CMP

Technical Specifications

Product Overview

Suitable Applications:	Wireless microphones, Two-Way Radios, Amateur (Ham) Radio, Low Power FM, GPS, RFID (Radio Frequency Identification)
------------------------	---

Construction Details

RG Type:	58
----------	----

Conductor

AWG	Stranding	Nom. Diameter	Material
20	Solid	0.032 in	BC - Bare Copper

Insulation

Material	Nom. Diameter
FEP - Fluorinated Ethylene Propylene	0.107 in

Outer Shield Material

Outer Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	95%
	Silvered Copper (SC)	

Outer Jacket Material

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.159 in

Electrical Characteristics

Attenuation

Frequency	Nom. Attenuation [dB/100ft]
1 MHz	0.5 dB/100ft
10 MHz	1.2 dB/100ft
50 MHz	3.0 dB/100ft
100 MHz	4.3 dB/100ft
200 MHz	6.4 dB/100ft
400 MHz	9.7 dB/100ft
700 MHz	13.7 dB/100ft
900 MHz	16.1 dB/100ft
1000 MHz	17.3 dB/100ft

Power Rating

Frequency [MHz]	Max. Power Rating [W]
1 MHz	4,799 W

10 MHz	1,937 W
50 MHz	782 W
100 MHz	542 W
200 MHz	370 W
400 MHz	248 W
700 MHz	178 W
900 MHz	153 W
1,000 MHz	143 W

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedance	Nom. Velocity
10.1 Ohm/1000ft	3.8 Ohm/1000ft	27.4 pF/ft	53 Ohm	70%

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Rating	Operating
75°C	0°C to +75°C

Bend Radius

Installation Min.
1.6 in

Bulk Cable Weight:	24 lbs/1000ft
Max. Pull Tension:	38 lbs

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	NFPA 262
NEC / UL Compliance:	CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	8240

History

Update and Revision:	Revision Number: 0.318 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[82240 877U500](#) [82240 8771000](#)