



## LC Sine Wave Filter for Motor Drives



- Smooth sine wave without voltage peaks
- Perfect motor protection
- Reduce bearing currents
- Motor frequency up to 200 Hz
- Extended motor cable length capability



### Performance indicators



### Technical specifications

|                                                  |                                                      |
|--------------------------------------------------|------------------------------------------------------|
| <b>Approvals</b>                                 | UL 508 pending                                       |
| <b>Declaration of conformity</b>                 | CE / LVD                                             |
| <b>Design corresponding to</b>                   | IEC 61558-2-20                                       |
| <b>Environmental reliability</b>                 | IEC 60068-2-1                                        |
| <b>Flammability corresponding to</b>             | UL 94 V-2 or better                                  |
| <b>High potential test voltage</b>               | P → E 3000 VAC, 1 minute<br>P → P 2500 VAC, 1 minute |
| <b>Impedance (uk)</b>                            | 8 to 10% @ 400 V, 50 Hz and rated current            |
| <b>Insulation class</b>                          | EIS 200                                              |
| <b>Max. operating voltage</b>                    | 3x 500 VAC + 10%                                     |
| <b>Motor cable length</b>                        | Up to 2,000 m (see graph)                            |
| <b>Motor frequency</b>                           | 70 Hz (up to 200Hz with derating (see graph))        |
| <b>MTBF 1</b>                                    | >100,000 hours                                       |
| <b>Overload capability</b>                       | 1.5x rated current for 1 minute, once per hour       |
| <b>Protection category</b>                       | IP00 (FN 5040)<br>IP20 (FN 5045)                     |
| <b>Rated currents</b>                            | 4.5 to 1200 A @ 45 °C max.                           |
| <b>Residual ripple voltage</b>                   | <5%                                                  |
| <b>Switching frequency</b>                       | See filter selection table                           |
| <b>Temperature range (operation and storage)</b> | - 25 °C to +70 °C (25/070/21)                        |

### Approvals



UL508C up to 260 A. For use with AC or DC drives (power conversion equipment) only


### Features and benefits

- Converts the rectangular PWM output voltage of motor drives into a smooth sine wave with low residual ripple
- Elimination of premature motor damage caused by high dv/dt, overvoltages, cable ringing, motor overheating, and eddy current losses
- Improves bearing life time because of bearing currents caused by circulating currents
- Complies with IEC 60034-17\* and NEMA-MG1 requirements for general purpose motors
- Optional with NEMA 1 protective cover

### Typical applications

- HVAC applications
- Pumps
- Ventilators
- Conveyors
- Compressors
- Elevators
- Cranes
- Medium voltage applications, deployed in front of the step-up transformer
- Retrofit installations with motor drives
- Motor drive with long motor cable
- Motor drive with multiple motors in parallel

### Typical electrical schematic



## Filter selection table

| Filter          | Rated<br>current<br>@ 45 °C/50<br>Hz | Rated<br>current<br>@ 45 °C/100<br>Hz | * Typical<br>motor<br>drive<br>rating | Nominal<br>inductance | Nominal<br>capacitance | Capacitance<br>connection | Min.<br>switching<br>frequency | **<br>Typical<br>power<br>loss | Input/Output<br>connections                                                                                                                                             | Weight |
|-----------------|--------------------------------------|---------------------------------------|---------------------------------------|-----------------------|------------------------|---------------------------|--------------------------------|--------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|
|                 | [A]                                  | [A]                                   | [kW]                                  | [mH]                  | [µF]                   |                           | [kHz]                          | [W]                            |   | [kg]   |
| FN 5040-4.5-82  | 4.5                                  | 4.05                                  | 1.1/1.5                               | 13                    | 2.2                    | Y                         | 4                              | 65                             | -82                                                                                                                                                                     | 3.3    |
| FN 5040-8-82    | 8                                    | 7.2                                   | 2.2/3                                 | 6.9                   | 4.7                    | Y                         | 4                              | 80                             | -82                                                                                                                                                                     | 4.6    |
| FN 5040-10-83   | 10                                   | 9                                     | 4                                     | 5.2                   | 6.8                    | Y                         | 4                              | 90                             | -83                                                                                                                                                                     | 6.1    |
| FN 5040-17-83   | 17                                   | 15.3                                  | 5.5/7.5                               | 3.1                   | 10                     | Y                         | 4                              | 115                            | -83                                                                                                                                                                     | 7.8    |
| FN 5040-24-84   | 24                                   | 21.6                                  | 11                                    | 2.4                   | 10                     | Y                         | 4                              | 150                            | -84                                                                                                                                                                     | 14.4   |
| FN 5040-38-84   | 38                                   | 34.2                                  | 15/18.5                               | 1.6                   | 10                     | Y                         | 4                              | 170                            | -84                                                                                                                                                                     | 25.0   |
| FN 5040-48-85   | 48                                   | 43.2                                  | 22                                    | 1.1                   | 14.7                   | Y                         | 4                              | 260                            | -85                                                                                                                                                                     | 33.0   |
| FN 5040-62-86   | 62                                   | 55.8                                  | 30                                    | 0.85                  | 30                     | Y                         | 3                              | 280                            | -86                                                                                                                                                                     | 36.0   |
| FN 5040-75-87   | 75                                   | 67.5                                  | 37                                    | 0.75                  | 30                     | Y                         | 3                              | 330                            | -87                                                                                                                                                                     | 42.0   |
| FN 5040-115-87  | 115                                  | 103.5                                 | 45/55                                 | 0.5                   | 20                     | Δ                         | 3                              | 500                            | -87                                                                                                                                                                     | 68.0   |
| FN 5040-180-99  | 180                                  | 162                                   | 75/90                                 | 0.3                   | 33                     | Δ                         | 3                              | 680                            | -99                                                                                                                                                                     | 86.0   |
| FN 5040-260-99  | 260                                  | 234                                   | 110/132                               | 0.2                   | 47                     | Δ                         | 3                              | 880                            | -99                                                                                                                                                                     | 125.0  |
| FN 5040-410-99  | 410                                  | 369                                   | 160/200                               | 0.13                  | 66                     | Δ                         | 3                              | 1100                           | -99                                                                                                                                                                     | 184.0  |
| FN 5040-480-99  | 480                                  | 432                                   | 250                                   | 0.11                  | 94                     | Δ                         | 3                              | 1350                           | -99                                                                                                                                                                     | 235.0  |
| FN 5040-660-99  | 660                                  | 594                                   | 315/355                               | 0.14                  | 141                    | Δ                         | 2                              | 2000                           | -99                                                                                                                                                                     | 310.0  |
| FN 5040-750-99  | 750                                  | 675                                   | 400                                   | 0.12                  | 165                    | Δ                         | 2                              | 2800                           | -99                                                                                                                                                                     | 470.0  |
| FN 5040-880-99  | 880                                  | 792                                   | 400/500                               | 0.11                  | 188                    | Δ                         | 2                              | 3400                           | -99                                                                                                                                                                     | 640.0  |
| FN 5040-1200-99 | 1200                                 | 1080                                  | 560/630                               | 0.075                 | 282                    | Δ                         | 2                              | 3800                           | -99                                                                                                                                                                     | 680.0  |
| FN 5045-4.5-44  | 4.5                                  | 4.05                                  | 1.1/1.5                               | 13                    | 2.2                    | Y                         | 4                              | 65                             | -44                                                                                                                                                                     | 4.1    |
| FN 5045-8-44    | 8                                    | 7.2                                   | 2.2/3                                 | 6.9                   | 4.7                    | Y                         | 4                              | 80                             | -44                                                                                                                                                                     | 5.4    |
| FN 5045-10-44   | 10                                   | 9                                     | 4                                     | 5.2                   | 6.8                    | Y                         | 4                              | 90                             | -44                                                                                                                                                                     | 6.9    |
| FN 5045-17-33   | 17                                   | 15.3                                  | 5.5/7.5                               | 3.1                   | 10                     | Y                         | 4                              | 115                            | -33                                                                                                                                                                     | 9.0    |
| FN 5045-24-33   | 24                                   | 21.6                                  | 11                                    | 2.4                   | 10                     | Y                         | 4                              | 150                            | -33                                                                                                                                                                     | 15.6   |
| FN 5045-38-33   | 38                                   | 34.2                                  | 15/18.5                               | 1.6                   | 10                     | Y                         | 4                              | 170                            | -33                                                                                                                                                                     | 18.9   |
| FN 5045-48-34   | 48                                   | 43.2                                  | 22                                    | 1.1                   | 14.7                   | Y                         | 4                              | 260                            | -34                                                                                                                                                                     | 35.8   |
| FN 5045-62-34   | 62                                   | 55.8                                  | 30                                    | 0.85                  | 30                     | Y                         | 3                              | 280                            | -34                                                                                                                                                                     | 37.8   |
| FN 5045-75-35   | 75                                   | 67.5                                  | 37                                    | 0.75                  | 30                     | Y                         | 3                              | 330                            | -35                                                                                                                                                                     | 60.0   |
| FN 5045-115-35  | 115                                  | 103.5                                 | 45/55                                 | 0.5                   | 20                     | Δ                         | 3                              | 500                            | -35                                                                                                                                                                     | 70.0   |
| FN 5045-180-99  | 180                                  | 162                                   | 75/90                                 | 0.3                   | 33                     | Δ                         | 3                              | 680                            | -99                                                                                                                                                                     | 92.0   |
| FN 5045-260-99  | 260                                  | 234                                   | 110/132                               | 0.2                   | 47                     | Δ                         | 3                              | 880                            | -99                                                                                                                                                                     | 131.0  |
| FN 5045-410-99  | 410                                  | 369                                   | 160/200                               | 0.13                  | 66                     | Δ                         | 3                              | 1100                           | -99                                                                                                                                                                     | 198.0  |
| FN 5045-480-99  | 480                                  | 432                                   | 250                                   | 0.11                  | 94                     | Δ                         | 3                              | 1350                           | -99                                                                                                                                                                     | 243.0  |
| FN 5045-660-99  | 660                                  | 594                                   | 315/355                               | 0.14                  | 141                    | Δ                         | 2                              | 2000                           | -99                                                                                                                                                                     | 425.0  |
| FN 5045-750-99  | 750                                  | 675                                   | 400                                   | 0.12                  | 165                    | Δ                         | 2                              | 2800                           | -99                                                                                                                                                                     | 482.0  |
| FN 5045-880-99  | 880                                  | 792                                   | 400/500                               | 0.11                  | 188                    | Δ                         | 2                              | 3400                           | -99                                                                                                                                                                     | 652.0  |
| FN 5045-1200-99 | 1200                                 | 1080                                  | 560/630                               | 0.075                 | 282                    | Δ                         | 2                              | 3800                           | -99                                                                                                                                                                     | 692.0  |


\* General purpose four-pole (1500 r/min) AC induction motor rated 400 V/50 Hz.

\*\* Exact value depends upon the motor cable type and length, switching frequency, motor frequency and further stray parameters within the system.

## Installation

### Filter placement

Lift the filter with appropriate crane using lifting eye bolts – smaller types may be lifted manually by two persons (no lifting eye bolt applicable).



### Wiring and connection


The filter rating has to be compatible with the inverter to which it is to be connected. All inverter manufacturer installation and safety instructions must be fulfilled. The typical block schematic is shown for a motor load but the load can be also multiple motors or a transformer. Inverter and load cable selection/placement should be in accordance with all local electrical standards and regulations. Filters with separate capacitor bank must be connected as follows:

### Required settings



Ensure the drive's switching frequency is set to the required minimum switching frequency (see filter selection table). Higher frequencies are allowed. The mode of operation must be "scalar" (V/Hz). Check the inverter manual whether special settings are necessary. In any doubt contact the inverter manufacturer.

**CAUTION:** If the inverter settings are not in accordance the filter may be damaged.


Never attempt to handle the filter with a forklift!




In order to ensure sufficient air flow, keep a distance of 150 mm above and below the filter to walls or other components. A 20 mm distance on either side is recommended.




## Typical block schematic



## Motor frequency derating




## Max. motor cable length




## Mechanical data FN 5040


### 4.5 to 75 A types



### 115 A types



## 180 to 1200 A types\*



Cable length of capacitor box:

180 to 410 A = 1000 mm

480A to 1200 A = 1500 mm

## Dimensions FN 5040

|          | 4.5 A               | 8 A                 | 10 A              | 17 A              | 24 A               | 38 A               | 48 A               | 62 A               | 75 A               | 115 A              |
|----------|---------------------|---------------------|-------------------|-------------------|--------------------|--------------------|--------------------|--------------------|--------------------|--------------------|
| <b>A</b> | 125                 | 155                 | 155               | 190               | 190                | 230                | 300                | 320                | 305                | 305                |
| <b>B</b> | 77                  | 84                  | 94                | 115               | 116                | 151                | 171                | 190                | 240                | 236                |
| <b>C</b> | 171                 | 212                 | 208               | 224               | 224                | 275                | 355                | 395                | 395                | 495                |
| <b>D</b> | 100                 | 130                 | 123               | 170               | 170                | 180                | 240                | 240                | 240                | 280                |
| <b>E</b> | 55                  | 56                  | 71.5              | 57.5              | 77.5               | 122                | 137                | 132                | 162                | 151                |
| <b>F</b> | 5x8                 | 8x12                | 8x12              | 8x12              | 8x12               | 8x12               | 11x15              | 11x15              | 11x15              | 11x15              |
| <b>G</b> | 2.5 mm <sup>2</sup> | 2.5 mm <sup>2</sup> | 4 mm <sup>2</sup> | 4 mm <sup>2</sup> | 10 mm <sup>2</sup> | 10 mm <sup>2</sup> | 16 mm <sup>2</sup> | 35 mm <sup>2</sup> | 50 mm <sup>2</sup> | 50 mm <sup>2</sup> |
| <b>V</b> | M3                  | M4                  | M4                | M6                | M6                 | M8                 | M8                 | M8                 | M8                 | M8                 |


|          | 180 A     | 260 A     | 410 A     | 480 A     | 660 A     | 750 A     | 880 A | 1200 A    |
|----------|-----------|-----------|-----------|-----------|-----------|-----------|-------|-----------|
| <b>A</b> | 450       | 453       | 490       | 510       | 645       | 665       | 660   | 750       |
| <b>B</b> | 260       | 255       | 355       | 355       | 410       | 468       | 450   | 375       |
| <b>C</b> | 385       | 485       | 600       | 618       | 732       | 670       | 885   | 925       |
| <b>D</b> | 400       | 370       | 430       | 430       | 570       | 570       | 570   | 570       |
| <b>E</b> | 130       | 150       | 194       | 195       | 210       | 220       | 220   | 220       |
| <b>F</b> | 9x13      | 11x15     | 10.5x18.5 | 13x27     | 13x27     | 13x26     | 13x26 | 13x26     |
| <b>H</b> | 328       | 328       | 328       | 328       | 463       | 555       | 463   | 665       |
| <b>I</b> | 170       | 170       | 170       | 270       | 370       | 375       | 370   | 375       |
| <b>J</b> | 200       | 220       | 240       | 220       | 220       | 200       | 220   | 220       |
| <b>K</b> | 300 (150) | 300 (150) | 300 (150) | 300 (150) | 400 (200) | 510 (255) |       | 620 (310) |
| <b>L</b> | 150       | 150       | 150       | 250       | 350       | 350       | 350   | 350       |
| <b>M</b> | 9         | 9         | 9         | 9         | 9         | 9         | 9     | 9         |
| <b>V</b> | M10       | M10       | M10       | M10       | M10       | M10       | M10   | M10       |
| <b>W</b> | 25        | 25        | 40        | 40        | 40        | 40        | 50    | 60        |
| <b>X</b> | 13/15     | 13/15     | 13/16     | 13/20     | 20        | 20        | 14    | 17        |
| <b>Y</b> | 21        | 20        | 25        | 23        | 40        | 40        | 22    | 26        |
| <b>Z</b> | 10.3      | 10.3      | 10.3      | 10.3      | 14        | 14        | 14    | 14        |

All dimensions in mm; 1 inch = 25.4 mm


Tolerances according: ISO 2768-m / EN 22768-m

## Mechanical data FN 5045


### 4.5 to 38 A types




### 48 to 115 A types



### 180 to 480 A types



### 660 to 1200 A types



## Dimensions FN 5045

|          | 4.5 A | 8 A | 10 A | 17 A | 24 A | 38 A | 48 A | 62 A | 75 A | 115 A | 180 A | 260 A | 410 A | 480 A | 660 A | 750 A | 880 A | 1200 A |
|----------|-------|-----|------|------|------|------|------|------|------|-------|-------|-------|-------|-------|-------|-------|-------|--------|
| <b>A</b> | 330   | 330 | 330  | 440  | 440  | 440  | 515  | 515  | 615  | 615   | 650   | 650   | 780   | 780   | 1280  | 1280  | 1280  | 1280   |
| <b>B</b> | 100   | 100 | 100  | 160  | 160  | 160  | 320  | 320  | 370  | 370   | 508   | 508   | 538   | 538   | 794   | 794   | 794   | 794    |
| <b>C</b> | 165   | 165 | 165  | 245  | 245  | 245  | 153  | 153  | 203  | 203   | 400   | 400   | 494   | 494   | 498   | 498   | 550   | 550    |
| <b>D</b> | 310   | 310 | 310  | 412  | 412  | 412  | 488  | 488  | 590  | 590   | 336   | 336   | 336   | 336   | 622   | 622   | 622   | 622    |
| <b>E</b> | 60    | 60  | 60   | 110  | 110  | 110  | 280  | 280  | 330  | 330   | 243   | 243   | 312   | 312   | 315   | 315   | 315   | 315    |
| <b>F</b> | 7     | 7   | 7    | 9    | 9    | 9    | 9    | 9    | 11   | 11    | 14x30 | 14x30 | 14x30 | 14x30 | 14x30 | 14x30 | 14x30 | 14x30  |
| <b>J</b> | M5    | M5  | M5   | M5   | M5   | M5   | M5   | M5   | M8   | M8    | M10   | M10   | M10   | M10   | M10   | M10   | M10   | M10    |
| <b>W</b> |       |     |      |      |      |      |      |      |      |       | 20    | 20    | 25    | 40    | 40    | 40    | 40    | 60     |
| <b>X</b> |       |     |      |      |      |      |      |      |      |       | 15    | 15    | 15    | 15    | 20    | 20    | 20    | 20     |
| <b>Y</b> |       |     |      |      |      |      |      |      |      |       |       |       |       |       | 40    | 40    | 40    | 30/40  |
| <b>Z</b> |       |     |      |      |      |      |      |      |      |       | 9     | 9     | 10.2  | 10.2  | 14    | 14    | 14    | 14     |

All dimensions in mm; 1 inch = 25.4 mm

Tolerances according: ISO 2768-m / EN 22768-m

## Filter output connector cross sections

|                           | <b>-33</b>                                                                          | <b>-34</b>                                                                          | <b>-35</b>                                                                            | <b>-44</b>                                                                            | <b>-82</b>                                                                            |
|---------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|                           |    |    |    |    |    |
| <b>Solid wire</b>         | 16 mm <sup>2</sup>                                                                  | 35 mm <sup>2</sup>                                                                  | 50 mm <sup>2</sup>                                                                    | 10 mm <sup>2</sup>                                                                    | 0.75 - 2.5 mm <sup>2</sup>                                                            |
| <b>Flex wire</b>          | 10 mm <sup>2</sup>                                                                  | 25 mm <sup>2</sup>                                                                  | 50 mm <sup>2</sup>                                                                    | 6 mm <sup>2</sup>                                                                     | 1.0 - 2.5 mm <sup>2</sup>                                                             |
| <b>AWG type wire</b>      | AWG 6                                                                               | AWG 2                                                                               | AWG 1/0                                                                               | AWG 8                                                                                 | AWG 18 - 12                                                                           |
| <b>Recommended torque</b> | 1.5-1.8 Nm                                                                          | 4.0-4.5 Nm                                                                          | 7-8 Nm                                                                                | 1.5-1.8 Nm                                                                            | 1.0-1.2 Nm                                                                            |
|                           | <b>-83</b>                                                                          | <b>-84</b>                                                                          | <b>-85</b>                                                                            | <b>-86</b>                                                                            | <b>-87</b>                                                                            |
|                           |  |  |  |  |  |
| <b>Solid wire</b>         | 0.75-4.0 mm <sup>2</sup>                                                            | 2.5-10.0 mm <sup>2</sup>                                                            | 2.5-25.0 mm <sup>2</sup>                                                              | 0.75-50 mm <sup>2</sup>                                                               | 16.0-50.0 mm <sup>2</sup>                                                             |
| <b>Flex wire</b>          | 1.0-4.0 mm <sup>2</sup>                                                             | 4.0-10.0 mm <sup>2</sup>                                                            | 4.0-16.0 mm <sup>2</sup>                                                              | 0.75-35 mm <sup>2</sup>                                                               | 25.0-50.0 mm <sup>2</sup>                                                             |
| <b>AWG type wire</b>      | AWG 18-10                                                                           | AWG 18-6                                                                            | AWG 22-4                                                                              | AWG 18-0/1                                                                            | AWG 6-0                                                                               |
| <b>Recommended torque</b> | 1.5-1.8 Nm                                                                          | 4.0-4.5 Nm                                                                          | 1.5-1.8 Nm                                                                            | 3.2-3.7 Nm                                                                            | 6.0-8.0 Nm                                                                            |

Please visit [www.schaffner.com](http://www.schaffner.com) to find more details on filter connectors.



## Headquarters, global innovation and development center

### Switzerland

#### Schaffner Group

Nordstrasse 11  
4542 Luterbach  
T +41 32 6816 626  
F +41 32 6816 630  
[info@schaffner.com](mailto:info@schaffner.com)  
<http://www.schaffner.com>



## Sales and application centers

### China

#### Schaffner EMC Ltd. Shanghai

T20-3, No 565 Chuangye Road  
Pudong New Area  
201201 Shanghai  
T +86 21 3813 9500  
F +86 21 3813 9501 / 02  
[cschina@schaffner.com](mailto:cschina@schaffner.com)  
<http://www.schaffner.com.cn/>

### Finland

#### Schaffner Oy

Sauvonrinne 19 H  
08500 Lohja  
T +358 19 35 72 71  
[finlandsales@schaffner.com](mailto:finlandsales@schaffner.com)

### France

#### Schaffner EMC S.A.S.

112 Quai de Bezons  
Boîte postale 133  
95100 Argenteuil  
T +33 1 34 34 30 60  
F +33 1 39 47 02 28  
[francesales@schaffner.com](mailto:francesales@schaffner.com)

### Germany

#### Schaffner Deutschland GmbH

Schoemperlenstrasse 12B  
76185 Karlsruhe  
T +49 721 56910  
F +49 721 569110  
[germanysales@schaffner.com](mailto:germanysales@schaffner.com)

### Italy

#### Schaffner EMC S.r.l.

Via Galileo Galilei 47  
20092 Cinisello Balsamo (MI)  
T +39 02 66 04 30 45/47  
F +39 02 61 23 943  
[italysales@schaffner.com](mailto:italysales@schaffner.com)

### Japan

#### Schaffner EMC K.K.

1-32-12, Kamiyama, Setagaya-ku  
7F Mitsui-seimei Sangenjaya Bldg.  
154-0011 Tokyo  
T +81 3 5712 3650  
F +81 3 5712 3651  
[japansales@schaffner.com](mailto:japansales@schaffner.com)  
<http://www.schaffner.jp>

### Singapore

#### Schaffner EMC Pte Ltd.

Blk 3015A Ubi Road 1  
05-09 Kampong Ubi Industrial Estate  
408705 Singapore  
T +65 6377 3283  
F +65 6377 3281  
[singaporesales@schaffner.com](mailto:singaporesales@schaffner.com)

### Spain

#### Schaffner EMC España

Calle Caléndula 93, Miniparc III, Edificio E,  
Alcobendas  
Miniparc III, Edificio E  
El Soto de la Moraleja  
Alcobendas  
28109 Madrid  
M +34 618 176 133  
T +34 917 912 900  
F +34 917 912 901  
[spainsales@schaffner.com](mailto:spainsales@schaffner.com)

### Sweden

#### Schaffner EMC AB

Turebergstorg 1, 6  
19147 Sollentuna  
T +46 8 5792 1121 / 22  
F +46 8 92 96 90  
[swedensales@schaffner.com](mailto:swedensales@schaffner.com)

### Switzerland

#### Schaffner EMV AG

Nordstrasse 11  
4542 Luterbach  
T +41 32 6816 626  
F +41 32 6816 641  
[sales@schaffner.ch](mailto:sales@schaffner.ch)

### Taiwan R.O.C.

#### Schaffner EMV Ltd.

6 Floor, No. 413  
Rui Guang Road  
114 Neihs District Taipei City  
T +886 2 87525050  
F +886 2 87518086  
[taiwansales@schaffner.com](mailto:taiwansales@schaffner.com)

### Thailand

#### Schaffner EMC Co. Ltd.

Northern Region Industrial Estate  
67 Moo 4 Tambon Ban Klang  
Amphur Muang P.O. Box 14  
51000 Lamphun  
T +66 53 58 11 04  
F +66 53 58 10 19  
[thailandsales@schaffner.com](mailto:thailandsales@schaffner.com)

### UK

#### Schaffner Ltd.

5 Ashville Way  
Molly Millars Lane  
Wokingham  
RG41 2PL Berkshire  
T +44 118 9770070  
F +44 118 9792969  
[uksales@schaffner.com](mailto:uksales@schaffner.com)  
<http://www.schaffner.uk.com>

### USA

#### Schaffner EMC Inc.

52 Mayfield Avenue  
08837 Edison, New Jersey  
T +1 800 367 5566  
T +1 732 225 9533  
F +1 732 225 4789  
[usasales@schaffner.com](mailto:usasales@schaffner.com)  
<http://www.schaffner.com/us>

#### Schaffner MTC LLC

6722 Thirlane Road  
24019 Roanoke, Virginia  
T +1 276 228 7943  
F +1 276 228 7953  
<http://www.schaffner-mtc.com>

#### Schaffner Trencos LLC

2550 Brookpark Road  
44134 Cleveland, Ohio  
T +1 216 741 5282  
F +1 216 741 4860  
<http://schaffner-trencos.com>

To find your local partner within Schaffner's global network: [www.schaffner.com](http://www.schaffner.com)

© 2014 Schaffner Group

The content of this document has been carefully checked and understood. However, neither Schaffner nor its subsidiaries assume any liability whatsoever for any errors or inaccuracies of this document and the consequences thereof. Published specifications are subject to change without notice. Product suitability for any area of application must ultimately be determined by the customer. In all cases, products must never be operated outside their published specifications. Schaffner does not guarantee the availability of all published products. This disclaimer shall be governed by substantive Swiss law and resulting disputes shall be settled by the courts at the place of business of Schaffner Holding AG. Latest publications and a complete disclaimer can be downloaded from the Schaffner website. All trademarks recognized.