



LIGHT PIPE


PREPARATION/INSTALLATION:

1.5±.5 [.06±.02]




NOTES:

1. ROHS COMPLIANT
2. UL 94V-2 FLAMMABILITY RATING
3. -40°C TO 85°C OPERATING TEMPERATURE
4. SUITABLE FOR LIGHT PIPE WITH Ø3.0mm JACKET AND OPTICAL CORE NO GREATER THAN Ø1.5mm
5. DO NOT WAVE SOLDER WITH THIS DEVICE
6. FOR BEST RESULTS USE ONLY NARROW VIEWING ANGLE NON-DIFFUSED LEDS WITH OUTPUT POWER GREATER THAN 100mcd
7. NOT RECOMMENDED FOR DATA COMMUNICATIONS



METRIC

REVISIONS					
REV	DESCRIPTION	ECO	DATE	DWN	APVD
C	REVISED STRIP LENGTH FROM 1.0±.05	0034	09/17/09	BB	KS



UNLESS OTHERWISE SPECIFIED		PRODUCT		NAME	
DIMENSIONS		MATERIAL		INDUSTRIAL FIBER OPTICS	
MILLIMETERS [IN.]		NYLON 66		TEMPE, AZ 85281	
TOLERANCES		FINISH		MOUNT, RIGHT-ANGLE	
0 PLC: ±.1		NONE		LED TO LIGHT PIPE	
1 PLC: ±.25		DRAWN BY B. BIDWELL		SIZE	
2 PLC: ±.127		DATE 11/12/08		SCALE 2:1	
3 PLC: ±.025		CHECKED BY K. STOTZ		PART NUMBER	
4 PLC: ±.013		DATE 09/17/09		51 0331	
ANGLE: ±1/2°		DO NOT SCALE		SHEET 1 OF 1	
REMOVE BURRS AND SHARP EDGES		DATE		REV	
FLATNESS .005 MM PER MM		09/17/09		C	
ALL DIMENSIONS AFTER FINISH		DATE		REV	