

Customer Information Sheet

DRAWING No:- M20-998XXXX

SHEET 2 OF 2


IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



ORDER CODE:

M20-998XXXX

No. OF WAYS PER ROW
02 TO 40

FINISH
05 = GOLD
06 = TIN

SPECIFICATION

MATERIAL:

PINS - BRASS

MOULDING - POLYESTER UL94V-0

FINISH:

05 - GOLD FLASH

06 - 5.0µm TIN

ELECTRICAL:

CURRENT RATING AT 25°C = 3.0A MAX.

CURRENT RATING AT 85°C = 2.0A MAX.

VOLTAGE PROOF AT 50 Hz = 750V AC/DC

CONTACT RESISTANCE (INITIAL) = 20 MILLIOHMS MAX. (TIN), 15 MILLIOHMS MAX. (GOLD)

CONTACT RESISTANCE (AFTER CONDITIONING) = 30 MILLIOHMS MAX. (TIN), 25 MILLIOHMS MAX. (GOLD)

INSULATION RESISTANCE (INITIAL) = 1,000,000 MEGOHMS MIN.

INSULATION RESISTANCE (AFTER CONDITIONING) = 10,000 MEGOHMS MIN.

MECHANICAL:

DURABILITY = 300 OPERATIONS (GOLD), 50 OPERATIONS (TIN)

ENVIRONMENTAL:

TEMPERATURE RANGE = -40°C TO +105°C

PACKING:

BAG

FOR COMPLETE ELECTRICAL AND MECHANICAL SPECIFICATIONS, SEE COMPONENT SPECIFICATION C001XX (LATEST ISSUE).

NOTES:

1. RECOMMENDED HOLE SIZE = Ø1.00mm.

17	06.05.98	4303
16	20.06.96	3374
1	12.02.90	----
ISS.	DATE	C/N
APPROVED:		
CHECKED:		
DRAWN: D. BECK		
CUSTOMER REF.		
ASSEMBLY DRG:		

HARWIN

TOLERANCES

X = ±1mm
XX = ±0.25mm
XXX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±1°
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²

TITLE:

2.54mm PITCH DIL VERTICAL
PIN HEADER (6.1mm)

DRAWING NUMBER:

M20-998XXXX

SHT
2 OF 2

HARWIN INC

U.S.A.

TEL: (812) 285 0055

FAX: (812) 285 0056

HARWIN PLC

UK

TEL: 01705 370451

FAX: 01705 314590

HARWIN PTE

SINGAPORE

TEL: 65 7794909

FAX: 65 7793868