



PRODUCT NO.
SEE TABLE



- NOTES:
1. APPLICABLE PC BOARD THICKNESS: 1.6 mm.
 2. CONTACTS: PHOSPHOR BRONZE ALLOY UNS-C51000, Ø0.460 ROUND WIRE, PLATING SEE TABLE.



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		A FCI www.fciconnect.com	
ltr	ecn no	dr	date			projection		title	
A	V50574	LP	3/15/95	linear	.X ±.3	MM		R/A GANG JACK FILTER ASSY	
B	V51452	LSS	12/5/95		.XX ±.13			8 POS UNSHIELDED SNAP PEG	
C	V90801	RGD	5/12/99	angles	.XXX ±.051			product family MOD JACK	code 213
D	V12594	LP	3/25/02	dr	0° ±2°			size dwg no	sheet 1 of 2
E	M05-0066	MHT	4/15/05	engr					
				chr					
				appd					
sheet index	revision sheet	E	E						
		1	2						

form no. 7530-001-103


cage code
22526

PRODUCT No. ③	PORTS No	DIM A $\begin{smallmatrix} +0.60 \\ -0.00 \end{smallmatrix}$	DIM B ± 0.20	DIM C ± 0.10	DIM D ± 0.15
95673-X01LF	1	15.24	-----	5.715	11.43
95673-X02LF	2	30.48	13.97	12.700	25.40
95673-X03LF	3	44.45	27.94	19.685	39.37
95673-X04LF	4	58.42	41.91	26.670	53.34
95673-X05LF	5	72.39	55.88	33.655	67.31
95673-X06LF	6	86.36	69.85	40.640	81.28
95673-X07LF	7	100.33	83.82	47.625	95.25
95673-X08LF	8	114.30	97.79	54.610	109.22
95673-X09LF	9	128.27	111.76	61.595	123.19
95673-X10LF	10	142.24	125.73	68.580	137.16
95673-X11LF	11	156.21	139.70	75.565	151.13
95673-X12LF	12	170.18	153.67	82.550	165.10

NOTES

1. APPLICABLE PC BOARD THICKNESS: 1.6 mm.
2. CONTACTS: PHOSPHOR BRONZE ALLOY UNS-C51000, $\emptyset 0.460$ ROUND WIRE, PLATING SEE TABLE.
- ③ LF SUFFIX AT THE END OF PART NUMBER IS LEAD FREE.
4. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
- ⑤ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- ⑥ PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

PLATING CODE X	PLATING ⑥
0	30u" G.X.T.
1	15u" GOLD.
3	30u" GOLD.
5	50u" GOLD.



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ± 3	projection	 MM	title	
E					.XX ± 13			R/A GANG JACK FILTER ASSY	
					.XXX ± 0.051			8 POS UNSHIELDED SNAP PEG	
				angles	0° $\pm 2^\circ$	scale	1:1	product family	
				dr	L.POTTERIGER 3/15/95			MOD JACK	
				enr	Y.BELOPOLSKY 3/15/95			code	
				chr	Y.BELOPOLSKY 3/15/95			213	
				appd	Y.BELOPOLSKY 3/15/95			sheet	
sheet index		revision sheet						2 of	