

Product-type designation

SCALANCE XB005



SCALANCE XB005 UNMANAGED INDUSTRIAL ETHERNET SWITCH FOR 10/100MBIT/S; WITH 5 X 10/100MBIT/S TWISTED PAIR- PORTS WITH RJ45-SOCKETS; FOR CONFIGURING SMALL STAR- AND LINE TOPOGRAPHIES; LED-DIAGNOSIS, IP20, 24 V DC POWER SUPPLY, INCL. MANUAL

Transmission rate

Transfer rate / 1	10 Mbit/s
Transfer rate / 2	100 Mbit/s

Interfaces

Number of electrical/optical connections / for network components or terminal equipment / maximum	5
Number of electrical connections	
• for network components and terminal equipment	5
• for power supply	1
Design of electrical connection	
• for network components and terminal equipment	RJ45 port
• for power supply	3-pole terminal block

Supply voltage, current consumption, power loss

Type of voltage / of supply voltage	DC
Supply voltage / external	24 V
• minimum	19.2 V
• maximum	28.8 V
Product component / fusing at power supply input	Yes
Consumed current / maximum	0.07 A
Active power loss / at 24 V / for DC	1.68 W

Permitted ambient conditions

Ambient temperature

- during operating -10 ... +60 °C
- during storage -40 ... +80 °C
- during transport -40 ... +80 °C

Relative humidity

- at 25 °C / without condensation / during operating / maximum 95 %

Protection class IP

IP20

Design, dimensions and weight

Design

Box

Width

45 mm

Height

100 mm

Depth

87 mm

Net weight

0.165 kg

Type of mounting

- 35 mm DIN rail mounting Yes
- wall mounting Yes

Standards, specifications, approvals

Standard

- for safety / of CSA and UL UL 60950-1, CSA C22.2 No. 60950-1
- for emitted interference EN 61000-6-4 (Class A)
- for interference immunity EN 61000-6-2

Verification of suitability

EN 61000-6-2, EN 61000-6-4

- CE mark Yes
- C-Tick Yes
- KC approval Yes

Marine classification association

- Det Norske Veritas (DNV) No
- Germanische Lloyd (GL) No
- Lloyds Register of Shipping (LRS) No
- Nippon Kaiji Kyokai (NK) No
- Polski Rejestr Statkow (PRS) No

letzte Änderung:

May 28, 2012