



SIZE :

50x50x15mm (1.97"x1.97"x0.59")

CONSTRUCTION :

Glass fiber reinforced plastic

Impeller and housing PBT are UL 94V-0 rating

OPERATING TEMPERATURE :

Ball bearing -30°C to +75°C

Sleeve bearing -10°C to +70°C

INSULATION RESISTANCE :

10meg Ohm min. at 500 VDC

(between frame and terminal)

DIELECTRIC STRENGTH :

5mA max. at 500 VAC 60Hz one minute

(between frame and terminal)

FUNCTION :

frequency generator signal option

WEIGHT :

30 grams


Specifications

Specifications are subject to change without notice

MODEL NO.	BEARING	RATED VOLTAGE	OPERATING VOLTAGE RANGE	RATED CURRENT	RATED INPUT POWER	SPEED R.P.M.	MAX. AIR FLOW		MAX. AIR PRESSURE		NOISE dB-A
		VDC	V	A	W		m ³ /min	CFM	mmH ₂ O	IN H ₂ O	
BP501512M	Ball	12	10.2-13.8	0.15	1.80	5600	0.45	15.75	5.16	0.20	35
SP501512M	Sleeve										
BP501512H	Ball	12	10.2-13.8	0.19	2.28	6300	0.49	17.22	5.93	0.23	38
SP501512H	Sleeve										

* 24V is available

Dimensions (mm)



Performance Curve

