

Datasheet

SPD II & III – AC Surge Protector



The SPD II range of surge protectors are used for transient surge protection of single and multi-phase power circuits at the main electrical panel. SPD IIIs are for the protection of individual electrical devices. They provide common-mode protection (between each Line and Ground), with impulse discharge capacity (Imax) 40kA for SPD II and 20kA for SPD III.

The SPD design is based on high-energy varistors (MOVs) equipped with thermal disconnects and integral failure indicators. A remote signaling contact for disconnection indication is standard on each unit. For ease of replacement, varistors are housed in pluggable modules with connections that are mechanically keyed to the base to prevent incorrect arrestor module replacement.

Typical applications include low voltage distribution or protection of industrial control systems, equipment assemblies and devices.

Weidmüller, Canada

10 Spy Court
Markham, Ontario L3R 5H6
Telephone: (800) 268-4080
Facsimile: (877) 300-5635
Email: info1@weidmuller.ca
Website: www.weidmuller.ca

Weidmüller, Mexico

Bldv. Hermanos Serdán 698,
Col. San Rafael Oriente
Puebla, Puebla, Mexico
C.P. 72029
Telephone: 01 222 2686267
Facsimile: 01 222 2686219
Email: clientes@weidmuller.com.mx
Website: www.weidmuller.com.mx

Weidmüller, United States

821 Southlake Blvd.
Richmond, Virginia 23236
Telephone: (800) 849-9343
Facsimile: (804) 379-2593
Email: info@weidmuller.com
Website: www.weidmuller.com

SPD II & III - AC Surge Protectors

For transient voltage protection of single and multi-phase circuits, in the main electrical panel, downstream of the main circuit breaker, or in control panels.

Technical Data


AC Network
Connection Mode
Max. Operating Voltage (MCOV)
TOV Withstand
Leakage Current at Uc
Follow Current
UL Nominal Discharge Current (In), 15 impulses 8/20 μs
Max. Discharge Current (Imax), 1 impulse 8/20 μs
UL Voltage Protection Rating (VPR)
Protection Level (Up)
UL Short-Circuit Current Rating (SCCR)
AC System
Thermal Disconnecter
Overcurrent Protection
Dimensions (mm)
Connection
Remote Signal Indicator
Mounting
Operating Temp
Operating Altitude (Max.)
Relative Humidity
Enclosure Material
Environmental Rating
Weight

Approvals

IEC 61643-1 - INTERNATIONAL
EN 61643-11 - EUROPE
NF EN 61643-11 - FRANCE
UL1449 3rd Edition - USA and CANADA
RoHS

Ordering Data

Surge Protector
Bus bars




SPD II 120V/40kA



120/240V, 120/208V
1 Pole, L-N or L-G
150VAC
150VAC
<1mA
none
20kA
40kA
500V
0.9kV
25kAIC
Single-phase
UL 60691
Time Delay - 125A Max.
90 x 18 x 67
Screw terminals, #4 AWG Max.
250VAC Max, 2A
Din-rail, TS35
-50°C to +85°C
13,000 ft (4,000m)
5 to 95% non-condensing, up to 100% external
Thermoplastic UL94-V0
IP20
3.4 oz

Class I, Class II
Class I, Class II
Class I, Class II
Low Voltage SPD
Directive 2002/95/EC

Type	Part No.
SPD II 120V/40kA	6720005410
Type	Part No.
SPD 2P LINK	6720005417
SPD 3P LINK	6720005418
SPD 4P LINK	6720005419




SPD II 230V/40kA



220/380V, 240/415V
1 Pole, L-N or L-G
275VAC
275VAC
<1mA
none
20kA
40kA
900V
1.25kV
25kAIC
Single-phase
UL 60691
Time Delay - 125A Max.
90 x 18 x 67
Screw terminals, #4 AWG Max.
250VAC Max, 2A
Din-rail, TS35
-50°C to +85°C
13,000 ft (4,000m)
5 to 95% non-condensing, up to 100% external
Thermoplastic UL94-V0
IP20
3.4 oz

Class I, Class II
Class I, Class II
Class I, Class II
Low Voltage SPD
Directive 2002/95/EC

Type	Part No.
SPD II 230V/40kA	6720005411
Type	Part No.
SPD 2P LINK	6720005417
SPD 3P LINK	6720005418
SPD 4P LINK	6720005419



For transient voltage protection of single and multi-phase circuits, in the main electrical panel, downstream of the main circuit breaker, or in control panels.

Technical Data

AC Network
Connection Mode
Max. Operating Voltage (MCOV)
TOV Withstand
Leakage Current at Uc
Follow Current
UL Nominal Discharge Current (In), 15 impulses 8/20 µs
Max. Discharge Current (Imax), 1 impulse 8/20 µs
UL Voltage Protection Rating (VPR)
Protection Level (Up)
UL Short-Circuit Current Rating (SCCR)
AC System
Thermal Disconnecter
Overcurrent Protection
Dimensions (mm)
Connection
Remote Signal Indicator
Mounting
Operating Temp
Operating Altitude (Max.)
Relative Humidity
Enclosure Material
Environmental Rating
Weight

Approvals

IEC 61643-1 - INTERNATIONAL
EN 61643-11 - EUROPE
NF EN 61643-11 - FRANCE
UL1449 3rd Edition - USA and CANADA
RoHS

Ordering Data

Surge Protector
Bus bars

SPD II 277V/40kA



220/380V, 277V
1 Pole, L-N or L-G
400VAC
400VAC
<1mA
none
20kA
40kA
1500V
1.8kV
25kAIC
Single-phase
UL 60691
Time Delay - 125A Max.
90 x 18 x 67
Screw terminals, #4 AWG Max.
250VAC Max, 2A
Din-rail, TS35
-50°C to +85°C
13,000 ft (4,000m)
5 to 95% non-condensing, up to 100% external
Thermoplastic UL94-V0
IP20
3.4 oz

Class I, Class II
Class I, Class II
Class I, Class II
Low Voltage SPD
Directive 2002/95/EC

Type	Part No.
SPD II 277V/40kA	6720005412
Type	Part No.
SPD 2P LINK	6720005417
SPD 3P LINK	6720005418
SPD 4P LINK	6720005419



SPD II 480V/40kA



347/600V, 480V
1 Pole, L-N or L-G
550VAC
550VAC
<1mA
none
20kA
40kA
1800V
2.5kV
25kAIC
Single-phase
UL 60691
Time Delay - 125A Max.
90 x 18 x 67
Screw terminals, #4 AWG Max.
250VAC Max, 2A
Din-rail, TS35
-50°C to +85°C
13,000 ft (4,000m)
5 to 95% non-condensing, up to 100% external
Thermoplastic UL94-V0
IP20
3.4 oz

Class I, Class II
Class I, Class II
Class I, Class II
Low Voltage SPD
Directive 2002/95/EC

Type	Part No.
SPD II 480V/40kA	6720005413
Type	Part No.
SPD 2P LINK	6720005417
SPD 3P LINK	6720005418
SPD 4P LINK	6720005419



SPD II bus bars

For transient voltage protection of multi-phase circuits with TT grounding systems.

SPD II N/PE





Technical Data

Network	230/400V, 120/208V
Max. Operating Voltage (MCOV)	255VAC
TOV Withstand	400VAC
Leakage Current at Uc	none
Follow Current	100A
Nominal Discharge Current (In), 15 impulses 8/20 µs	20kA
Max. Discharge Current (Imax), 1 impulse 8/20 µs	40kA
Protection Level (Up)	1.5kV
UL Short-Circuit Current Rating (SCCR)	25kAIC
Dimensions (mm)	90 x 18 x 67
Connection	Screw terminals, #4 AWG Max.
Mounting	Din-rail, TS35
Operating Temp	-40°C to +85°C
Enclosure Material	Thermoplastic UL94-V0
Environmental Rating	IP20
Approvals	
IEC 61643-1 - INTERNATIONAL	Class II
EN 61643-11 - EUROPE	Class II
NF EN 61643-11 - FRANCE	Class II
UL1449 3rd Edition - USA and CANADA	Low Voltage SPD

Ordering Data

Surge Protector	Type	Part No.
	SPD II N/PE	6720005414
Bus bars	Type	Part No.
	SPD S LINK 1/3	6720005461



SPD II bus bars

For devices with single phase voltage supplies

- Protects L & N conductors (common and differential modes)
- Integrated contact for remote status indication
- Local status indicator on arrester
- Quick replacement with pluggable arrester

SPD II 120V/G/40kA



SPD II 240V/G/40kA



Technical Data

AC Network	120V
Connection Mode	TN-TT
Max. Operating Voltage (MCOV)	150VAC
TOV Withstand	150VAC
Leakage Current at U_c	<1mA
Protection Mode	MC/MD
Nominal Discharge Current (I_n), 15 impulses 8/20 μ s	20kA
Max. Discharge Current (I_{max}), 1 impulse 8/20 μ s	40kA
Protection Level (U_p)	1.5/0.9kV
Residual Voltage @ 5k	0.6kV
Short-Circuit Current Rating (SCCR)	10kAIC
AC System	Single-phase
Thermal Disconnecter	Internal
Overcurrent Protection	Fuses type gG 50A Max.
Dimensions (mm)	90 x 18 x 58
Connection	Screw terminals, #4AWG Max.
Disconnection Indicator	2 mechanical indicators
Installation Ground Fault Breaker	Type S or delayed
Mounting	Din-rail, TS35
Operating Temp	-40°C to +85°C
Operating Altitude	13,000 ft (4,000m)
Relative Humidity	5 to 95% non-condensing, up to 100% external
Enclosure Material	Thermoplastic UL94-V0
Environmental Rating	IP20
Weight	3.4 oz
Approvals	
IEC 61643-1 - INTERNATIONAL	
EN 61643-11 - EUROPE	
NF EN 61643-11 - FRANCE	
UL1449 3rd Edition - USA and CANADA	

120V
TN-TT
150VAC
150VAC
<1mA
MC/MD
20kA
40kA
1.5/0.9kV
0.6kV
10kAIC
Single-phase
Internal
Fuses type gG 50A Max.
90 x 18 x 58
Screw terminals, #4AWG Max.
2 mechanical indicators
Type S or delayed
Din-rail, TS35
-40°C to +85°C
13,000 ft (4,000m)
5 to 95% non-condensing, up to 100% external
Thermoplastic UL94-V0
IP20
3.4 oz
Low Voltage SPD - Test Class II
Low Voltage SPD - Test Class II
Low Voltage SPD - Test Class II
UL file E338172, CSA file 253665



230V
TN
255VAC
255VAC
<1mA
MC/MD
20kA
40kA
1.5/1.25kV
0.9kV
10000 A
Single-phase
Internal
Fuses type gG 50A Max.
90 x 18 x 67
Screw terminals, #4AWG Max.
2 mechanical indicators
Type S or delayed
Din-rail, TS35
-40°C to +85°C
13,000 ft (4,000m)
5 to 95% non-condensing, up to 100% external
Thermoplastic UL94-V0
IP20
3.4 oz
Low Voltage SPD - Test Class
Low Voltage SPD - Test Class
Parafoudre Basse Tension - Essais Classe
UL file E338172, CSA file 253665

Ordering Data


Surge Protector
Bus bars

Type	Part No.
SPD II 120V/G/40kA	6720005415
Type	Part No.
SPD 2P LINK	6720005417
SPD 3P LINK	6720005418
SPD 4P LINK	6720005419

Type	Part No.
SPD II 240V/G/40kA	6720005503
Type	Part No.
SPD 2P LINK	6720005417
SPD 3P LINK	6720005418
SPD 4P LINK	6720005419



SPD II bus bars



For transient voltage protection of single-phase devices.

- Protects 2 conductors - typically L & N, but could also be L1 & L2
- Integrated contact for remote status indication
- Pluggable replaceable arrester

SPD III 120V/40kA



Technical Data

AC Network	120V
Connection Mode	TN
Max. Operating Voltage (MCOV)	150VAC
TOV Withstand	150VAC
Max load current	16A
Leakage Current at Uc	<1mA
Follow Current	none
Nominal Discharge Current (In), 15 impulses 8/20 µs	20kA
Max. Discharge Current (Imax), 1 impulse 8/20 µs	40kA
Protection Level (Up)	1.5/0.9kV
Short-Circuit Current Rating (SCCR)	10kAIC
AC System	Single-phase
Thermal Disconnecter	UL 60691 Internal
Overcurrent Protection	Fuses type gG - 50A Max.
Dimensions (mm)	90 x 18 x 58
Connection	Screw terminals, #4 AWG Max.
Remote Signal Indicator	250VAC Max, 2A
Mounting	Din-rail, TS35
Operating Temp	-40°C to +85°C
Operating Altitude	13,000 ft (4,000m)
Relative Humidity	5 to 95% non-condensing, up to 100% external
Enclosure Material	Thermoplastic UL94-V0
Environmental Rating	IP20
Weight	3.4 oz

Approvals



IEC 61643-1 - INTERNATIONAL	Class II, Class III
EN 61643-11 - EUROPE	Class II, Class III
NF EN 61643-11 - FRANCE	Class II, Class III
UL1449 3rd Edition - USA and CANADA	UL file E338172, file 253665

Ordering Data


Surge Protector

120V
TN
150VAC
150VAC
16A
<1mA
none
20kA
40kA
1.5/0.9kV
10kAIC
Single-phase
UL 60691 Internal
Fuses type gG - 50A Max.
90 x 18 x 58
Screw terminals, #4 AWG Max.
250VAC Max, 2A
Din-rail, TS35
-40°C to +85°C
13,000 ft (4,000m)
5 to 95% non-condensing, up to 100% external
Thermoplastic UL94-V0
IP20
3.4 oz

Type	Part No.
SPD III 120V/40kA	6720005416




Basic configurations 1



SPD parts needed:

Nom. V	Description	Qty	Qty	Qty	Part No.
110/120V	SPD II 120V/40kA	1	2	3	6720005410
230/240V	SPD II 230V 40kA	1	2	3	6720005411
277V	SPD II 277V 40kA	1	2	3	6720005412
480V	SPD II 480V 40kA	1	2	3	6720005413
All	SPD 2P Link	0	1	0	6720005417
All	SPD 3P Link	0	0	1	6720005418


Basic configurations 2



SPD parts needed:


Nom. V	Description	Qty	Part No.
110/120V	SPD II 120V/40kA	4	6720005410
230/240V	SPD II 230V 40kA	4	6720005411
277V	SPD II 277V 40kA	4	6720005412
480V	SPD II 480V 40kA	4	6720005413
All	SPD 4P Link	1	6720005419

Basic configurations 3



SPD parts needed:

Nom. V	Description	Qty	Part No.
120V	SPD II 120V/G/40kA	1	6720005415



SPD parts needed:

Nom. V	Description	Qty	Part No.
110/120V	SPD II 120V/40kA	3	6720005410
230/240V	SPD II 230V 40kA	3	6720005411
277V	SPD II 277V 40kA	3	6720005412
480V	SPD II 480V 40kA	3	6720005413
All	SPD II N/PE	1	6720005414
All	SPD S Link 1/3	1	6720005461