



SWITCH FUNCTION	
POS. 1	POS. 2
OFF	(ON)
OPEN	1-2



(ON) = MOMENTARY



▲ SPST
CONTACT CONFIGURATION

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER PLATED
5. RATING: 2A 48VDC
6. ELECTRIC LIFE: 50,000 CYCLES (B)
7. INSULATION RESISTANCE: 1,000 MΩ MIN.
8. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
10. OPERATING TEMP.: -20°C to 55°C
- ▲ 11. TRAVEL: 1.8mm
12. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 13. ILLUMINATION COLOR: NONE
14. HARDWARE SUPPLIED: O-RING AND HEXNUT (NOT SHOWN)
15. 2002/95/EC (ROHS) COMPLIANT
16. INGRESS PROTECTION: IP65 (B)



B	21526	DRAWING UPDATES	7/29/14	EBP
A	20675	RELEASE FOR PRODUCTION	7/24/12	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV6F240SS

SCALE
2:1DATE
7/24/2012DR
rcDWG
52-PV6F240SSREV
B