






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		A	REV PER ECO 06-002539	07APR06	GB	JH



- 1 ZINC PER QQ-Z-363.
- 2 POLYPHENYLENE OXIDE.
- 3 PHOSPHOR BRONZE PER QQ-B-750.
- 4 TIN PLATE PER ASTM-B-545, 3.05 μm [.000120] MINIMUM THICK.
- 5 SILVER PLATE PER QQ-S-365, 1.27 μm [.000050] MINIMUM THICK.
6. WHEN NOT MATED, THE SIGNAL AND SWITCHING CONTACTS ARE ON A COMMON CIRCUIT. WHEN A BNC PLUG IS MATED, THE CIRCUIT IS OPENED.
7. THE CENTER CONTACT PIN OF MATING BNC PLUGS MAY BE RECESSED UP TO 0.51 [.020] MAXIMUM FROM THE TIP OF THE OUTER CONTACT REFERENCE PLANE.



RECOMMENDED PCB LAYOUT
(TOLERANCE: ±0.08 [±.003] UNLESS OTHERWISE SPECIFIED)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA – CHK J. HAVENER APVD J. LIPPERT	28APR2005 DOCK5 28APR2005 28APR2005	tyco Electronics		Tyco Electronics Corporation Harrisburg, PA 17105–3608	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108–1929		NAME JACK, VERTICAL, SWITCHING, PCB, BNC			
	0 PLC ± – 1 PLC ± – 2 PLC ± 0.20 [.008] 3 PLC ± – 4 PLC ± – ANGLES ± –	APPLICATION SPEC –					
MATERIAL –	FINISH –	WEIGHT –	A2	SIZE 00779	CAGE CODE G=6274314	DRAWING NO	RESTRICTED TO –
CUSTOMER DRAWING					SCALE 4:1	SHEET 1 of 1	REV A