




NOTES:

- 1) MATERIALS:
HOUSING - LIQUID CRYSTAL POLYMER (LCP), GLASS FILLED,
UL94V-0, COLOR: BLACK
TERMINALS - COPPER ALLOY
- 2) TERMINAL FINISH:
30 MICROINCH/0.76 MICROMETER MINIMUM GOLD IN CONTACT AREA AND
50 MICROINCH/1.27 MICROMETER MINIMUM TIN IN TAIL AREA OVER
NICKEL UNDERPLATE OVERALL.
- 3) ASSEMBLY MATES WITH MOLEX PART NUMBER 71660-7***.
CONFORMS TO PRODUCT SPECIFICATION PS-71660.
- 4) RECOMMENDED P.C. BOARD THICKNESS IS .062/1.6 MILLIMETER.
- 5) FOUR DIGIT DATE CODE TO BE LOCATED ON SURFACE
AS SHOWN.
- 6) PRODUCT PACKAGED PER SPECIFICATION PK-71660.



NOTE FOR LEAD FREE CONVERSION:

THE PRIMARY SHIPPING CARTON WILL BE
LABELED "COMPLIANT TO RoHS DIRECTIVE
2002/95/EC AND ELV ANNEX II OF
DIRECTIVE 2000/53/EC". CARTONS WITHOUT
THIS LABEL MAY CONTAIN PRODUCT WITH
LEAD.

L	LEAD FREE CONV ECN UCP2004-2096 RKADAMS 04/04/26
K	REVISED PER ECN U71314 ACHAMMER 97-4-28
J	REVISED PER ECN U70133 ACHAMMER 96-8-7
I	REVISED PER ECN U61477 7-3-96 DGA
H	REVISED PER ECN U61278 5-2-96 DGA
G	REVISED PER ECN U60641 11-28-95 DRS
F	REVISED PER ECN U60564 11-8-95 RAN
E	REVISED PER ECN U50229 9-23-94 RAN
D	REVISED PER ECN U40090 8-30-94 RAN
C	REVISED PER ECN U40506 4-15-94 RAN
B	REVISED PER ECN U40305 3-4-94 RAN
A	INITIAL RELEASE PER ECN U51832 12-15-93 RAN

2	K
I	L
MFG.	SH.
REV.	LTR.
REV.	REVISIONS

DIMENSIONS SHOWN (METRIC) INCH UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR $\pm 1/2^\circ$		TITLE SALES ASSEMBLY EBBI 50D, VERTICAL PLUG BLIND MATE CONNECTOR													
<table border="1"> <tr> <th>INCH</th> <th>METRIC</th> </tr> <tr> <td>3 PLACE $\pm .005$</td> <td>---</td> </tr> <tr> <td>2 PLACE $\pm .01$</td> <td>---</td> </tr> <tr> <td>1 PLACE ---</td> <td>---</td> </tr> </table>		INCH	METRIC	3 PLACE $\pm .005$	---	2 PLACE $\pm .01$	---	1 PLACE ---	---	<table border="1"> <tr> <td>FILE NAME ST1661X7</td> <td>SHEET NO. 1 OF 2</td> </tr> <tr> <td>DATE 11/17/93</td> <td>DATE 11/17/93</td> </tr> </table>		FILE NAME ST1661X7	SHEET NO. 1 OF 2	DATE 11/17/93	DATE 11/17/93
INCH	METRIC														
3 PLACE $\pm .005$	---														
2 PLACE $\pm .01$	---														
1 PLACE ---	---														
FILE NAME ST1661X7	SHEET NO. 1 OF 2														
DATE 11/17/93	DATE 11/17/93														
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		PART NO. SEE TABLE													
<table border="1"> <tr> <td>DRWG. BY RAN</td> <td>CHK'D. BY RAN</td> </tr> <tr> <td>APP'D. BY CAB</td> <td>SCALE 4: 1</td> </tr> </table>		DRWG. BY RAN	CHK'D. BY RAN	APP'D. BY CAB	SCALE 4: 1	<table border="1"> <tr> <td>THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td> <td>DIV. C</td> </tr> </table>		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	DIV. C						
DRWG. BY RAN	CHK'D. BY RAN														
APP'D. BY CAB	SCALE 4: 1														
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	DIV. C														

