





4

3

2

1


LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION		DATE	APVD
			T7	REVISED PER ECO 12-016336		12SEPT12	PD



- 1 SUPPLIED IN LOOSE PIECE.
- 2 THIS PART ACCEPTS .250 SERIES FASTON FLAG RECEPTACLES PART NUMBERS 41531, 41532, 42511, 60641 AND 60645.
- 3 SEE CP-23587 FOR RECOMMENDED TAB DETAILS.
- 4 MAX INSULATION IS .210.

5 GLOW WIRE APPROVED, CONTACT TYCO ELECTRONICS FOR ENGN SPECIFICATIONS, ALL WALL THICKNESSES ARE BETWEEN 0.4mm AND 3.0mm.

150° C	4/6 NYLON – BLACK	1-480307-9
–	5	1-480307-8
120° C	V0, 6/66 NYLON – NATURAL	1-480307-7
150° C	4/6 NYLON – NATURAL	1-480307-6
125° C	6/6 NYLON – NATURAL	1-480307-1
UL TEMP RATING	MATERIAL/COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 1/24/97	 TE Connectivity						
		CHK MS FEHER 1/24/97							
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R BEAVER 1/24/97	NAME						
	0 PLC ± -	PRODUCT SPEC	INSULATION POD, AMPIP-POST						
	1 PLC ± -	—							
	2 PLC ± -	APPLICATION SPEC	—						
	3 PLC ± .015	—							
4 PLC ± -	WEIGHT —	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO			
MATERIAL	FINISH	A3		00779		C-480307		—	
SEE TABLE	SEE TABLE	CUSTOMER DRAWING				SCALE	SHEET		REV
						4:1	1 OF 1		T7