


# SN65C3222, SN75C3222

## 3-V TO 5.5-V MULTICHANNEL RS-232 COMPATIBLE LINE DRIVER/RECEIVER

SLLS534B – MAY 2002 – REVISED OCTOBER 2004

- Operates With 3-V to 5.5-V  $V_{CC}$  Supply
- Operates Up To 1 Mbit/s
- Low Standby Current . . . 1  $\mu$ A Typ
- External Capacitors . . .  $4 \times 0.1 \mu$ F
- Accepts 5-V Logic Input With 3.3-V Supply
- RS-232 Bus-Pin ESD Protection Exceeds  $\pm 15$  kV Using Human-Body Model (HBM)
- Applications
  - Battery-Powered Systems, PDAs, Notebooks, Laptops, Palmtop PCs, and Hand-Held Equipment

DB, DW, OR PW PACKAGE  
(TOP VIEW)



NC – No internal connection

### description/ordering information

The SN65C3222 and SN75C3222 consist of two line drivers, two line receivers, and a dual charge-pump circuit with  $\pm 15$ -kV ESD protection pin to pin (serial-port connection pins, including GND). The devices provide the electrical interface between an asynchronous communication controller and the serial-port connector. The charge pump and four small external capacitors allow operation from a single 3-V to 5.5-V supply. The devices operate at data signaling rates up to 1 Mbit/s and a driver output slew rate of 24 V/ $\mu$ s to 150 V/ $\mu$ s.

The SN65C3222 and SN75C3222 can be placed in the power-down mode by setting  $\overline{\text{PWRDOWN}}$  low, which draws only 1  $\mu$ A from the power supply. When the devices are powered down, the receivers remain active while the drivers are placed in the high-impedance state. Also, during power down, the onboard charge pump is disabled,  $V+$  is lowered to  $V_{CC}$ , and  $V-$  is raised toward GND. Receiver outputs also can be placed in the high-impedance state by setting  $\overline{\text{EN}}$  high.

### ORDERING INFORMATION

| $T_A$         | PACKAGE <sup>†</sup> |              | ORDERABLE PART NUMBER | TOP-SIDE MARKING |
|---------------|----------------------|--------------|-----------------------|------------------|
| –0°C to 70°C  | SOIC (DW)            | Tube of 25   | SN75C3222DW           | 75C3222          |
|               |                      | Reel of 2000 | SN75C3222DWR          |                  |
|               | SSOP (DB)            | Reel of 2000 | SN75C3222DBR          | CA3222           |
|               | TSSOP (PW)           | Tube of 70   | SN75C3222PW           | CA3222           |
|               |                      | Reel of 2000 | SN75C3222PWR          |                  |
| –40°C to 85°C | SOIC (DW)            | Tube of 25   | SN65C3222DW           | 65C3222          |
|               |                      | Reel of 2000 | SN65C3222DWR          |                  |
|               | SSOP (DB)            | Reel of 2000 | SN65C3222DBR          | CB3222           |
|               | TSSOP (PW)           | Tube of 70   | SN65C3222PW           | CB3222           |
|               |                      | Reel of 2000 | SN65C3222PWR          |                  |

<sup>†</sup> Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at [www.ti.com/sc/package](http://www.ti.com/sc/package).



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS  
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 2004, Texas Instruments Incorporated

SN65C3222, SN75C3222  
3-V TO 5.5-V MULTICHANNEL RS-232 COMPATIBLE LINE DRIVER/RECEIVER

SLLS534B – MAY 2002 – REVISED OCTOBER 2004

Function Tables

EACH DRIVER

| INPUTS |         | OUTPUT<br>DOUT |
|--------|---------|----------------|
| DIN    | PWRDOWN |                |
| X      | L       | Z              |
| L      | H       | H              |
| H      | H       | L              |


H = high level, L = low level, X = irrelevant,  
Z = high impedance

EACH RECEIVER

| INPUTS |    | OUTPUT<br>ROUT |
|--------|----|----------------|
| RIN    | EN |                |
| L      | L  | H              |
| H      | L  | L              |
| X      | H  | Z              |
| Open   | L  | H              |

H = high level, L = low level, X = irrelevant,  
Z = high impedance (off), Open = input  
disconnected or connected driver off

logic diagram (positive logic)



# SN65C3222, SN75C3222

## 3-V TO 5.5-V MULTICHANNEL RS-232 COMPATIBLE LINE DRIVER/RECEIVER

SLLS534B – MAY 2002 – REVISED OCTOBER 2004

### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>

|                                                                              |                            |
|------------------------------------------------------------------------------|----------------------------|
| Supply voltage range, $V_{CC}$ (see Note 1)                                  | –0.3 V to 6 V              |
| Positive output supply voltage range, $V+$ (see Note 1)                      | –0.3 V to 7 V              |
| Negative output supply voltage range, $V-$ (see Note 1)                      | 0.3 V to –7 V              |
| Supply voltage difference, $V+ - V-$ (see Note 1)                            | 13 V                       |
| Input voltage range, $V_I$ : Drivers, $\overline{EN}$ , $\overline{PWRDOWN}$ | –0.3 V to 6 V              |
| Receivers                                                                    | –25 V to 25 V              |
| Output voltage range, $V_O$ : Drivers                                        | –13.2 V to 13.2 V          |
| Receivers                                                                    | –0.3 V to $V_{CC} + 0.3$ V |
| Package thermal impedance, $\theta_{JA}$ (see Notes 2 and 3): DB package     | 70°C/W                     |
| DW package                                                                   | 58°C/W                     |
| PW package                                                                   | 83°C/W                     |
| Operating virtual junction temperature, $T_J$                                | 150°C                      |
| Storage temperature range, $T_{stg}$                                         | –65°C to 150°C             |

<sup>†</sup> Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTES: 1. All voltages are with respect to network GND.

2. Maximum power dissipation is a function of  $T_J(\text{max})$ ,  $\theta_{JA}$ , and  $T_A$ . The maximum allowable power dissipation at any allowable ambient temperature is  $P_D = (T_J(\text{max}) - T_A)/\theta_{JA}$ . Operating at the absolute maximum  $T_J$  of 150°C can affect reliability.

3. The package thermal impedance is calculated in accordance with JEDEC 51-7.

### recommended operating conditions (see Note 4 and Figure 5)

|                 |                                             |                                             |                         | MIN | NOM | MAX | UNIT |    |
|-----------------|---------------------------------------------|---------------------------------------------|-------------------------|-----|-----|-----|------|----|
| Supply voltage  |                                             | V <sub>CC</sub> = 3.3 V                     |                         | 3   | 3.3 | 3.6 | V    |    |
|                 |                                             | V <sub>CC</sub> = 5 V                       |                         | 4.5 | 5   | 5.5 |      |    |
| V <sub>IH</sub> | Driver and control high-level input voltage | DIN, $\overline{EN}$ , $\overline{PWRDOWN}$ | V <sub>CC</sub> = 3.3 V | 2   |     |     | V    |    |
|                 |                                             |                                             | V <sub>CC</sub> = 5 V   | 2.4 |     |     |      |    |
| V <sub>IL</sub> | Driver and control low-level input voltage  | DIN, $\overline{EN}$ , $\overline{PWRDOWN}$ |                         |     | 0.8 |     | V    |    |
| V <sub>I</sub>  | Driver and control input voltage            | DIN, $\overline{EN}$ , $\overline{PWRDOWN}$ |                         |     | 0   |     | 5.5  | V  |
| V <sub>I</sub>  | Receiver input voltage                      |                                             |                         | –25 |     | 25  |      | V  |
| T <sub>A</sub>  | Operating free-air temperature              | SN65C3222                                   |                         | –40 |     | 85  |      | °C |
|                 |                                             | SN75C3222                                   |                         | 0   |     | 70  |      |    |

NOTE 4: Test conditions are C1–C4 = 0.1  $\mu$ F at  $V_{CC} = 3.3$  V  $\pm$  0.3 V; C1 = 0.047  $\mu$ F, C2–C4 = 0.33  $\mu$ F at  $V_{CC} = 5$  V  $\pm$  0.5 V.

### electrical characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see Note 4 and Figure 5)

| PARAMETER |                                                                  | TEST CONDITIONS                           | MIN | TYP <sup>‡</sup> | MAX     | UNIT    |
|-----------|------------------------------------------------------------------|-------------------------------------------|-----|------------------|---------|---------|
| $I_I$     | Input leakage current ( $\overline{EN}$ , $\overline{PWRDOWN}$ ) |                                           |     | $\pm 0.01$       | $\pm 1$ | $\mu$ A |
| $I_{CC}$  | Supply current                                                   | No load, $\overline{PWRDOWN}$ at $V_{CC}$ |     | 0.3              | 1       | mA      |
|           | Supply current (powered off)                                     | No load, $\overline{PWRDOWN}$ at GND      |     | 1                | 10      | $\mu$ A |

<sup>‡</sup> All typical values are at  $V_{CC} = 3.3$  V or  $V_{CC} = 5$  V, and  $T_A = 25^\circ\text{C}$ .

NOTE 4: Test conditions are C1–C4 = 0.1  $\mu$ F at  $V_{CC} = 3.3$  V  $\pm$  0.3 V; C1 = 0.047  $\mu$ F, C2–C4 = 0.33  $\mu$ F at  $V_{CC} = 5$  V  $\pm$  0.5 V.



# SN65C3222, SN75C3222

## 3-V TO 5.5-V MULTICHANNEL RS-232 COMPATIBLE LINE DRIVER/RECEIVER

SLLS534B – MAY 2002 – REVISED OCTOBER 2004

### DRIVER SECTION

**electrical characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see Note 4 and Figure 5)**

| PARAMETER                                                 | TEST CONDITIONS                                             | MIN                                                      | TYP <sup>†</sup> | MAX | UNIT |
|-----------------------------------------------------------|-------------------------------------------------------------|----------------------------------------------------------|------------------|-----|------|
| V <sub>OH</sub> High-level output voltage                 | DOUT at R <sub>L</sub> = 3 kΩ to GND, DIN = GND             | 5                                                        | 5.4              |     | V    |
| V <sub>OL</sub> Low-level output voltage                  | DOUT at R <sub>L</sub> = 3 kΩ to GND, DIN = V <sub>CC</sub> | –5                                                       | –5.4             |     | V    |
| I <sub>IH</sub> High-level input current                  | V <sub>I</sub> = V <sub>CC</sub>                            |                                                          | ±0.01            | ±1  | μA   |
| I <sub>IL</sub> Low-level input current                   | V <sub>I</sub> at GND                                       |                                                          | ±0.01            | ±1  | μA   |
| I <sub>OS</sub> Short-circuit output current <sup>‡</sup> | V <sub>CC</sub> = 3.6 V, V <sub>O</sub> = 0 V               |                                                          | ±35              | ±60 | mA   |
|                                                           | V <sub>CC</sub> = 5.5 V, V <sub>O</sub> = 0 V               |                                                          | ±35              | ±90 |      |
| r <sub>o</sub> Output resistance                          | V <sub>CC</sub> , V+, and V– = 0 V, V <sub>O</sub> = ±2 V   | 300                                                      | 10M              |     | Ω    |
| I <sub>off</sub> Output leakage current                   | PWRDOWN = GND                                               | V <sub>O</sub> = ±12 V, V <sub>CC</sub> = 3 V to 3.6 V   |                  | ±25 | μA   |
|                                                           |                                                             | V <sub>O</sub> = ±10 V, V <sub>CC</sub> = 4.5 V to 5.5 V |                  | ±25 |      |

<sup>†</sup> All typical values are at V<sub>CC</sub> = 3.3 V or V<sub>CC</sub> = 5 V, and T<sub>A</sub> = 25°C.

<sup>‡</sup> Short-circuit durations should be controlled to prevent exceeding the device absolute power-dissipation ratings, and not more than one output should be shorted at a time.

NOTE 4: Test conditions are C1–C4 = 0.1 μF at V<sub>CC</sub> = 3.3 V ± 0.3 V; C1 = 0.047 μF, C2–C4 = 0.33 μF at V<sub>CC</sub> = 5 V ± 0.5 V.

**switching characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see Note 4 and Figure 4)**

| PARAMETER                           |                                                   | TEST CONDITIONS                                                                                 |                                  | MIN  | TYP <sup>†</sup> | MAX    | UNIT |
|-------------------------------------|---------------------------------------------------|-------------------------------------------------------------------------------------------------|----------------------------------|------|------------------|--------|------|
| Maximum data rate<br>(see Figure 1) | R <sub>L</sub> = 3 kΩ,<br>One DOUT switching      | C <sub>L</sub> = 1000 pF                                                                        |                                  | 250  |                  | kbit/s |      |
|                                     |                                                   | C <sub>L</sub> = 250 pF,                                                                        | V <sub>CC</sub> = 3 V to 4.5 V   | 1000 |                  |        |      |
|                                     |                                                   | C <sub>L</sub> = 1000 pF,                                                                       | V <sub>CC</sub> = 4.5 V to 5.5 V | 1000 |                  |        |      |
| t <sub>sk(p)</sub>                  | Pulse skew <sup>§</sup>                           | C <sub>L</sub> = 150 pF to 2500 pF<br>R <sub>L</sub> = 3 kΩ to 7 kΩ,<br>See Figure 2            |                                  | 300  |                  | ns     |      |
| SR(tr)                              | Slew rate,<br>transition region<br>(see Figure 1) | R <sub>L</sub> = 3 kΩ to 7 kΩ,<br>V <sub>CC</sub> = 3.3 V<br>C <sub>L</sub> = 150 pF to 1000 pF |                                  | 18   |                  | 150    | V/μs |

<sup>†</sup> All typical values are at V<sub>CC</sub> = 3.3 V or V<sub>CC</sub> = 5 V, and T<sub>A</sub> = 25°C.

<sup>§</sup> Pulse skew is defined as |t<sub>pLH</sub> – t<sub>pHL</sub>| of each channel of the same device.

NOTE 4: Test conditions are C1–C4 = 0.1 μF at V<sub>CC</sub> = 3.3 V ± 0.3 V; C1 = 0.047 μF, C2–C4 = 0.33 μF at V<sub>CC</sub> = 5 V ± 0.5 V.



# SN65C3222, SN75C3222

## 3-V TO 5.5-V MULTICHANNEL RS-232 COMPATIBLE LINE DRIVER/RECEIVER

SLLS534B – MAY 2002 – REVISED OCTOBER 2004

### RECEIVER SECTION

**electrical characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see Note 4 and Figure 5)**

| PARAMETER                                                                | TEST CONDITIONS                 | MIN                     | TYP <sup>†</sup>        | MAX | UNIT |
|--------------------------------------------------------------------------|---------------------------------|-------------------------|-------------------------|-----|------|
| V <sub>OH</sub> High-level output voltage                                | I <sub>OH</sub> = -1 mA         | V <sub>CC</sub> - 0.6 V | V <sub>CC</sub> - 0.1 V |     | V    |
| V <sub>OL</sub> Low-level output voltage                                 | I <sub>OL</sub> = 1.6 mA        |                         |                         | 0.4 | V    |
| V <sub>IT+</sub> Positive-going input threshold voltage                  | V <sub>CC</sub> = 3.3 V         |                         | 1.5                     | 2.4 | V    |
|                                                                          | V <sub>CC</sub> = 5 V           |                         | 1.8                     | 2.4 |      |
| V <sub>IT-</sub> Negative-going input threshold voltage                  | V <sub>CC</sub> = 3.3 V         | 0.6                     | 1.2                     |     | V    |
|                                                                          | V <sub>CC</sub> = 5 V           | 0.8                     | 1.5                     |     |      |
| V <sub>hys</sub> Input hysteresis (V <sub>IT+</sub> - V <sub>IT-</sub> ) |                                 |                         | 0.3                     |     | V    |
| I <sub>off</sub> Output leakage current                                  | $\overline{\text{EN}} = V_{CC}$ |                         | ±0.05                   | ±10 | μA   |
| r <sub>i</sub> Input resistance                                          | V <sub>I</sub> = ±3 V to ±25 V  | 3                       | 5                       | 7   | kΩ   |

<sup>†</sup> All typical values are at V<sub>CC</sub> = 3.3 V or V<sub>CC</sub> = 5 V, and T<sub>A</sub> = 25°C.

NOTE 4: Test conditions are C1–C4 = 0.1 μF at V<sub>CC</sub> = 3.3 V ± 0.3 V; C1 = 0.047 μF, C2–C4 = 0.33 μF at V<sub>CC</sub> = 5 V ± 0.5 V.

**switching characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see Note 4)**

| PARAMETER                                                          | TEST CONDITIONS                                              | MIN | TYP <sup>†</sup> | MAX | UNIT |
|--------------------------------------------------------------------|--------------------------------------------------------------|-----|------------------|-----|------|
| t <sub>PLH</sub> Propagation delay time, low- to high-level output | C <sub>L</sub> = 150 pF, See Figure 3                        |     | 300              |     | ns   |
| t <sub>PHL</sub> Propagation delay time, high- to low-level output | C <sub>L</sub> = 150 pF, See Figure 3                        |     | 300              |     | ns   |
| t <sub>en</sub> Output enable time                                 | C <sub>L</sub> = 150 pF, R <sub>L</sub> = 3 kΩ, See Figure 4 |     | 200              |     | ns   |
| t <sub>dis</sub> Output disable time                               | C <sub>L</sub> = 150 pF, R <sub>L</sub> = 3 kΩ, See Figure 4 |     | 200              |     | ns   |
| t <sub>sk(p)</sub> Pulse skew <sup>‡</sup>                         | See Figure 3                                                 |     | 300              |     | ns   |

<sup>†</sup> All typical values are at V<sub>CC</sub> = 3.3 V or V<sub>CC</sub> = 5 V, and T<sub>A</sub> = 25°C.

<sup>‡</sup> Pulse skew is defined as |t<sub>PLH</sub> - t<sub>PHL</sub>| of each channel of the same device.

NOTE 4: Test conditions are C1–C4 = 0.1 μF at V<sub>CC</sub> = 3.3 V ± 0.3 V; C1 = 0.047 μF, C2–C4 = 0.33 μF at V<sub>CC</sub> = 5 V ± 0.5 V.




# SN65C3222, SN75C3222

## 3-V TO 5.5-V MULTICHANNEL RS-232 COMPATIBLE LINE DRIVER/RECEIVER

SLLS534B – MAY 2002 – REVISED OCTOBER 2004


### PARAMETER MEASUREMENT INFORMATION



NOTES: A.  $C_L$  includes probe and jig capacitance.

B. The pulse generator has the following characteristics: PRR = 250 kbit/s,  $Z_O = 50\ \Omega$ , 50% duty cycle,  $t_r \leq 10\text{ ns}$ ,  $t_f \leq 10\text{ ns}$ .


**Figure 1. Driver Slew Rate**



NOTES: A.  $C_L$  includes probe and jig capacitance.

B. The pulse generator has the following characteristics: PRR = 250 kbit/s,  $Z_O = 50\ \Omega$ , 50% duty cycle,  $t_r \leq 10\text{ ns}$ ,  $t_f \leq 10\text{ ns}$ .

**Figure 2. Driver Pulse Skew**



NOTES: A.  $C_L$  includes probe and jig capacitance.

B. The pulse generator has the following characteristics:  $Z_O = 50\ \Omega$ , 50% duty cycle,  $t_r \leq 10\text{ ns}$ ,  $t_f \leq 10\text{ ns}$ .


**Figure 3. Receiver Propagation-Delay Times**

# SN65C3222, SN75C3222


## 3-V TO 5.5-V MULTICHANNEL RS-232 COMPATIBLE LINE DRIVER/RECEIVER

SLLS534B – MAY 2002 – REVISED OCTOBER 2004

### PARAMETER MEASUREMENT INFORMATION



TEST CIRCUIT



VOLTAGE WAVEFORMS

NOTES: A.  $C_L$  includes probe and jig capacitance.


B. The pulse generator has the following characteristics:  $Z_O = 50 \Omega$ , 50% duty cycle,  $t_r \leq 10$  ns,  $t_f \leq 10$  ns.

Figure 4. Receiver Enable and Disable Times

SN65C3222, SN75C3222  
3-V TO 5.5-V MULTICHANNEL RS-232 COMPATIBLE LINE DRIVER/RECEIVER

SLLS534B – MAY 2002 – REVISED OCTOBER 2004

APPLICATION INFORMATION



† C3 can be connected to V<sub>CC</sub> or GND.  
NOTES: A. Resistor values shown are nominal.  
B. NC – No internal connection

| V <sub>CC</sub> vs CAPACITOR VALUES |          |                |
|-------------------------------------|----------|----------------|
| V <sub>CC</sub>                     | C1       | C2, C3, and C4 |
| 3.3 V ± 0.3 V                       | 0.1 μF   | 0.1 μF         |
| 5 V ± 0.5 V                         | 0.047 μF | 0.33 μF        |
| 3 V to 5.5 V                        | 0.1 μF   | 0.47 μF        |

Figure 5. Typical Operating Circuit and Capacitor Values



**PACKAGING INFORMATION**

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)            | Lead/Ball Finish<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5) | Samples                 |
|------------------|---------------|--------------|--------------------|------|----------------|----------------------------|-------------------------|----------------------|--------------|-------------------------|-------------------------|
| SN65C3222DBR     | ACTIVE        | SSOP         | DB                 | 20   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -40 to 85    | CB3222                  | <a href="#">Samples</a> |
| SN65C3222DBRE4   | ACTIVE        | SSOP         | DB                 | 20   |                | TBD                        | Call TI                 | Call TI              | -40 to 85    |                         | <a href="#">Samples</a> |
| SN65C3222DBRG4   | ACTIVE        | SSOP         | DB                 | 20   |                | TBD                        | Call TI                 | Call TI              | -40 to 85    |                         | <a href="#">Samples</a> |
| SN65C3222DWR     | ACTIVE        | SOIC         | DW                 | 20   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -40 to 85    | 65C3222                 | <a href="#">Samples</a> |
| SN65C3222DWRE4   | ACTIVE        | SOIC         | DW                 | 20   |                | TBD                        | Call TI                 | Call TI              | -40 to 85    |                         | <a href="#">Samples</a> |
| SN65C3222DWRG4   | ACTIVE        | SOIC         | DW                 | 20   |                | TBD                        | Call TI                 | Call TI              | -40 to 85    |                         | <a href="#">Samples</a> |
| SN65C3222PW      | ACTIVE        | TSSOP        | PW                 | 20   | 70             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -40 to 85    | CB3222                  | <a href="#">Samples</a> |
| SN65C3222PWE4    | ACTIVE        | TSSOP        | PW                 | 20   |                | TBD                        | Call TI                 | Call TI              | -40 to 85    |                         | <a href="#">Samples</a> |
| SN65C3222PWG4    | ACTIVE        | TSSOP        | PW                 | 20   |                | TBD                        | Call TI                 | Call TI              | -40 to 85    |                         | <a href="#">Samples</a> |
| SN65C3222PWR     | ACTIVE        | TSSOP        | PW                 | 20   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -40 to 85    | CB3222                  | <a href="#">Samples</a> |
| SN65C3222PWRE4   | ACTIVE        | TSSOP        | PW                 | 20   |                | TBD                        | Call TI                 | Call TI              | -40 to 85    |                         | <a href="#">Samples</a> |
| SN65C3222PWRG4   | ACTIVE        | TSSOP        | PW                 | 20   |                | TBD                        | Call TI                 | Call TI              | -40 to 85    |                         | <a href="#">Samples</a> |
| SN75C3222DW      | ACTIVE        | SOIC         | DW                 | 20   | 25             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 70      | 75C3222                 | <a href="#">Samples</a> |
| SN75C3222DWG4    | ACTIVE        | SOIC         | DW                 | 20   | 25             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 70      | 75C3222                 | <a href="#">Samples</a> |
| SN75C3222DWR     | ACTIVE        | SOIC         | DW                 | 20   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 70      | 75C3222                 | <a href="#">Samples</a> |
| SN75C3222PW      | ACTIVE        | TSSOP        | PW                 | 20   | 70             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 70      | CA3222                  | <a href="#">Samples</a> |
| SN75C3222PWR     | ACTIVE        | TSSOP        | PW                 | 20   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 70      | CA3222                  | <a href="#">Samples</a> |
| SN75C3222PWRE4   | ACTIVE        | TSSOP        | PW                 | 20   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | 0 to 70      | CA3222                  | <a href="#">Samples</a> |

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.


<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**TAPE AND REEL INFORMATION**


\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN65C3222DBR | SSOP         | DB              | 20   | 2000 | 330.0              | 16.4               | 8.2     | 7.5     | 2.5     | 12.0    | 16.0   | Q1            |
| SN65C3222DWR | SOIC         | DW              | 20   | 2000 | 330.0              | 24.4               | 10.8    | 13.3    | 2.7     | 12.0    | 24.0   | Q1            |
| SN65C3222PWR | TSSOP        | PW              | 20   | 2000 | 330.0              | 16.4               | 6.95    | 7.1     | 1.6     | 8.0     | 16.0   | Q1            |
| SN75C3222DWR | SOIC         | DW              | 20   | 2000 | 330.0              | 24.4               | 10.8    | 13.3    | 2.7     | 12.0    | 24.0   | Q1            |
| SN75C3222PWR | TSSOP        | PW              | 20   | 2000 | 330.0              | 16.4               | 6.95    | 7.1     | 1.6     | 8.0     | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS




\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN65C3222DBR | SSOP         | DB              | 20   | 2000 | 367.0       | 367.0      | 38.0        |
| SN65C3222DWR | SOIC         | DW              | 20   | 2000 | 367.0       | 367.0      | 45.0        |
| SN65C3222PWR | TSSOP        | PW              | 20   | 2000 | 367.0       | 367.0      | 38.0        |
| SN75C3222DWR | SOIC         | DW              | 20   | 2000 | 367.0       | 367.0      | 45.0        |
| SN75C3222PWR | TSSOP        | PW              | 20   | 2000 | 367.0       | 367.0      | 38.0        |

DW (R-PDSO-G20)


PLASTIC SMALL OUTLINE



- NOTES:
- All linear dimensions are in inches (millimeters). Dimensioning and tolerancing per ASME Y14.5M-1994.
  - This drawing is subject to change without notice.
  - Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
  - Falls within JEDEC MS-013 variation AC.

DW (R-PDSO-G20)


PLASTIC SMALL OUTLINE



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Refer to IPC7351 for alternate board design.
  - D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525
  - E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.

PW (R-PDSO-G20)

PLASTIC SMALL OUTLINE



4040064-5/G 02/11



- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
  - B. This drawing is subject to change without notice.
  - C. Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0,15 each side.
  - D. Body width does not include interlead flash. Interlead flash shall not exceed 0,25 each side.
  - E. Falls within JEDEC MO-153

PW (R-PDSO-G20)

PLASTIC SMALL OUTLINE


Example Board Layout

Based on a stencil thickness  
of .127mm (.005inch).



Example  
Non Soldermask Defined Pad

Example  
Solder Mask Opening  
(See Note F)



4211284-5/F 12/12


- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Publication IPC-7351 is recommended for alternate design.
  - D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
  - E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.



## DB (R-PDSO-G\*\*)

## PLASTIC SMALL-OUTLINE

28 PINS SHOWN



- NOTES: A. All linear dimensions are in millimeters.  
 B. This drawing is subject to change without notice.  
 C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.  
 D. Falls within JEDEC MO-150

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

### Products

|                              |                                                                                      |
|------------------------------|--------------------------------------------------------------------------------------|
| Audio                        | <a href="http://www.ti.com/audio">www.ti.com/audio</a>                               |
| Amplifiers                   | <a href="http://amplifier.ti.com">amplifier.ti.com</a>                               |
| Data Converters              | <a href="http://dataconverter.ti.com">dataconverter.ti.com</a>                       |
| DLP® Products                | <a href="http://www.dlp.com">www.dlp.com</a>                                         |
| DSP                          | <a href="http://dsp.ti.com">dsp.ti.com</a>                                           |
| Clocks and Timers            | <a href="http://www.ti.com/clocks">www.ti.com/clocks</a>                             |
| Interface                    | <a href="http://interface.ti.com">interface.ti.com</a>                               |
| Logic                        | <a href="http://logic.ti.com">logic.ti.com</a>                                       |
| Power Mgmt                   | <a href="http://power.ti.com">power.ti.com</a>                                       |
| Microcontrollers             | <a href="http://microcontroller.ti.com">microcontroller.ti.com</a>                   |
| RFID                         | <a href="http://www.ti-rfid.com">www.ti-rfid.com</a>                                 |
| OMAP Applications Processors | <a href="http://www.ti.com/omap">www.ti.com/omap</a>                                 |
| Wireless Connectivity        | <a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a> |

### Applications

|                               |                                                                                          |
|-------------------------------|------------------------------------------------------------------------------------------|
| Automotive and Transportation | <a href="http://www.ti.com/automotive">www.ti.com/automotive</a>                         |
| Communications and Telecom    | <a href="http://www.ti.com/communications">www.ti.com/communications</a>                 |
| Computers and Peripherals     | <a href="http://www.ti.com/computers">www.ti.com/computers</a>                           |
| Consumer Electronics          | <a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>                   |
| Energy and Lighting           | <a href="http://www.ti.com/energy">www.ti.com/energy</a>                                 |
| Industrial                    | <a href="http://www.ti.com/industrial">www.ti.com/industrial</a>                         |
| Medical                       | <a href="http://www.ti.com/medical">www.ti.com/medical</a>                               |
| Security                      | <a href="http://www.ti.com/security">www.ti.com/security</a>                             |
| Space, Avionics and Defense   | <a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a> |
| Video and Imaging             | <a href="http://www.ti.com/video">www.ti.com/video</a>                                   |

### TI E2E Community

[e2e.ti.com](http://e2e.ti.com)