

AO5800



Dual N-Channel Enhancement Mode Field Effect Transistor

General Description

The AO5800 uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge, and operation with gate voltages as low as 4.5V, in the small SC89-6L footprint. It can be used for a wide variety of applications, including load switching, low current inverters and low current DC-DC converters. It is ESD protected. *Standard Product AO5800 is Pb-free (meets ROHS & Sony 259 specifications).*

Features

$V_{DS} (V) = 60V$
 $I_D = 0.4A (V_{GS} = 10V)$
 $R_{DS(ON)} < 1.6\Omega (V_{GS} = 10V)$
 $R_{DS(ON)} < 1.9\Omega (V_{GS} = 4.5V)$



Absolute Maximum Ratings $T_A=25^\circ C$ unless otherwise noted

Parameter	Symbol	Maximum	Units
Drain-Source Voltage	V_{DS}	60	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current ^{A, F}	$T_A=25^\circ C$	0.4	A
	$T_A=70^\circ C$	0.3	
Pulsed Drain Current ^B	I_{DM}	1.6	
Power Dissipation ^A	$T_A=25^\circ C$	0.4	W
	$T_A=70^\circ C$	0.24	
Junction and Storage Temperature Range	T_J, T_{STG}	-55 to 150	$^\circ C$

Thermal Characteristics

Parameter	Symbol	Typ	Max	Units
Maximum Junction-to-Ambient ^A	$R_{\theta JA}$	275	330	$^\circ C/W$
Maximum Junction-to-Ambient ^A		360	450	$^\circ C/W$
Maximum Junction-to-Lead ^C	$R_{\theta JL}$	300	350	$^\circ C/W$

Electrical Characteristics (T_J=25°C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
STATIC PARAMETERS						
BV _{DSS}	Drain-Source Breakdown Voltage	I _D =250μA, V _{GS} =0V	60			V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =48V, V _{GS} =0V T _J =55°C			1 5	μA
I _{GSS}	Gate-Body leakage current	V _{DS} =0V, V _{GS} =±10V V _{DS} =0V, V _{GS} =±4.5V			±1 ±100	μA nA
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} I _D =250μA	1	1.6	2.5	V
I _{D(ON)}	On state drain current	V _{GS} =10V, V _{DS} =5V	1.6			A
R _{DS(ON)}	Static Drain-Source On-Resistance	V _{GS} =10V, I _D =0.4A T _J =125°C V _{GS} =4.5V, I _D =0.3A		1.3 2.45 1.5	1.6 3 1.9	Ω
g _{FS}	Forward Transconductance	V _{DS} =5V, I _D =0.4A		0.5		S
V _{SD}	Diode Forward Voltage	I _S =0.1A,V _{GS} =0V		0.8	1	V
I _S	Maximum Body-Diode Continuous Current				0.4	A
DYNAMIC PARAMETERS						
C _{iss}	Input Capacitance	V _{GS} =0V, V _{DS} =30V, f=1MHz		41	50	pF
C _{oss}	Output Capacitance			9		pF
C _{rss}	Reverse Transfer Capacitance			6		pF
SWITCHING PARAMETERS						
t _{D(on)}	Turn-On DelayTime	V _{GS} =10V, V _{DS} =30V, R _L =75Ω, R _{GEN} =3Ω		39.2		ns
t _r	Turn-On Rise Time			35.7		ns
t _{D(off)}	Turn-Off DelayTime			261		ns
t _f	Turn-Off Fall Time			79		ns
t _{rr}	Body Diode Reverse Recovery Time	I _F =0.4A, dI/dt=100A/μs, V _{GS} =-9V		11.3	14	ns
Q _{rr}	Body Diode Reverse Recovery Charge	I _F =0.4A, dI/dt=100A/μs, V _{GS} =-9V		7.5		nC

A: The value of R_{θJA} is measured with the device mounted on 1in² FR-4 board with 2oz. Copper, in a still air environment with T_A=25°C. The value in any given application depends on the user's specific board design.

B: Repetitive rating, pulse width limited by junction temperature.

C: The R_{θJA} is the sum of the thermal impedance from junction to lead R_{θJL} and lead to ambient.

D: The static characteristics in Figures 1 to 6 are obtained using <300 μs pulses, duty cycle 0.5% max.

E: These tests are performed with the device mounted on 1 in² FR-4 board with 2oz. Copper, in a still air environment with T_A=25°C. The SOA curve provides a single pulse rating.

F: The current rating is based on the t ≤ 10s thermal resistance rating.

Rev 1: January 2007

THIS PRODUCT HAS BEEN DESIGNED AND QUALIFIED FOR THE CONSUMER MARKET. APPLICATIONS OR USES AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS ARE NOT AUTHORIZED. AOS DOES NOT ASSUME ANY LIABILITY ARISING OUT OF SUCH APPLICATIONS OR USES OF ITS PRODUCTS. AOS RESERVES THE RIGHT TO IMPROVE PRODUCT DESIGN, FUNCTIONS AND RELIABILITY WITHOUT NOTICE.

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




Figure 1: On-Region Characteristics




Figure 2: Transfer Characteristics




Figure 3: On-Resistance vs. Drain Current and Gate Voltage




Figure 4: On-Resistance vs. Junction Temperature




Figure 5: On-Resistance vs. Gate-Source Voltage




Figure 6: Body-Diode Characteristics

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




Figure 7: Gate-Charge Characteristics




Figure 8: Capacitance Characteristics




Figure 9: Maximum Forward Biased Safe Operating Area (Note E)




Figure 10: Single Pulse Power Rating Junction-to-Ambient (Note E)




Figure 11: Normalized Maximum Transient Thermal Impedance