

## Product Datasheet

## HBL2621




Black and white nylon.

HBL2621

## Product Specifications

<b>Device Type</b>	Plug
<b>Device Style</b>	Twist-Lock
<b>Amperage</b>	30A
<b>Volts</b>	250V
<b>Poles and Wires</b>	2 Pole, 3 Wire Grounding
<b>Design Type for Plugs and Connectors</b>	Insulgrip
<b>Body Style</b>	Straight
<b>Configuration Type</b>	L6-30P
<b>Color</b>	 Black
<b>Horsepower</b>	2
<b>Cord Dia.</b>	.360"-.930" (9-24)
<b>Blade Holder Material</b>	Natural White Nylon
<b>Terminal Retainer Material</b>	Clear polycarbonate
<b>Housing Material</b>	Black nylon
<b>Cord Clamp Material</b>	Natural (white) nylon
<b>Blade Material</b>	Brass
<b>Terminal Clamp Material</b>	.08" (2 )steel-nickel plated
<b>Terminal Screw Material</b>	#10-32 Brass (white finish on neutral screw when used) Multi-drive
<b>Ground Screw Material</b>	#10-32 Brass (green finish) Multi-drive
<b>Cord Clamp Screw Material</b>	Steel, zinc plated Multi-drive
<b>Body Holding Screw Material</b>	Steel, zinc plated Multi-drive
<b>Ratings</b>	Molded into face
<b>Catalog No.</b>	Permanently ink marked on body.
<b>Dielectric Voltage Withstand</b>	2,000V minimum.
<b>Current Interrupting</b>	Certified for current interrupting at full rated current.
<b>Temperature Rise</b>	Max 30 C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
<b>Cord Accommodation</b>	Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49.
<b>Terminal Accommodation</b>	30A #10 AWG

<b>Terminal Identification</b>	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
<b>Flammability</b>	HB or better per UL 94 or CSA 22.2 No. 0.6
<b>Operating Temperatures</b>	Maximum Continuous 75 C Minimum -40 C (w/o impact)
<b>Moisture Resistance</b>	IP20
<b>Listings</b>	UL/CSA



Hubbell Incorporated (Delaware)  
185 Plains Road  
Milford, CT 06460-2420  
Ph: (203) 882-4800  
Fax: (800) 255-1031

