







LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		P2		REVISED PER ECO-12-008643	08AUG12	KH	AS



12	OBSELETE	7-10, 27-34, 53-56	121,16 [4,770]	114,30 [4,500]	30	31	11 8-650728-1
		7-10, 25-32, 47-50	109,73 [4,520]	102,87 [4,060]	27	28	11 7-650728-8
		7-10, 29-32	75,44 [2,970]	68,58 [2,700]	18	19	11 6-650728-9
		7-10, 15-18	48,77 [1,920]	41,91 [1,650]	11	12	11 6-650728-2
	OBSELETE	7-10, 39-46, 75-78	163,06 [6,120]	156,21 [6,150]	41	42	4-650728-2
12	OBSELETE	7-10, 27-34, 53-56	121,16 [4,770]	114,30 [4,500]	30	31	3 650728-1
		7-10, 25-32, 47-50	109,73 [4,520]	102,87 [4,060]	27	28	2-650728-8
		7-10, 29-32	75,44 [2,970]	68,58 [2,700]	18	19	1-650728-9
	OBSELETE	7-10, 27-30	72,63 [2,820]	64,77 [2,550]	17	18	1-650728-8
	OBSELETE	7-10, 17-20	52,58 [2,070]	45,72 [1,800]	12	13	1-650728-3
		7-10, 15-18	48,77 [1,920]	41,91 [1,650]	11	12	1-650728-2
	BOARD RETENTION LOCATION		B	A	X	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11JULY91 R. SHIREY/UTA CHK J. DIORAZIO 080C192 APP'D J. DIORAZIO 080C192		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± ± -		NAME CONNECTOR ASSEMBLY, STANDARD EDGE II, 3.81 [.150] q SELECT BOARD RETENTION	
		PRODUCT SPEC 108-9039 APPLICATION SPEC -		SIZE CAGE CODE DRAWING NO A1 00779 C-650728	
MATERIAL HOUSING:  CONTACT: 		FINISH CONTACT:   		RESTRICTED TO -	
		WEIGHT -		SCALE 4:1 SHEET 1 OF 1 REV P2	
		CUSTOMER DRAWING			