




83.82	92.82	98.02	87.64	23	2-1986724-3
80.01	89.01	94.21	83.83	22	2-1986724-2
76.20	85.20	90.40	80.02	21	2-1986724-1
72.39	81.39	86.59	76.21	20	2-1986724-0
68.58	77.58	82.78	72.40	19	1-1986724-9
64.77	73.77	78.97	68.59	18	1-1986724-8
60.96	69.96	75.16	64.78	17	1-1986724-7
57.15	66.15	71.35	60.97	16	1-1986724-6
53.34	62.34	67.54	57.16	15	1-1986724-5
49.53	58.53	63.73	53.35	14	1-1986724-4
45.72	54.72	59.92	49.54	13	1-1986724-3
41.91	50.91	56.11	45.73	12	1-1986724-2
38.10	47.10	52.30	41.92	11	1-1986724-1
34.29	43.29	48.49	38.11	10	1-1986724-0
30.48	39.48	44.68	34.30	9	1986724-9
26.67	35.67	40.87	30.49	8	1986724-8
22.86	31.86	37.06	26.68	7	1986724-7
19.05	28.05	33.25	22.87	6	1986724-6
15.24	24.24	29.44	19.06	5	1986724-5
11.43	20.43	25.63	15.25	4	1986724-4
7.62	16.62	21.82	11.44	3	1986724-3
3.81	12.81	18.01	7.63	2	1986724-2
DIM X	DIM C	DIM A	DIM B	POLE	PART NUMBER



SECTION A - A



MECHANICAL
 INSERTION FORCE PER POLE- 3 NEWTON MAX
 WITHDRAWAL FORCE PER POLE- 1.5 NEWTON MIN
 STRIPPING LENGTH- 10.5 TO 11.5 MM
 OPERATING TEMPERATURE-- 40°C TO +110°C

ELECTRICAL
WIRE SIZE= 30 TO 14 AWG SOLID OR STRANDED
VOLTAGE RATING- 300 VOLTS
CURRENT RATING- 11 AMP STRANDED; 9AMP SOLID
CONTACT RESISTANCE-15 MILLOHM MAX
INSULATION RESISTANCE- 10^9 OHMS MIN (500V DC)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 13JAN2012 KIRAN HOLAI CHK 13JAN2012 MIKE SARVER APVD 13JAN2012 MIKE SARVER		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME STRAIGHT SPRING TYPE PLUG CONNECTOR, RIGHT SIDE, LOCKING W/FLANGES 02 - 23 POLES, PITCH 3.81mm	
		0 PLC ±- 1 PLC ±0.40 2 PLC ±0.20 3 PLC ±- 4 PLC ±- ANGLES ±1°			
MATERIAL -		FINISH -		PRODUCT SPEC -	
				APPLICATION SPEC -	
		WEIGHT -		SIZE A3	
				CAGE CODE 00779	
				DRAWING NO C-1986724	
				RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 2:1	
				SHEET 1 OF 1	
				REV A	