


Part Number: AS32 20010



Electrical Specifications:

Resistance @ 25°C	20.0 $\Omega \pm 25\%$
Max Steady State Current Up to 65°C	10.0 A
Max recommended energy rating (Joules)	250.00 J
Actual failure point of instantaneous energy (Joules)	500.00 J
Resistance @ 100% of Max Current	0.056 Ω
Body Temperature @ 100% Current rating	192°C
Dissipation Constant	58mW/°C
Cool down time: 50% of Initial R	36 sec
Cool down time: 100% of Initial Resistance	67 sec
Material Type	I
ROHS Compliant	Yes
MSL (moisture sensitivity level)	# 2

Mechanical Specifications:

D	29 ± 2.0 mm
T	9.0 ± 1.0 mm
S	17.1 ± 2.0 mm
Straight Leads Coating run down	5.0 ± 3.0 mm
L	22.0 ± 2.0 mm
A (Lead Width)	2.2 ± 0.2 mm
B	6.4 ± 1.0 mm
C (Lead Thickness)	0.9 ± 0.2 mm

Revision Date: 1/26/11

Ametherm, Inc. 3111 N. Deer Run Road #4 Carson City, NV 89701
Telephone: (800) 808-2434 (775) 884-2434 Fax: (775) 884-0670
www.ametherm.com