




LOC		DIST		REVISIONS			
F	LTR	DESCRIPTION		DATE	DWN	APVD	
B		REV: EC 0B40-0259-01		23OCT01	TLP	CD	
C		ECO-06-016706		13JUL2006	JM	BM	

- 1 MATERIAL: JACK HOUSING - POLYPHENYLENE OXIDE, 94V-0 RATED.
TERMINAL BLOCK - POLYPHENYLENE OXIDE, 94V-0 RATED.
STUFFER CAP - POLYCARBONATE, CLEAR, 94V-0 RATED.
DOOR - POLYCARBONATE, CLEAR, 94V-0 RATED.
JACK CONTACTS - PHOSPHOROUS BRONZE, PLATED WITH
1.27um [0.00050] MINIMUM THICK GOLD IN LOCALIZED
AREA AND 3.81um [0.00150] MINIMUM THICK MATTE TIN IN
SOLDER AREA OVER 1.27um [0.00050] MINIMUM THICK
NICKEL UNDERPLATE.
- 2 TOOLLESS WILL TERMINATE 22-24 AWG SOLID CONDUCTORS AND 24 AWG
STRANDED CONDUCTORS, 1.14 [0.045] MAXIMUM INSULATION DIAMETER.
- 3 CAVITY CONFORMS TO FCC RULES AND REGULATIONS)
PART 68 SUBPART F REQUIREMENTS.
- 4 MOUNTING PANEL THICKNESS 1.473 - 1.600 [0.058 - .063].
- 5 THESE TWO SUGGESTED CUTOUT OPENINGS ARE USED
IN TANDEM WITH DUAL FRONT AND BACK CUTOUTS.
- 6 ONE MODULAR JACK ASSEMBLY PER POLYBAG.
- 7 ASSEMBLY SHIPPED WITH STUFFER CAP NOT LATCHED
AT REAR OF HOUSING ASSEMBLY AS SHOWN.
- 8 DIMENSION SHOWN WITH STUFFER CAP IN LATCHED POSITION.



OPEN POSITION



DETAIL A
SCALE 10:1


PART NUMBER

COLOR CODE	IDC TERMINAL	MODULAR JACK	
WHITE/BLUE			5
BLUE			4
WHITE/ORANGE			3
ORANGE			6
WHITE/GREEN			1
GREEN			2
WHITE/BROWN			7
BROWN			8


ELECTRICAL SCHEMATIC
T568A

COLOR CODE	IDC TERMINAL	MODULAR JACK	
WHITE/BLUE			5
BLUE			4
WHITE/ORANGE			1
ORANGE			2
WHITE/GREEN			3
GREEN			6
WHITE/BROWN			7
BROWN			8

ELECTRICAL SCHEMATIC
T568B



SINGLE PANEL CUTOUT



SUGGESTED FLUSH MOUNT
PANEL APPLICATION CUTOUT

6	ELECTRIC IVORY	1-1339189-1
	VIOLET	1-1339189-0
	GREEN	1339189-9
	YELLOW	1339189-8
	RED	1339189-7
	BLUE	1339189-6
	ORANGE	1339189-5
	NEMA GRAY	1339189-4
	WHITE	1339189-3
	BLACK	1339189-2
	LIGHT ALMOND	1339189-1
PACKAGE HOUSING COLOR		PART NUMBER

THIS DRAWING IS UNPUBLISHED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED. IT IS TO BE RETURNED TO TYCO ELECTRONICS CORPORATION WHEN NO LONGER REQUIRED FOR THE LATEST REVISION.		DWN P. PEPE 09JUN99	tyco Electronics AMP Incorporated Harrisburg, PA 17103-3608
DIMENSIONS: mm [INCHES]		CHK P. PEPE 09JUN99	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD P. PEPE 09JUN99	
9 PLC ±.01 1 PLC ±.01 2 PLC ±.01 3 PLC ±.01 4 PLC ±.01 ANGLES ±.01		PRODUCT SPEC APPLICATION SPEC	
MATERIAL FINISH		WEIGHT CUSTOMER DRAWING	SIZE CASE CODE DRAWING NO 00779 C=1339189