

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

©

COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD


E

CHANGE LOGO, VENT HOLE; ADD CQC, LINE IDENTIFIER AND PLATING THICKNESS ECO-12-005725

21-AUG-12

D.L

BH.Y



(D) (E)

PART A PART B

C:MADE IN CHINA

TE

OMI-SS-112DM

UL **us**

CSA

S

CCC

VE

10A

COSØ1 240V ~

10A

COSØ1 240V ~

3A COSØ0.4 240V ~

OEG

LOT NO.

1 CHARACTER(A TO Z)
FOR LINE IDENTIFIER

(E)

20,6

4,1

0,6

0,5

0,3

0,3

2,6

7,6

0,6

1

1

12,8

20

29,2

3,5

3,5

3,65

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

H.SASAKI

CHK

Y.OIKAWA

APVD

A.NAGAI

PRODUCT SPEC


APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC

± -

1 PLC

± -

2 PLC

± -

3 PLC

± -

4 PLC

± -

ANGLES

± -

FINISH

-

MATERIAL

-

DWN

H.SASAKI

CHK

Y.OIKAWA

APVD

A.NAGAI

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME

OMI -SS-D/L CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-4

1440000-6

SCALE

4:1

SHEET


1 of 2

REV


E

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HB	—						

CONNECTION DIAGRAM
(BOTTOM VIEW)



DRILLING DIAGRAM(2/1)
(BOTTOM VIEW)



B1	1461385-2	OMI-SS-109D	OMI-SS-109D	9V
	6-1440000-4	OMI-SS-148L	OMI-SS-148L	48V
	6-1440000-3	OMI-SS-148D	OMI-SS-148D	48V
	6-1440000-2	OMI-SS-136D	OMI-SS-136D	36V
	6-1440000-0	OMI-SS-124L	OMI-SS-124L	24V
	5-1440000-8	OMI-SS-124D	OMI-SS-124D	24V
	5-1440000-6	OMI-SS-112L	OMI-SS-112L	12V
	5-1440000-4	OMI-SS-112D	OMI-SS-112D	12V
	5-1440000-3	OMI-SS-109L	OMI-SS-109L	9V
	5-1440000-1	OMI-SS-106L	OMI-SS-106L	6V
	5-1440000-0	OMI-SS-106D	OMI-SS-106D	6V
	4-1440000-8	OMI-SS-105L	OMI-SS-105L	5V
	4-1440000-6	OMI-SS-105D	OMI-SS-105D	5V
	TE PART NO	EC TYPE NAME	PART A	PART B

RELAY TYPE

		EPOXY RESIN	RESIN	17
UL94 V-0		PBT	CASE	16
		—	TAPE	15
CLASS E		UEW	MAGNETIC WIRE	14
UL94 V-0		PET	BASE	13
UL94 V-0		PBT	BOBBIN	12
	SOLDER DIP	CP WIRE	COIL TERMINAL	11
UL94 V-0		PPS	CARD	10
		Ag ALLOY	MOVABLE CONTACT	9
		Ag ALLOY	STATIONARY CONTACT	8
		Cu ALLOY	HINGE SPRING	7
	SOLDER DIP	Cu ALLOY	B TERMINAL	6
	SOLDER DIP	Cu ALLOY	M TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
		STEEL	CORE	3
		STEEL	ARMATURE	2
		STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —
FINISH —

MATERIAL

—

DWN
H.SASAKI

CHK
Y.OIKAWA

APVD
A.NAGAI

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

OMI -SS-D/L CUSTOMER DRAWING

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-4-1440000-6

RESTRICTED TO

SCALE
4:1

SHEET
2 of 2

REV
E