



FEATURES:

- Allows four parallel connectors to the same point.
- 3 cross .166 dia. holes
- 4.2 (.166) dia., provide side stackup connection.

MATERIALS:

Upper Conn.: Banana Jack

Material: Brass per QQ-B-626. Alloy 360 ½ Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200 to 300 microinches.

Insulation: ABS molded to Banana Jack and Banana Plug Body.

Color: See Tab Block

Marking: "POMONA ELECTRONICS 3364."

Lower Conn.: Banana Plug

Material: Spring – Beryllium Copper per QQ-C-533, Alloy 170, Cond. H.T.

Body: Same as Upper Conn.

RATINGS:

Operating Temperature: +50° C (+122° F) Max.

Operating Voltage: 5000 VDC.

Current: 15 Amperes Cont.

Contact Resistance: Less than 1 milliohm.

ORDERING INFORMATION: Model 3364-*

*= Color, -0 Black, -2 Red

Ordering Example: 3364 -2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[3364-2](#) [3364-0](#)