

EW-460, EW-560

UNIPOLAR HALL EFFECT SWITCHES

ASAHI HALL EFFECT ICs


ASAHI KASEI ELECTRONICS Hall Effect ICs are composed of a Ultra-high sensitive InSb Hall element and a signal processing IC chip in a package. ASAHI KASEI ELECTRONICS Hall Effect ICs have high sensitivity and good stability.

FEATURES


- Bop(max):6mT
- 4.5V to 18V Operation
- Highly Resistant to Mechanical Stress
- Stable Operation in Broad Temperature Range
- Compact Size
- Open Collector

APPLICATIONS

- Rotor Position Sensor for Precision Motors.
- Stroke Sensor
- Proximity Switch
- Encoder
- Current Switch etc.



FUNCTIONAL BLOCK DIAGRAM




ABSOLUTE MAXIMUM RATINGS(Ta=25°C)

Item	Symbol	Limit	Unit
Supply Voltage *1	Vcc	18	V
Output "OFF" Voltage	Vo(off)	18	V
Output "ON" Current	I sink	15	mA
Operating Temperature Range	Topr	-30~+115	°C
Storage Temperature Range	Tstg	-40~+125	°C

*1:Please refer to(Fig.1)"DERATING CURVE"

OPERATIONAL CHARACTERISTICS




ELECTRICAL CHARACTERISTICS(Ta=25°C, Vcc=4.5~18V DC.)

Item	Symbol	Conditions	Min.	Typ.	Max.	Unit
Operate Point	Bop	Vcc=12V			6	mT
Release Point	Brp	Vcc=12V	0.5			mT
Hysteresis	Bh		0.2			mT
Output Saturation Voltage	Vsat	Output"L", I sink=10mA			0.4	V
Supply Current	I cc	Output"H", Vcc=12V			8	mA
Output Leakage Current	I leak	Output"H", Vo=12V			1	μA


1mT=10Gauss

(Fig. 1)

EW-560



EW-460




560
WG9

460
WG9


TYPE NO.

Supplied by
EW-560:500pcs./Pack.
EW-460:5000pcs./Reel

[Unit : mm]



EW-460 series



EW-560 series