



FB-EM-30345-000

SHT 1.1




TOP VIEW  
W/WINDSHIELD SHOWN  
SCALE 1:1


$\varnothing 19,0 \pm 0,3$   
[.748  $\pm$  .012]



60  $\pm$  5  
[2.36  $\pm$  .20]



PLASTIC HOUSING, BLACK



6,10  $\pm$  0,12  
[.240  $\pm$  .005]

BLACK POLYURETHANE SHRINK COVER  
ON FLEXI-SET BOOM



WIRES

2mm STRIPPED & TINNED ENDS

WIRE COLOR			WEIGHT GRAMS
+ve	OUTPUT	-ve	
RED	---	BLACK	---


DIMENSIONS IN MILLIMETERS [INCHES]

**KNOWLES ELECTRONICS**  
ITASCA, ILLINOIS U.S.A.

Revision	C.O. #	Implementation Date	RELEASE LEVEL	REVISION
B	CI0107747	8-9-08	Active	B
A	CI0107368	5-27-08		
SCALE: 1:1			DR. BY	DATE
DO NOT SCALE DRAWING			TT	5-27-08
TITLE: BOOM MICROPHONE FB-EM-30345-000			CK. BY	DATE
			GJP	6-4-08
OUTLINE DRAWING SHT 1.1			APP. BY	DATE
			GJP	6-4-08

KE111ASIZE.FRM



Rev: B



FREQUENCY	SENSITIVITY			DEVICE CONFORMITY RANGE OF DEVIATION FROM 1KHZ	
	MIN.	NOM.	MAX.		
300	---	-50.0	---	-4.0	+4.0
1000	-54.0	-50.0	-46	0.0	0.0
2000	---	-49.5	---	-4.0	---
6000	---	-45.5	---	0.0	+9

**NOTES:**

- MICROPHONE TO BE FUNCTIONAL WITH 10 VDC SUPPLY.
- SENSITIVITY VALUES INDICATED ON THIS SPECIFICATION ARE VALID AT 50% HUMIDITY.
- TEST CONDITIONS:  
HEAD OF BOOM EXPOSED TO 74 dB SPL SWEPT  
SOUND FIELD AT 6mm FROM VOICE APERTURE,  
ARTIFICIAL VOICE:  
B & K 4227 MOUTH SIMULATOR.
- FOR MICROPHONE CAPSULE SPEC. SEE DRAWING NR-25994-D63 SHEET 2.1.
- SURVIVES SUBMERSION IN 20m OF WATER FOR 5 MINUTES; SENSITIVITY WITHIN 3dB OF INITIAL SENSITIVITY AFTER DRIED FOR 30 MINUTES AT ROOM TEMPERATURE.



LEAD IDENTIFICATION  
& TEST CIRCUIT

**KNOWLES ELECTRONICS**  
ITASCA, ILLINOIS U.S.A.

Revision	C.O. #	Implementation Date	RELEASE LEVEL	REVISION
B	C10107747	8-9-08	<b>Active</b>	<b>B</b>
A	C10107368	5-27-08		
WHEN TEST LIMITS ARE USED TO ESTABLISH INCOMING INSPECTION ACCEPTANCE/REJECTION CRITERIA, CORRELATION OF TEST EQUIPMENT WITH KNOWLES IS ALSO REQUIRED FOR ELIMINATION OF EQUIPMENT AND TEST METHOD VARIATION			DR. BY	DATE
TITLE: <b>BOOM MICROPHONE FB-EM-30345-000</b>			TT	5-27-08
			CK. BY	DATE
			GJP	6-4-08
			APP. BY	DATE
PERFORMANCE SPECIFICATION			GJP	6-4-08
			<b>SHT 2.1</b>	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Knowles:

[FB-EM-30345-000](#)