

Features


Unregulated Converters

- Low cost 2W converter
- Industry standard SIP7 package
- 3kVDC or 4kVDC isolation options
- Single or dual outputs
- Short circuit protected (/P versions)
- EN62368-1 pending

RECOM
DC/DC Converter

RKZE

**2 Watt
SIP7
Single and Dual
Output**



EN62368-1 pending
EN55032 pending
EN55024 pending

Description

The RKZE series are low cost 2W DC/DC converters in a standard SIP7 footprint. This makes them suitable for price sensitive industrial, test and measurement and high volume applications. The RKZE converters are pin-compatible with the RK and RH converter series, offering a simple way to upgrade a 1W high isolation supply to 2W. Standard isolation is 3kVDC with a /H version factory tested to 4kVDC. The RKZE is available with single or dual outputs with optional continuous short circuit protection (/P suffix).

Selection Guide


Part Number	nom. Input Voltage [VDC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ. ⁽¹⁾ [%]	max. Capacitive Load ⁽²⁾ [μF]
RKZE-xx05S ^(3,4)	5, 12, 15, 24	5	400	81-83	1500
RKZE-xx09S ^(3,4)	5, 12, 15, 24	9	222	84-85	680
RKZE-xx12S ^(3,4)	5, 12, 15, 24	12	167	82-88	330
RKZE-xx15S ^(3,4)	5, 12, 15, 24	15	133	84-86	330
RKZE-xx05D ^(3,4)	5, 12, 15, 24	±5	±200	83-85	±680
RKZE-xx12D ^(3,4)	5, 12, 15, 24	±12	±84	84-85	±220
RKZE-xx15D ^(3,4)	5, 12, 15, 24	±15	±66	83-86	±220

Notes:

Note1: Efficiency is tested at nominal input and full load at +25°C ambient

Note2: Max Cap Load is tested at nominal input and full resistive load

Model Numbering



Notes:

Note3: standard part is without suffixes
without suffix, standard isolation voltage (3kVDC/1 second)
add suffix „/H“ for 4kVDC isolation

Note4: add suffix „/P“ for Continuous Short Circuit Protection
or add suffix „/HP“ for 4kVDC Isolation and Continuous Short Circuit Protection

Ordering Examples





RKZE-1205S = 12V Input Voltage, 5V Output Voltage, Single Output with 3kVDC Isolation
RKZE-1509S/H = 15V Input Voltage, 9V Output Voltage, Single Output with 4kVDC Isolation
RKZE-0505D/P = 5V Input Voltage, 5V Output Voltage, Dual Output with 3kVDC Isolation and Continuous Short Circuit Protection
RKZE-2415D/HP = 24V Input Voltage, 15V Output Voltage, Dual Output with 4kVDC Isolation and Continuous Short Circuit Protection

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

BASIC CHARACTERISTICS

Parameter	Condition		Min.	Typ.	Max.
Internal Input Filter			capacitor type		
Input Voltage Range				±10%	
Input Current	nom. Vin=	5VDC		500mA	
		12VDC		200mA	
		15VDC		160mA	
		24VDC		100mA	
Quiescent Current	nom. Vin=	5VDC		30mA	
		12VDC		15mA	
		15VDC		12mA	
		24VDC		7mA	
Minimum Load			0%		
Start-up Time				10ms	
Rise Time				2ms	
Internal Operating Frequency			20kHz		
Output Ripple and Noise	20MHz BW			75mVp-p	150mVp-p

Efficiency vs. Load



Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)



REGULATIONS

Parameter	Condition		Value
Output Accuracy			±5.0% max.
Line Regulation	low line to high line		±1.2% typ. / 1.0% max.
Load Regulation ⁽⁵⁾	10% to 100% load	5Vout	15% max.
		9, 12, 15Vout	10% max.
Cross Regulation	dual output only		±5.0% typ.

Notes:

Note5: Operation below 10% load will not harm the converter, but specifications may not be met

Tolerance Envelope



PROTECTIONS

Parameter	Type		Value
Short Circuit Protection (SCP)	below 100mΩ, "/P" suffix		continuous
Isolation Voltage ⁽⁶⁾	I/P to O/P	standard part	tested for 1 second rated for 1 minute 3kVDC 1.5kVAC
		"/H" suffix	tested for 1 second rated for 1 minute 4kVDC 1.8kVAC
Isolation Resistance			10GΩ min.
Isolation Capacitance			120pF max.
Leakage Current			0.3μA max.
Insulation Grade			functional

Notes:

Note6: For repeat Hi-Pot testing, reduce the time and/or the test voltage

Note7: Refer to local safety regulations if input over-current protection is also required. Recommended fuse: slow blow type

ENVIRONMENTAL

Parameter	Condition	Value
Operating Temperature Range	full load @ natural convection 0.1m/s (see graph)	-40°C to +80°C
Maximum Case Temperature		+110°C
Temperature Coefficient		±0.01%/K
Thermal Impedance	0.1m/s, horizontal	46K/W
Operating Altitude		2000m
Operating Humidity	non-condensing	5% - 95% RH


continued on next page

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Parameter	Condition		Value
MTBF	according to MIL-HDBK-217F, G.B.	+25°C +80°C	18300 x 10 ³ hours 8070 x 10 ³ hours

Derating Graph

(@ Chamber and natural convection 0.1 m/s)



SAFETY AND CERTIFICATIONS

Certificate Type (Safety)	Report / File Number	Standard
Audio/video, information and communication technology equipment. Safety requirements	pending	EN62368-1
RoHs 2+		RoHs 10/10, 2011/65/EU + AM2015/863
EMC Compliance	Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment – Emission Requirements	pending	EN55032, Class A EN55032, Class B
Information technology equipment - Radio disturbance characteristics - Limits and methods of measurement	pending	EN55024



DIMENSION and PHYSICAL CHARACTERISTICS

Parameter	Type	Value
Material	case potting	black plastic, (UL94V-0) epoxy, (UL94V-0)
Dimension (LxWxH)		19.65 x 7.05 x 10.20mm
Weight		2.8g typ.

continued on next page

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Dimension Drawing (mm)




Pin Connections

Pin #	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
5	-Vout	-Vout
6	No Pin	Com
7	+Vout	+Vout

XX.X ± 0.5mm
XX.XX ± 0.25mm

Recommended Footprint Details



PACKAGING INFORMATION

Parameter	Type	Value
Packaging Dimension (LxWxH)	tube	520.0 x 16.0 x 9.0mm
Packaging Quantity	tube	25pcs
Storage Temperature Range		-55°C to +125°C
Storage Humidity		5% to 95% RH

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.