






	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1
	PART NUMBER	PLATING			RECOMMENDED WIRE SIZE	DIM "A" BLADE LENGTH	DIM "B" WIDTH	DIM "C" HEIGHT	RECOMMENDED CRIMP APPLICATOR	PRODUCT STATUS										
M	44262-6510	80-160μ INCHES TIN OVERALL OVER 50μ INCHES NICKEL OVERALL			8 AWG (2) 12 AWG	10.03/.395	N/A	N/A	63832-6300	NOT TOOLED	NOTES: 1. MATERIAL: COPPER ALLOY .032 IN THICK 2. FINISH: PER MOLEX PLATING SPECIFICATION ES-88 - SEE CHART 3. SEE CHART FOR CRIMP APPLICATOR NUMBER 4. FOR CRIMP TOOLING CONTACT MOLEX OR VISIT THE MOLEX WEBSITE AT WWW.MOLEX.COM 5. STD PACKAGE SIZE: 2,500 PARTS/REEL 6. SEE PRODUCT SPECIFICATION: PS-44262-001 FOR MORE INFORMATION. 7. PARTS ARE RoHS COMPLIANT 8. THIS PART MATES WITH RECEPTACLE (FEMALE) POWER CONTACT 44262-43** (SEE SD-44262-100) 9. FOR CRIMP SET UP INFORMATION SEE MOLEX APPLICATION DOCUMENT: 8 AWG - ATS-638326300 10/12 AWG - ATS-638326000 14/16 AWG - ATS-638326100									
L	44262-6511					11.56/.455														
	44262-6512					13.08/.515														
L	44262-6520	30μ INCHES SELECT GOLD STRIPE OVER 50μ INCHES NICKEL OVERALL WITH 80-160μ INCHES SELECT TIN			(2) 12 AWG	10.03/.395	N/A	N/A	63832-6300	NOT TOOLED										
	44262-6521					11.56/.455														
	44262-6522					13.08/.515														
K	44262-6310	80-160μ INCHES TIN OVERALL OVER 50μ INCHES NICKEL OVERALL			10-12 AWG (2) 14 AWG	10.03/.395	5.33+-.025 .210+-.010	5.97+-.050 .235+-.020	63832-6000	TOOLED										
	44262-6311					11.56/.455														
	44262-6312					13.08/.515														
K	44262-6320	30μ INCHES SELECT GOLD STRIPE OVER 50μ INCHES NICKEL OVERALL WITH 80-160μ INCHES SELECT TIN			(2) 14 AWG	10.03/.395			63832-6000	TOOLED										
	44262-6321					11.56/.455														
	44262-6322					13.08/.515														
J	44262-6410	80-160μ INCHES TIN OVERALL OVER 50μ INCHES NICKEL OVERALL			14-16 AWG (2) 16 AWG	10.03/.395	5.33+-.025 .210+-.010	5.21+-.050 .205+-.020	63832-6100	TOOLED										
	44262-6411					11.56/.455														
	44262-6412					13.08/.515														
I	44262-6420	30μ INCHES SELECT GOLD STRIPE OVER 50μ INCHES NICKEL OVERALL WITH 80-160μ INCHES SELECT TIN			(2) 18 AWG	10.03/.395			63832-6100	TOOLED										
	44262-6421					11.56/.455														
	44262-6422					13.08/.515														



REV DIMS & CHART IEC NO: 2010/01/06 DRAWN: JUILLES CHKD: C6 APPR:	QUALITY SYMBOLS V=0 V=0 V=0	GENERAL TOLERANCES (UNLESS SPECIFIED): mm INCH 4 PLACES ± .010 ± .010 3 PLACES ± .010 ± .010 2 PLACES ± .025 ± .010 1 PLACE ± .025 ± .010 ANGULAR ± 1/2°	DIMENSION STYLE MM/IN SCALE 5:1 DESIGN UNITS INCH	THIRD ANGLE PROJECTION
		DRAWN BY: BKOSTIC DATE: 2006/11/14 CHECKED BY: BKOSTIC DATE: 2006/11/14 APPROVED BY: APATEL DATE: 2006/11/14	TITLE TERMINAL - BLADE POWER TERMINAL	
		MATERIAL NO. SEE CHART	DOCUMENT NO. SD-44262-026	
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	SHEET NO. 1 OF 1	