

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0848546042

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

DeviceNet Micro-Change Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), NMEA 2000 Style Cable, 8.0m (26.25') Length, meets NMEA 2000

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Industrial Cordsets

Series

84854

Connector End A

Micro-Change (M12)

Connector End B

Micro-Change (M12)

IP Rating

IP67

Material - Contact

Copper Alloy

Overview

Brad Micro-Change (M12) Connectors

Product Name

Micro-Change (M12)

Protocol

N/A

Region

Europe

Type

Double Ended

UPC

822350898379

Physical

Cable Diameter

5.72mm (.225")

Cable Length

8.0m (26.25')

Color - Cable Jacket

Gray

Coupling Style

Threaded

Gender

Female-Male

Keyway

Single

LED Indicator

No

Material - Cable Jacket

PVC

Material - Connector Body

PVC

Material - Coupling Nut

Nickel-plated Brass

Material - Plating Mating

Gold

Orientation

Straight to Straight

Poles

5

Temperature Range - Operating

-20°C to +105°C

Wire Size AWG

22

Wire/Cable Type

Thin Standard Cable

Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

250V

Material Info

Engineering Number

NMEA-DND22NB-M080

Reference - Drawing Numbers

Sales Drawing

SD-84854-016



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Not Relevant

Not Relevant

Not Reviewed

Search Parts in this Series

84854 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION