

NB12, Surface Mount Thermistors

NC 12 – NC 20



Chip thermistors are a high quality and low cost device especially developed for surface mounting applications. They are widely used for temperature compensation but can also achieve temperature control of printed circuits. Its silver - palladium - platinum metallization provides a high degree of resistance to dewetting of the terminations during soldering (typically 260°C / 30 s).

HOW TO ORDER

NC 20

Type

K 0

Material Code
K

0103

Resistance
10,000 Ω

M

Tolerance
M (±20%)
J (±5%)
K (±10%)

BA

Suffix: Packaging
--: Bulk
BA: Plastic tape
(180mm diam. reel)
BE: Plastic tape (1/2 reel)
BC: Plastic tape
(330mm diam. reel)
BB: Cardboard tape
(180mm diam. reel)
BF: Cardboard tape (1/2 reel)
BD: Cardboard tape
(330mm diam. reel)

TABLE OF VALUES (Min/Max)

NC 12 IEC SIZE : 0805				
Types	Rn at 25°C (Ω)	Material Code	B (K) ($\Delta B/B$ ⁽¹⁾ ± 5% ₍₂₎ ± 3%)	α at 25°C (%/°C)
NC 12 KC 0 180 NC 12 KC 0 101	18 100	KC	3470 ± 5%	- 3.9
NC 12 MC 0 121 NC 12 MC 0 332	120 3,300	MC	3910 ± 3%	- 4.4
NC 12 J 0 0332 NC 12 J 0 0562	3,300 5,600	J	3480 ± 3%	- 3.9
NC 12 K 0 0682 NC 12 K 0 0123	6,800 12,000	K	3630 ± 3%	- 4.0
NC 12 L 0 0153 NC 12 L 0 0183	15,000 18,000	L	3790 ± 3%	- 4.2
NC 12 M 0 0223 NC 12 M 0 0393	22,000 39,000	M	3950 ± 3%	- 4.4
NC 12 N 0 0473 NC 12 N 0 0563	47,000 56,000	N	4080 ± 3%	- 4.6
NC 12 L 2 0683 NC 12 N 0 0823	68,000 82,000	L2 N	3805 ± 3% 4080 ± 3%	- 4.1 - 4.6
NC 12 P 0 0104 NC 12 P 0 0184	100,000 180,000	P	4220 ± 3%	- 4.7
NC 12 Q 0 0224	220,000	Q	4300 ± 3%	-4.7

NC 20 IEC SIZE : 1206				
Types	Rn at 25°C (Ω)	Material Code	B (K) ($\Delta B/B$ ⁽¹⁾ ± 5% ₍₂₎ ± 3%)	α at 25°C (%/°C)
NC 20 KC 0 100 NC 20 KC 0 101	10 100	KC	3470 ± 5%	- 3.9
NC 20 MC 0 121 NC 20 MC 0 152	120 1,500	MC	3910 ± 3%	- 4.4
NC 20 I 0 0182 NC 20 I 0 0332	1,800 3,300	I	3250 ± 5%	- 3.7
NC 20 J 0 0392 NC 20 J 0 0682	3,900 6,800	J	3480 ± 3%	- 3.9
NC 20 K 0 0822 NC 20 K 0 0153	8,200 15,000	K	3630 ± 3%	- 4.0
NC 20 L 0 0183 NC 20 L 0 0223	18,000 22,000	L	3790 ± 3%	- 4.2
NC 20 M 0 0273 NC 20 M 0 0473	27,000 47,000	M	3950 ± 3%	- 4.4
NC 20 N 0 0563 NC 20 N 0 0104	56,000 100,000	N	4080 ± 3%	- 4.6
NC 20 P 0 0124 NC 20 P 0 0224	120,000 220,000	P	4220 ± 3%	- 4.7
NC 20 Q 0 0274 NC 20 Q 0 0474	270,000 470,000	Q	4300 ± 3%	- 4.7
NC 20 R 0 0564 NC 20 R 0 0105	560,000 1,000,000	R	4400 ± 3%	- 4.8