




- 1 BULK PACKAGED
- 2 FLAT END FACE
- 3 RADIUSSED END FACE
- 4 BARE BUFFER STRAIN RELIEF, 900µm
- 5 BEND LIMITING STRAIN RELIEF (BLACK)
- 6 SHORT STRAIN RELIEF (1.0 INCH LENGTH) (BLACK)
- 8 BEND LIMITING STRAIN RELIEF (RED)
- 9 BEND LIMITING STRAIN RELIEF (BLUE)

- 10 NO STRAIN RELIEF
- 11 SHORT STRAIN RELIEF (1.0 INCH LG) (BLUE)
- 12 LONG STRAIN RELIEF (BLACK)
- 13 BEND LIMITING STRAIN RELIEF (BLUE, NO LOGO)
- 14. ALL KITS FOR 3.1mm MAX CABLE OD USE INSTRUCTION SHEET 408-4151.
- 15. ALL KITS FOR 4.3mm MAX CABLE OD USE INSTRUCTION SHEET 408-4162.

DESCRIPTION	A MAX
LONG STRAIN RELIEF	73.7[2.90]
BEND LIMITING STRAIN RELIEF	77.6[3.06]
SHORT STRAIN RELIEF (1.0 IN)	48.8[1.92]
BARE BUFFER STRAIN RELIEF	56.6[2.23]

OBSOLETE	5/3	3.1mm	180µm	5-504008-5
OBSOLETE	10/3	3.1mm	125µm	5-504008-4
OBSOLETE	5/3	3.1mm	500µm	5-504008-3
OBSOLETE	5/3	3.1mm	400µm	5-504008-2
OBSOLETE	5/3	3.1mm	267µm	5-504008-1
SUPERSEDED BY 5-504008-4 PLUS 502128-8	13/2	3.1mm	125µm	5-504008-0
OBSOLETE	13/2	3.1mm	140µm	4-504008-9
OBSOLETE	6/3	3.1mm	140µm	4-504008-8
OBSOLETE	6/3	3.1mm	140µm	4-504008-7
OBSOLETE	5/3	3.1mm	280µm	4-504008-6
OBSOLETE	12/3	4.3mm	600µm	4-504008-5
OBSOLETE	5/2	3.1mm	436µm	4-504008-4
OBSOLETE	5/3	3.1mm	250µm	4-504008-3
OBSOLETE	5/3	3.1mm	160µm	4-504008-2
OBSOLETE	5/3	3.1mm	231µm	4-504008-1
OBSOLETE	5/2	3.1mm	125µm	4-504008-0
OBSOLETE	5/3	3.1mm	229µm	3-504008-9
OBSOLETE	5/2	3.1mm	280µm	3-504008-8
OBSOLETE	5/2	3.1mm	126µm	3-504008-7
OBSOLETE	4/3	3.1mm	140µm	3-504008-6
OBSOLETE	12/3	4.3mm	240µm	3-504008-5
SUPERSEDED BY 1-504008-4	5/3	3.1mm	231µm	3-504008-4
OBSOLETE	12/3	4.3mm	.042in	3-504008-3
OBSOLETE	5/3	3.1mm	640µm	3-504008-2
OBSOLETE	5/3	3.1mm	336µm	3-504008-1
SUPERSEDED BY 504008-7	5/3	3.1mm	140µm	3-504008-0
SUPERSEDED BY 504008-7	5/3	3.1mm	140µm	2-504008-9
SUPERSEDED BY 504008-4	4/3	4.3mm	125µm	2-504008-8
OBSOLETE	12/3	4.3mm	125µm	2-504008-7
SUPERSEDED BY 5-504008-4 PLUS 1-501457-2	11/3	3.1mm	125µm	2-504008-6
SUPERSEDED BY 5-504008-4 PLUS 1-501457-2	11/3	3.1mm	125µm	2-504008-5
OBSOLETE	9/3	3.1mm	125µm	2-504008-4
SUPERSEDED BY 5-504008-4 PLUS 1-502128-3	9/3	3.1mm	125µm	2-504008-3
SUPERSEDED BY 5-504008-4 PLUS 1-501457-8	6/3	3.1mm	125µm	2-504008-2
SUPERSEDED BY 5-504008-4 PLUS 1-501457-8	6/3	3.1mm	125µm	2-504008-1
SUPERSEDED BY 5-504008-4 PLUS 1-502128-1	8/3	3.1mm	125µm	2-504008-0
OBSOLETE	8/3	3.1mm	125µm	1-504008-9
SUPERSEDED BY 504008-3	5/3	3.1mm	125µm	1-504008-8
OBSOLETE	5/3	3.1mm	125µm	1-504008-7
OBSOLETE	5/3	4.3mm	410µm	1-504008-6
OBSOLETE	5/3	3.1mm	436µm	1-504008-5
OBSOLETE	5/3	3.1mm	231µm	1-504008-4
OBSOLETE	5/3	3.1mm	240µm	1-504008-3
SUPERSEDED BY 5-504008-4 PLUS 501457-8	6/3	3.1mm	125µm	1-504008-2
SUPERSEDED BY 5-504008-4 PLUS 501457-8	6/3	3.1mm	125µm	1-504008-1
SUPERSEDED BY 5-504008-4 PLUS 1-503628-5	4/3	3.1mm	125µm	1-504008-0
SUPERSEDED BY 5-504008-4 PLUS 1-503628-5	4/3	3.1mm	125µm	504008-9
OBSOLETE	12/3	4.3mm	140µm	504008-8
OBSOLETE	5/3	3.1mm	140µm	504008-7
SUPERSEDED BY 504008-8	12/3	4.3mm	140µm	504008-6
SUPERSEDED BY 504008-7	5/2	3.1mm	140µm	504008-5
OBSOLETE	12/3	4.3mm	125µm	504008-4
OBSOLETE	5/3	3.1mm	125µm	504008-3
SUPERSEDED BY 504008-4	12/2	4.3mm	125µm	504008-2
SUPERSEDED BY 504008-3	5/2	3.1mm	125µm	504008-1

MAX CABLE O.D.	HOLE SIZE	PART NUMBER
----------------	-----------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. YEAGER 3-26-94	AMP AMP Incorporated Harrisburg, PA 17105-3608
DIMENSIONS: mm (INCHES)		CHK S. BUCHTER 3-26-94	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD B. EDWARDS 3-26-94	
0 PLC +/- 1 PLC +/- 2 PLC +/- 3 PLC +/- 4 PLC +/- ANGLES		PRODUCT SPEC	
MATERIAL SST FERRULE ALUM REAR BODY		FINISH -	APPLICATION SPEC
WEIGHT -		SIZE A1	CAGE CODE 00779
CUSTOMER DRAWING		SCALE -	SHEET 1 OF 1
		REV V	