


TOSHIBA Transistor Silicon NPN Epitaxial Type (PCT Process)

RN1321A, RN1322A, RN1323A, RN1324A RN1325A, RN1326A, RN1327A

Switching, Inverter Circuit, Interface Circuit
and Driver Circuit Applications

- High current driving is possible.
- Since bias resistors are built in the transistor, the miniaturization of the apparatus by curtailment of the number of parts and labor saving of an assembly are possible.
- Many kinds of resistance value are lined up in order to support various kinds of circuit design.
- Complementary to RN2321A to RN2327A
- Low $V_{CE(sat)}$ enable to be low power dissipation on high current driving.

Equivalent Circuit And Bias Resistance Values



Type No.	R1 (k Ω)	R2 (k Ω)
RN1321A	1	1
RN1322A	2.2	2.2
RN1323A	4.7	4.7
RN1324A	10	10
RN1325A	0.47	10
RN1326A	1	10
RN1327A	2.2	10

Unit: mm

USM	—
JEDEC	—
JEITA	SC-70
TOSHIBA	2-2E1A

1. BASE
2. EMITTER
3. COLLECTOR

Weight: 6 mg (typ.)

Absolute Maximum Ratings ($T_a = 25^\circ\text{C}$)





Characteristic	Symbol	Rating	Unit
Collector-base voltage	V_{CBO}	15	V
Collector-emitter voltage	V_{CEO}	12	V
Emitter-base voltage	V_{EBO}	10	V
		5	V
		6	V
Collector current	I_C	500	mA
Collector power dissipation	P_C	100	mW
Junction temperature	T_j	150	$^\circ\text{C}$
Storage temperature range	T_{stg}	-55 to 150	$^\circ\text{C}$





Note: Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings.





Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).





Electrical Characteristics (Ta = 25°C)





Characteristic		Symbol	Test Circuit	Test Condition	Min	Typ.	Max	Unit
Collector cut-off current	RN1321A to 1327A	I_{CBO}	—	$V_{CB} = 15V, I_E = 0$	—	—	100	nA
		I_{CEO}		$V_{CE} = 12V, I_B = 0$	—	—	500	
Emitter cut-off current	RN1321A	I_{EBO}	—	$V_{EB} = 10V, I_C = 0$	3.85	—	7.14	mA
	RN1322A				1.75	—	3.25	
	RN1323A				0.82	—	1.52	
	RN1324A			$V_{EB} = 5V, I_C = 0$	0.38	—	0.71	
	RN1325A				0.365	—	0.682	
	RN1326A				0.35	—	0.65	
	RN1327A			$V_{EB} = 6V, I_C = 0$	0.378	—	0.703	
DC current gain	RN1321A	h_{FE}	—	$V_{CE} = 1V, I_C = 50mA$	35	—	—	
	RN1322A				65	—	—	
	RN1323A				100	—	—	
	RN1324A				140	—	—	
	RN1325A				140	—	—	
	RN1326A				140	—	—	
	RN1327A				140	—	—	
Collector-emitter saturation voltage	RN1321A	$V_{CE(sat)}$	—	$I_C = 50mA, I_B = 2mA$	—	—	0.25	V
	RN1322A to 1327A			$I_C = 50mA, I_B = 1mA$	—	—	0.25	
Input voltage (ON)	RN1321A	$V_{I(ON)}$	—	$V_{CE} = 0.2V, I_C = 50mA$	1.0	—	2.4	V
	RN1322A				1.1	—	2.7	
	RN1323A				1.3	—	3.5	
	RN1324A				1.5	—	5.2	
	RN1325A				0.5	—	1.2	
	RN1326A				0.6	—	1.4	
	RN1327A				0.7	—	1.9	
Input voltage (OFF)	RN1321A to 1324A	$V_{I(OFF)}$	—	$V_{CE} = 5V, I_C = 0.1mA$	0.8	—	1.4	V
	RN1325A, 1326A				0.4	—	0.8	
	RN1327A				0.5	—	1.0	
Transition frequency	RN1321A to 1327A	f_T	—	$V_{CE} = 5V, I_C = 20mA$	—	300	—	MHz
Collector Output capacitance	RN1321A to 1327A	C_{ob}	—	$V_{CB} = 10V, I_E = 0, f = 1MHz$	—	4	7	pF
Input resistor	RN1321A	R_1	—	—	0.7	1	1.3	kΩ
	RN1322A				1.54	2.2	2.86	
	RN1323A				3.29	4.7	6.11	
	RN1324A				7	10	13	
	RN1325A				0.329	0.47	0.611	
	RN1326A				0.7	1	1.3	
	RN1327A				1.54	2.2	2.86	
Resistor ratio	RN1321A to 1324A	R_1/R_2	—	—	0.85	1.00	1.15	
	RN1325A				0.040	0.047	0.054	
	RN1326A				0.085	0.100	0.115	
	RN1327A				0.187	0.220	0.253	






























Type Name	Marking
RN1321A	
RN1322A	
RN1323A	
RN1324A	
RN1325A	
RN1326A	
RN1327A	

RESTRICTIONS ON PRODUCT USE

- Toshiba Corporation, and its subsidiaries and affiliates (collectively "TOSHIBA"), reserve the right to make changes to the information in this document, and related hardware, software and systems (collectively "Product") without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. **TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.**
- Product is intended for use in general electronics applications (e.g., computers, personal equipment, office equipment, measuring equipment, industrial robots and home electronics appliances) or for specific applications as expressly stated in this document. Product is neither intended nor warranted for use in equipment or systems that require extraordinarily high levels of quality and/or reliability and/or a malfunction or failure of which may cause loss of human life, bodily injury, serious property damage or serious public impact ("Unintended Use"). Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, devices related to electric power, and equipment used in finance-related fields. Do not use Product for Unintended Use unless specifically permitted in this document.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- **ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.**
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. TOSHIBA assumes no liability for damages or losses occurring as a result of noncompliance with applicable laws and regulations.