


8685/9036




Basic Part Number	Length A
8685-0	.125
9036-0	.175

XXXX-0-00-XX-00-00-03-0

Press-fit in .033 mounting hole.
Pin material is Ph. Br. 544 (B2)


9051



9051-0-00-XX-00-00-03-0

Press-fit in .057 mounting hole


8969



8969-0-05-XX-00-00-03-0

Square press-fit in .023 plated thru hole (use .7 mm drill prior to plating)


8979



8979-0-00-XX-00-00-03-0

Hex press-fit in .074 plated thru hole


9159



9159-0-00-XX-00-00-03-0

Press-fit in .026 mounting hole

3155/5155




X155-0-00-XX-00-00-03-0

Press-fit in .026 mounting hole
Pin material is Ph. Br. 544 (B2)

Basic Part Number	Length A
3155-0	.180
5155-0	.130


4194



4194-0-00-XX-00-00-08-0

Wire termination
Press-fit in .036 hole


5556



5556-0-00-XX-00-00-38-0

Wire termination


3790



3790-0-00-XX-00-00-03-0

Press-fit in .057 mounting hole

3796



3796-0-00-XX-00-00-03-0

Press-fit in .057 mounting hole

SPECIFICATIONS

PIN MATERIAL:
Brass Alloy 360, 1/2 Hard
(Except where noted)

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 0X - XX - 00 - 00 - 0X - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 200μ" TIN/LEAD OVER NICKEL
- 80 200μ" TIN OVER NICKEL
- 15 10μ" GOLD OVER NICKEL
- 21 20μ" GOLD OVER NICKEL
- 34 50μ" GOLD OVER NICKEL

