



# Wire Pulling Grips

Klein Tools has been manufacturing grips for over 135 years. Klein combines strength and durability to create an extremely high-quality line of grips. With ease-of-use and reliability, Klein wire-pulling grips set the mark.

For Professionals...  
Since 1857™

## Recommended Care and Maintenance

### Grip Cleaning, Lubricating and Inspecting

The following guidelines have been established to keep all grips in good working condition.

#### Cleaning




◀ **Step 1.** Use the Klein Grip Cleaning Wire Brush Set (Cat. No. 25450) or emery cloth to clean the surfaces of grip jaws



▲ **Step 2.**  
Spray degreaser on the grip jaws, all joints and moving parts




◀ **Step 3.** Use the Klein Grip Cleaning Wire Brush to remove dirt and debris from the grip jaws




**Step 4.** Wipe grips dry with soft cloth. Repeat all cleaning steps as necessary until grip is completely clean ▶

#### Lubricating



◀ **Step 5.**  
Apply lubricant to all joints and moving parts. Do NOT lubricate gripping surfaces of jaws


**Step 6.** Carefully inspect jaw condition, proper alignment of jaws and all parts, and possible distortion caused by exceeding safe-load specifications. Grips should operate smoothly. Spring-loaded grips should lock open with loop handle in "Down" position and should close automatically with loop handle "Up." The Klein Parallel Jaw Grip may be tested by opening and closing the jaws by hand, exercising proper caution. All parts and rivets should be checked for distortion ▶



**Note:** Conductors may have a die-grease coating which can deposit on grip jaws. New conductors should be wiped clean before grip application. Grip jaws should be wiped clean of all grease before use.

**Never repair any grip.** Grips that are bent, misaligned, or otherwise distorted should be discarded and replaced.

If there is ever a question about the safe condition of any grip, please contact Klein Tools Customer Service directly at 844-395-3235 or email [Hisupport@kleintools.com](mailto:Hisupport@kleintools.com).



## Types of Wire Pulling Grips

Klein Chicago™, Parallel Jaw and Haven's™ Grips are widely used in the power, communications, and general construction fields to pull wire and cable. The grips maintain temporary tension until the wire or cable can be permanently terminated.

### Klein Chicago™ Grips

**Designed for use on aluminum, copper, weatherproof coated wire, PVC covered conductors and messenger and guy strand**

- Locking loop handles allow the jaws to be held in an open position for easy placement on wire or cable
- Available in Round, Double V, Single V and Aggressive jaw contours



1656-30

### Parallel Jaw Grips

**Lightweight compact grips pull an exceptionally wide range of cable types and sizes**

- Latch helps maintain cable position
- Large-diameter eye accommodates large hooks on hoists, winches and tackle blocks
- Available in Round and Double V jaw contours



KT4500

### Haven's™ Grips

**Designed for use when a light, compact grip is desired where conductor deformation is not a factor**

- Knurled eccentric jaw applies gripping pressure to 1/4" of cable area
- Some models include a swing latch that holds cable securely in jaw
- Recommended for messenger and guy strand and wire rope
- 1625 Series can be used for wire rope




1625-20

### Hot-line Latch

**Designed for placing a grip on cable with a hot-line stick.**

- The three notches in the hot-line latch adjust the balance of the grip to better match the direction of the cable sag
- When stick is removed, latch closes automatically to guard against grip accidentally disengaging from wire
- Standard hot-line grips are not supplied with springs or lock-open features
- Some grips are available with a positionable latch



## Wire Pulling Grips Warnings

**⚠ WARNING:** Grips are to be used for temporary installation, not for permanent anchorage.

**⚠ WARNING:** When used on/or near energized lines, ground, insulate, or isolate grip before pulling.





**⚠ WARNING:** Do not exceed rated capacity.

**⚠ WARNING:** Always match proper size and type of grip to application.

**⚠ WARNING:** Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.



## Types of Jaw Contours

| Single V                                                                           |                                                                                                                                                                                                                                                                                  | Steel Strand<br>Cat. No.                                                                                                                                                                      |                                                                                                                                                                               |                                                                                                                                             |                                                                                                                    |                    |
|------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------|--------------------|
|    | <ul style="list-style-type: none"><li>Simple three-point contact jaws.</li><li>Designed for use on small diameter bare wire and cable (solid and stranded).</li></ul>                                                                                                            | 1613-30                                                                                                                                                                                       | -                                                                                                                                                                             |                                                                                                                                             |                                                                                                                    |                    |
| Double V                                                                           |                                                                                                                                                                                                                                                                                  | Steel Strand<br>Cat. No.                                                                                                                                                                      | Wide Range of Cables<br>Cat. No.                                                                                                                                              |                                                                                                                                             |                                                                                                                    |                    |
|    | <ul style="list-style-type: none"><li>Four-point contact provides greater gripping pressure and assures proper alignment of wire and cable within the jaws.</li><li>Designed for high strength messenger and guy strand and extra high-strength cables and conductors.</li></ul> | 1613-40 and 1613-40H, 1628-16 1628-16AT (Bell System) 1628-17, 1628-18, 1684-5 1684-5AT (Bell System) 1684-5H, 1692-5 1692-5AT (Bell System) 1684-74 and S1684-74H (EHS Cable) 1684-5F        | 1671-10 1672-10 1686-10 1686-20                                                                                                                                               | -                                                                                                                                           |                                                                                                                    |                    |
| Round                                                                              |                                                                                                                                                                                                                                                                                  | ACSR and AAC<br>Cat. No.                                                                                                                                                                      | Weatherproof and PVC Covered Copper<br>Cat. No.                                                                                                                               | Steel Strand<br>Cat. No.                                                                                                                    | Wide Range of Cables<br>Cat. No.                                                                                   |                    |
|   | <ul style="list-style-type: none"><li>Round jaws provide maximum contact and gripping power to minimize conductor deformation. (Smooth and knurled styles).</li><li>Recommended for use on bare aluminum, and copper conductors.</li></ul>                                       | 1628-16P SERIES<br>1628-30 SERIES<br>1628-40 SERIES<br>1628-50 SERIES<br>1656-20 and 1656-20H<br>1656-30 and 1656-30H<br>1656-40 and 1656-40H<br>1656-50 and 1656-50H<br>1656-60 and 1656-60H | <br>Notched Jaw<br>1611-20 1659-20<br>1611-30 1659-30<br>1611-40 1659-40<br>1611-50 1659-50 | <br>Serpentine Jaw<br>1659-20 1659-30<br>1659-40 1659-50 | <br>Serpentine Jaw<br>1659-5AT | 1685-20<br>1685-31 |
| Aggressive                                                                         |                                                                                                                                                                                                                                                                                  | Steel Strand<br>Cat. No.                                                                                                                                                                      |                                                                                                                                                                               |                                                                                                                                             |                                                                                                                    |                    |
|  | <ul style="list-style-type: none"><li>Recommended for use when conductor deformation is not an issue or when a more aggressive bite is needed.</li></ul>                                                                                                                         | 1604-10<br>1604-20<br>1604-20L<br>1625-20 (For Wire Rope)<br>1625-20 1 (For Wire Rope)<br>1625-20 7/8 (For Wire Rope)<br>1684-5C (EHS)                                                        | -                                                                                                                                                                             |                                                                                                                                             |                                                                                                                    |                    |

## Selecting the Proper Grip


### Grip Recommendation

Klein Tools offers a service of recommending the proper grip for a particular application based on a sample of cable. This service is free of charge. All that we require is a minimum 6-9 foot (2-3 m) length of cable.

If there is ever a question about the safe condition of any grip, please contact Klein Tools at **844.395.3235** or email: [HiSupport@kleintools.com](mailto:HiSupport@kleintools.com)

Three basic factors are needed in order to determine the proper grip for each specific application:

1. Type of wire or cable  
(ACSR, ACSS, AAC, Copper, Steel Strand).
2. AWG or MCM (diameter) of wire or cable.
3. Maximum safe load required.



## ACSR (Aluminum Conductor Steel Reinforced)

For Cable Diameter

**4 AWG - 636 MCM**

**.250" - .953" (6.35 mm - 24.21 mm)**

### MAXIMUM SAFE LOAD

| AWG or MCM<br>Cable Size | Diameter inches<br>(mm) | No. of Alum. &<br>Steel Strands | Code<br>Word | MAXIMUM SAFE LOAD                                              |                                    |                                     |                                     |
|--------------------------|-------------------------|---------------------------------|--------------|----------------------------------------------------------------|------------------------------------|-------------------------------------|-------------------------------------|
|                          |                         |                                 |              | <b>A</b><br>4,500 lbs<br>(2041 kg)                             | <b>B</b><br>8,000 lbs<br>(3629 kg) | <b>C</b><br>15,000 lbs<br>(6803 kg) | <b>D</b><br>20,000 lbs<br>(9072 kg) |
|                          |                         |                                 |              | Cat. No.                                                       | Cat. No.                           | Cat. No.                            | Cat. No.                            |
| 4                        | .250" (6.35 mm)         | 6 x 1                           | Swan         | 1656-20, 1656-20H & S1656-20H                                  |                                    |                                     |                                     |
| 4                        | .257" (6.53 mm)         | 7 x 1                           | Swanate      | 1656-20, 1656-20H & S1656-20H                                  |                                    |                                     |                                     |
| 2                        | .316" (8.03 mm)         | 6 x 1                           | Sparrow      | 1656-20, 1656-20H, S1656-20H,<br>1656-30, 1656-30H & S1656-30H |                                    |                                     |                                     |
| 2                        | .325" (8.26 mm)         | 7 x 1                           | Sparate      | 1656-20, 1656-20H, S1656-20H,<br>1656-30, 1656-30H & S1656-30H |                                    |                                     |                                     |
| 1                        | .354" (9.02 mm)         | 6 x 1                           | Robin        | 1656-20, 1656-20H, S1656-20H,<br>1656-30, 1656-30H & S1656-30H |                                    |                                     |                                     |
| 1/0                      | .398" (10.11 mm)        | 6 x 1                           | Raven        | 1656-20, 1656-20H, S1656-20H,<br>1656-30, 1656-30H & S1656-30H |                                    |                                     |                                     |
| 2/0                      | .447" (11.35 mm)        | 6 x 1                           | Quail        | 1656-30, 1656-30H & S1656-30H                                  |                                    | 1628-16PG*                          |                                     |
| 3/0                      | .502" (12.75 mm)        | 6 x 1                           | Pigeon       | 1656-30, 1656-30H & S1656-30H                                  |                                    | 1628-16PH*                          |                                     |
| 4/0                      | .563" (14.30 mm)        | 6 x 1                           | Penguin      |                                                                | 1656-40, 1656-40H<br>& S1656-40H   | 1628-16PI*                          |                                     |
| 266.8 MCM                | .609" (15.47 mm)        | 18 x 1                          | Waxwing      |                                                                | 1656-40, 1656-40H &<br>S1656-40H   | 1628-16PJ*                          |                                     |
| 266.8 MCM                | .642" (16.31 mm)        | 26 x 7                          | Partridge    |                                                                | 1656-40, 1656-40H &<br>S1656-40H   | 1628-16PK*                          |                                     |
| 300 MCM                  | .680" (17.27 mm)        | 26 x 7                          | Ostrich      |                                                                | 1656-40, 1656-40H &<br>S1656-40H   | 1628-16PK*                          |                                     |
| 336.4 MCM                | .684" (17.37 mm)        | 18 x 1                          | Merlin       |                                                                | 1656-40, 1656-40H &<br>S1656-40H   | 1628-16PK*                          |                                     |
| 336.4 MCM                | .720" (18.31 mm)        | 26 x 7                          | Linnet       |                                                                | 1656-40, 1656-40H &<br>S1656-40H   | 1628-16PL*                          |                                     |
| 336.4 MCM                | .741" (18.82 mm)        | 30 x 7                          | Oriole       |                                                                | 1656-50, 1656-50H<br>& S1656-50H   | 1628-16PL*                          |                                     |
| 397.5 MCM                | .743" (18.87 mm)        | 18 x 1                          | Chickadee    |                                                                | 1656-50, 1656-50H<br>& S1656-50H   | 1628-16PL*                          |                                     |
| 397.5 MCM                | .772" (19.61 mm)        | 24 x 7                          | Brant        |                                                                | 1656-50, 1656-50H<br>& S1656-50H   | 1628-16PM*                          |                                     |
| 397.5 MCM                | .783" (19.89 mm)        | 26 x 7                          | Ibis         |                                                                | 1656-50, 1656-50H &<br>S1656-50H   | 1628-16PM*                          |                                     |
| 397.5 MCM                | .806" (20.47 mm)        | 30 x 7                          | Lark         |                                                                | 1656-50, 1656-50H &<br>S1656-50H   | 1628-16PM*                          |                                     |
| 477 MCM                  | .814" (20.68 mm)        | 18 x 1                          | Pelican      |                                                                | 1656-50, 1656-50H &<br>S1656-50H   | 1628-16PM*                          |                                     |
| 477 MCM                  | .846" (21.49 mm)        | 24 x 7                          | Flicker      |                                                                | 1656-50, 1656-50H &<br>S1656-50H   | 1628-16PN*                          | 1628-30N*                           |
| 477 MCM                  | .858" (21.79 mm)        | 26 x 7                          | Hawk         |                                                                | 1656-50, 1656-50H &<br>S1656-50H   | 1628-16PN*                          | 1628-30N*                           |
| 477 MCM                  | .883" (22.43 mm)        | 30 x 7                          | Hen          |                                                                | 1656-60, 1656-60H &<br>S1656-60H   | 1628-16PN*                          | 1628-30N*                           |
| 556.5 MCM                | .879" (22.33 mm)        | 18 x 1                          | Osprey       |                                                                | 1656-60, 1656-60H &<br>S1656-60H   | 1628-16PN*                          | 1628-30N*                           |
| 556.5 MCM                | .914" (23.22 mm)        | 24 x 7                          | Parakeet     |                                                                | 1656-60, 1656-60H and<br>S1656-60H |                                     | 1628-300*                           |
| 556.5 MCM                | .927" (23.55 mm)        | 26 x 7                          | Dove         |                                                                | 1656-60, 1656-60H &<br>S1656-60H   |                                     | 1628-300*                           |
| 556.5 MCM                | .953" (24.21 mm)        | 30 x 7                          | Eagle        |                                                                | 1656-60, 1656-60H &<br>S1656-60H   |                                     | 1628-300*                           |
| 605 MCM                  | .953" (24.21 mm)        | 24 x 7                          | Peacock      |                                                                | 1656-60, 1656-60H &<br>S1656-60H   |                                     | 1628-300*                           |
| 636 MCM                  | .940" (23.88 mm)        | 18 x 1                          | Kingbird     |                                                                | 1656-60, 1656-60H &<br>S1656-60H   |                                     | 1628-300*                           |

"S" is for spring. "H" is for hot latch.

\*Special order only. Please allow 30 days for delivery. These are not returnable.

For grip details  
See pages 281 and 282.

## ACSR (Aluminum Conductor Steel Reinforced)


For Cable Diameter  
**605 - 2515 MCM**  
**.966" - 1.88" (24.54 mm - 47.75 mm)**

### MAXIMUM SAFE LOAD

|                   |                         |                                 |              | <b>D</b><br>20,000 lbs<br>(9,072 kg) | <b>E</b><br>25,000 lbs<br>(11,340 kg) | <b>F</b><br>25,000 lbs.<br>with bolt on jaw<br>(11,340 kg) |
|-------------------|-------------------------|---------------------------------|--------------|--------------------------------------|---------------------------------------|------------------------------------------------------------|
| MCM<br>Cable Size | Diameter<br>inches (mm) | No. of Alum. &<br>Steel Strands | Code<br>Word | Cat. No.                             | Cat. No.                              | Cat. No.                                                   |
| 605 MCM           | .966" (24.54 mm)        | 26 x 7                          | Squab        | 1628-30P*                            |                                       | 1628-50P*                                                  |
| 605 MCM           | .994" (25.25 mm)        | 30 x 19                         | Teal         | 1628-30P*                            |                                       | 1628-50P*                                                  |
| 605 MCM           | .994" (25.25 mm)        | 30 x 7                          | Wood Duck    | 1628-30P*                            |                                       | 1628-50P*                                                  |
| 636 MCM           | .940" (23.88 mm)        | 18 x 1                          | Kingbird     | 1628-30U*                            |                                       | 1628-50P*                                                  |
| 636 MCM           | .977" (24.82 mm)        | 24 x 7                          | Rook         | 1628-30P*                            |                                       | 1628-50P*                                                  |
| 636 MCM           | 1.019" (25.88 mm)       | 30 x 19                         | Egret        | 1628-30R*                            |                                       | 1628-50R*                                                  |
| 636 MCM           | 1.019" (25.88 mm)       | 30 x 7                          | Scoter       | 1628-30R*                            |                                       | 1628-50R*                                                  |
| 636 MCM           | .991" (25.15 mm)        | 26 x 7                          | Grosbeak     | 1628-30P*                            |                                       | 1628-50P*                                                  |
| 666.6 MCM         | 1.00" (25.40 mm)        | 24 x 7                          | Flamingo     | 1628-30P*                            |                                       | 1628-50P*                                                  |
| 666.6 MCM         | 1.014" (25.76 mm)       | 26 x 7                          | Gannet       | 1628-30P*                            |                                       | 1628-50P*                                                  |
| 715.5 MCM         | 1.051" (26.70 mm)       | 26 x 7                          | Starling     | 1628-30R*                            |                                       | 1628-50R*                                                  |
| 715.5 MCM         | 1.081" (27.46 mm)       | 30 x 19                         | Redwing      | 1628-30S*                            |                                       | 1628-50S*                                                  |
| 795 MCM           | 1.040" (26.41 mm)       | 36 x 1                          | Coot         | 1628-30R*                            |                                       | 1628-50R*                                                  |
| 795 MCM           | 1.063" (27.00 mm)       | 45 x 7                          | Tern         | 1628-30R*                            |                                       | 1628-50R*                                                  |
| 795 MCM           | 1.092" (27.76 mm)       | 54 x 7                          | Condor       | 1628-30S*                            |                                       | 1628-50S*                                                  |
| 795.0 MCM         | 1.092" (27.74 mm)       | 24 x 7                          | Cuckoo       | 1628-30S*                            |                                       | 1628-50S*                                                  |
| 795 MCM           | 1.107" (28.14 mm)       | 26 x 7                          | Drake        | 1628-30S*                            |                                       | 1628-50S*                                                  |
| 795 MCM           | 1.140" (28.96 mm)       | 30 x 19                         | Mallard      | 1628-30S*                            |                                       | 1628-50S*                                                  |
| 900 MCM           | 1.131" (28.73 mm)       | 45 x 7                          | Ruddy        | 1628-30S*                            |                                       | 1628-50S*                                                  |
| 900 MCM           | 1.162" (29.51 mm)       | 54 x 7                          | Canary       | 1628-30T*                            |                                       | 1628-50T*                                                  |
| 954 MCM           | 1.165" (29.59 mm)       | 20 x 7                          | Corncrake    | 1628-30T*                            |                                       | 1628-50T*                                                  |
| 954 MCM           | 1.165" (29.59 mm)       | 45 x 7                          | Rail         | 1628-30T*                            |                                       | 1628-50T*                                                  |
| 954 MCM           | 1.175" (29.85 mm)       | 48 x 7                          | Towhee       | 1628-30T*                            |                                       | 1628-50T*                                                  |
| 954 MCM           | 1.196" (30.38 mm)       | 54 x 7                          | Cardinal     | 1628-30T*                            |                                       | 1628-50T*                                                  |
| 954 MCM           | 1.196" (30.38 mm)       | 24 x 7                          | Redbird      | 1628-30T*                            |                                       | 1628-50T*                                                  |
| 1033.5 MCM        | 1.212" (30.81 mm)       | 45 x 7                          | Ortolan      | 1628-30U*                            | 1628-40U*                             | 1628-50U*                                                  |
| 1033.5 MCM        | 1.245" (31.65 mm)       | 54 x 7                          | Curlew       | 1628-30U*                            | 1628-40U*                             | 1628-50U*                                                  |
| 1113 MCM          | 1.258" (31.95 mm)       | 45 x 7                          | Bluejay      | 1628-30U*                            | 1628-40U*                             | 1628-50U*                                                  |
| 1113 MCM          | 1.292" (32.84 mm)       | 54 x 19                         | Finch        |                                      | 1628-40W*                             | 1628-50W*                                                  |
| 1192.5 MCM        | 1.302" (33.07 mm)       | 45 x 7                          | Bunting      |                                      | 1628-40W*                             | 1628-50W*                                                  |
| 1192.5 MCM        | 1.337" (33.99 mm)       | 54 x 19                         | Grackle      |                                      | 1628-40X*                             | 1628-50X*                                                  |
| 1272 MCM          | 1.317" (33.45 mm)       | 36 x 1                          | Skylark      |                                      | 1628-40W*                             | 1628-50W*                                                  |
| 1272 MCM          | 1.345" (34.16 mm)       | 45 x 7                          | Bittern      |                                      | 1628-40X*                             | 1628-50X*                                                  |
| 1272 MCM          | 1.381" (35.10 mm)       | 54 x 19                         | Pheasant     |                                      | 1628-40X*                             | 1628-50X*                                                  |
| 1351.5 MCM        | 1.386" (35.20 mm)       | 45 x 7                          | Dipper       |                                      | 1628-40X*                             | 1628-50X*                                                  |
| 1351.5 MCM        | 1.424" (36.17 mm)       | 54 x 19                         | Martin       |                                      | 1628-40Y*                             | 1628-50Y*                                                  |
| 1431 MCM          | 1.427" (36.25 mm)       | 45 x 7                          | Bobolink     |                                      | 1628-40Y*                             | 1628-50Y*                                                  |
| 1431 MCM          | 1.465" (37.21 mm)       | 54 x 19                         | Plover       |                                      | 1628-40Z*                             | 1628-50Z*                                                  |
| 1590 MCM          | 1.504" (38.15 mm)       | 45 x 7                          | Lapwing      |                                      | 1628-40Z*                             | 1628-50Z*                                                  |
| 1590 MCM          | 1.544" (39.24 mm)       | 54 x 19                         | Falcon       |                                      | 1628-40A*                             | 1628-50A*                                                  |
| 1780 MCM          | 1.602" (40.69 mm)       | 84 x 19                         | Chukar       |                                      |                                       | 1628-50B*                                                  |
| 2034.5 MCM        | 1.681" (42.70 mm)       | 72 x 7                          | Mockingbird  |                                      |                                       | 1628-50C*                                                  |
| 2156 MCM          | 1.762" (44.75 mm)       | 84 x 19                         | Bluebird     |                                      |                                       | 1628-50D*                                                  |
| 2167 MCM          | 1.735" (44.12 mm)       | 72 x 7                          | Kiwi         |                                      |                                       | 1628-50D*                                                  |
| 2312 MCM          | 1.802" (45.77 mm)       | 76 x 19                         | Thrasher     |                                      |                                       | 1628-50E*                                                  |
| 2515 MCM          | 1.88" (47.75 mm)        | 76 x 19                         | Joree        |                                      |                                       | 1628-50F*                                                  |

\*Special order only. Please allow 30 days for delivery. These are not returnable.

For grip details  
 See pages 281 and 282.



## ACSS (Aluminum Conductor Steel Supported)

For Cable Diameter

**605 - 2515 MCM**

**.966" - 1.88" (24.54 mm - 47.75 mm)**

**MAXIMUM SAFE LOAD**

**F**

**25,000 lbs.**  
(11,340 kg)  
with bolt on jaw

| MCM Cable Size | Diameter inches (mm) | No. of Alum. & Steel Strands | Code Word        | Cat. No.  |
|----------------|----------------------|------------------------------|------------------|-----------|
| 605 MCM        | .966" (24.54 mm)     | 26 x 7                       | Squab/ACSS       | 1628-50P* |
| 605 MCM        | .994" (25.25 mm)     | 30 x 7                       | Wood Duck/ACSS   | 1628-50P* |
| 605 MCM        | .994" (25.25 mm)     | 30 x 19                      | Teal/ACSS        | 1628-50P* |
| 636 MCM        | .977" (24.82 mm)     | 24 x 7                       | Rook/ACSS        | 1628-50P* |
| 636 MCM        | .991" (25.15 mm)     | 26 x 7                       | Grosbeak/ACSS    | 1628-50P* |
| 636 MCM        | 1.019" (25.88 mm)    | 30 x 19                      | Egret/ACSS       | 1628-50R* |
| 636 MCM        | 1.019" (25.88 mm)    | 30 x 7                       | Scoter/ACSS      | 1628-50R* |
| 666.6 MCM      | 1.00" (25.40 mm)     | 24 x 7                       | Flamingo/ACSS    | 1628-50P* |
| 666.6 MCM      | 1.014" (25.76 mm)    | 26 x 7                       | Gannet/ACSS      | 1628-50P* |
| 715.5 MCM      | 1.081" (27.46 mm)    | 30 x 19                      | Redwing/ACSS     | 1628-50S* |
| 715.5 MCM      | 1.051" (26.70 mm)    | 26 x 7                       | Starling/ACSS    | 1628-50R* |
| 795 MCM        | 1.063" (27.00 mm)    | 45 x 7                       | Tern/ACSS        | 1628-50R* |
| 795 MCM        | 1.092" (27.74 mm)    | 24 x 7                       | Cuckoo/ACSS      | 1628-50S* |
| 795 MCM        | 1.092" (27.76 mm)    | 54 x 7                       | Condor/ACSS      | 1628-50S* |
| 795 MCM        | 1.139" (28.93 mm)    | 30 x 19                      | Mallard/ACSS     | 1628-50S* |
| 795 MCM        | 1.107" (28.14 mm)    | 26 x 7                       | Drake/ACSS       | 1628-50S* |
| 900 MCM        | 1.131" (28.73 mm)    | 45 x 7                       | Ruddy/ACSS       | 1628-50S* |
| 900 MCM        | 1.162" (29.51 mm)    | 54 x 7                       | Canary/ACSS      | 1628-50T* |
| 954 MCM        | 1.165" (29.59 mm)    | 20 x 7                       | Corncrake/ACSS   | 1628-50T* |
| 954 MCM        | 1.165" (29.59 mm)    | 45 x 7                       | Rail/ACSS        | 1628-50T* |
| 954 MCM        | 1.175" (29.85 mm)    | 48 x 7                       | Towhee/ACSS      | 1628-50T* |
| 954 MCM        | 1.196" (30.38 mm)    | 54 x 7                       | Cardinal/ACSS    | 1628-50T* |
| 954 MCM        | 1.196" (30.38 mm)    | 24 x 7                       | Redbird/ACSS     | 1628-50T* |
| 954 MCM        | 1.248" (31.70 mm)    | 30 x 19                      | Canvasback/ACSS  | 1628-50U* |
| 1033.5 MCM     | 1.212" (30.81 mm)    | 45 x 7                       | Ortolan/ACSS     | 1628-50U* |
| 1033.5 MCM     | 1.245" (31.65 mm)    | 54 x 7                       | Curlew/ACSS      | 1628-50U* |
| 1113 MCM       | 1.258" (31.95 mm)    | 45 x 7                       | Bluejay/ACSS     | 1628-50U* |
| 1113 MCM       | 1.292" (32.84 mm)    | 54 x 19                      | Finch/ACSS       | 1628-50W* |
| 1192.5 MCM     | 1.302" (33.07 mm)    | 45 x 7                       | Bunting/ACSS     | 1628-50W* |
| 1192.5 MCM     | 1.337" (33.99 mm)    | 54 x 19                      | Grackle/ACSS     | 1628-50X* |
| 1272 MCM       | 1.345" (34.16 mm)    | 45 x 7                       | Bittern/ACSS     | 1628-50X* |
| 1272 MCM       | 1.381" (35.10 mm)    | 54 x 19                      | Pheasant/ACSS    | 1628-50X* |
| 1351.5 MCM     | 1.386" (35.20 mm)    | 45 x 7                       | Dipper/ACSS      | 1628-50X* |
| 1351.5 MCM     | 1.424" (36.17 mm)    | 54 x 19                      | Martin/ACSS      | 1628-50Y* |
| 1431 MCM       | 1.427" (36.25 mm)    | 45 x 7                       | Bobolink/ACSS    | 1628-50Y* |
| 1431 MCM       | 1.465" (37.21 mm)    | 54 x 19                      | Plover/ACSS      | 1628-50Z* |
| 1590 MCM       | 1.504" (38.15 mm)    | 45 x 7                       | Lapwing/ACSS     | 1628-50Z* |
| 1590 MCM       | 1.544" (39.24 mm)    | 54 x 19                      | Falcon/ACSS      | 1628-50A* |
| 1780 MCM       | 1.602" (40.69 mm)    | 84 x 19                      | Chukar/ACSS      | 1628-50B* |
| 2034.5 MCM     | 1.681" (42.70 mm)    | 72 x 7                       | Mockingbird/ACSS | 1628-50C* |
| 2167 MCM       | 1.735" (44.12 mm)    | 72 x 7                       | Kiwi/ACSS        | 1628-50D* |
| 2156 MCM       | 1.762" (44.75 mm)    | 84 x 19                      | Bluebird/ACSS    | 1628-50D* |
| 2312 MCM       | 1.802" (45.77 mm)    | 76 x 19                      | Thrasher/ACSS    | 1628-50E* |
| 2515 MCM       | 1.88" (47.75 mm)     | 76 x 19                      | Joree/ACSS       | 1628-50F* |

Special order only.  
Please allow 30 days for delivery. These are not returnable.

For grip details  
See pages 281 and 282.

## ACSS/TW (Aluminum Conductor Steel Supported/Trapezoidal Wire)

For Cable Diameter

**795 - 2627.3 MCM**

**.960" - 1.762" (24.38 mm - 44.75 mm)**

### MAXIMUM SAFE LOAD

**F**


**25,000 lbs.**  
(11,340 kg)  
with bolt on jaw

| MCM Cable Size | Diameter inches (mm) | No. of Alum. & Steel Strands | Code Word           | Cat. No   |
|----------------|----------------------|------------------------------|---------------------|-----------|
| 762.8 MCM      | .990" (25.15 mm)     | 20 x 7                       | Wabash/ACSS/TW      | 1628-50P* |
| 768.2 MCM      | .977" (24.82 mm)     | 20 x 7                       | Maumee/ACSS/TW      | 1628-50P* |
| 795 MCM        | .960" (24.38 mm)     | 17 x 7                       | Tern/ACSS/TW        | 1628-50P* |
| 795 MCM        | .980" (24.89 mm)     | 18 x 7                       | Puffin/ACSS/TW      | 1628-50P* |
| 795 MCM        | .993" (25.22 mm)     | 20 x 7                       | Condor/ACSS/TW      | 1628-50P* |
| 795 MCM        | 1.010" (25.65 mm)    | 20 x 7                       | Drake/ACSS/TW       | 1628-50P* |
| 946.7 MCM      | 1.077" (27.36 mm)    | 35 x 7                       | Fraser/ACSS/TW      | 1628-50R* |
| 954.0 MCM      | 1.044" (26.52 mm)    | 30 x 7                       | Phoenix/ACSS/TW     | 1628-50R* |
| 954.0 MCM      | 1.061" (26.94 mm)    | 32 x 7                       | Rail/ACSS/TW        | 1628-50R* |
| 954.0 MCM      | 1.080" (27.43 mm)    | 20 x 7                       | Cardinal/ACSS/TW    | 1628-50S* |
| 957.2 MCM      | 1.060" (26.92 mm)    | 32 x 7                       | Kettle/ACSS/TW      | 1628-50R* |
| 959.6 MCM      | 1.110" (28.19 mm)    | 22 x 7                       | Suwannee/ACSS/TW    | 1628-50S* |
| 966.2 MCM      | 1.092" (27.73 mm)    | 21 x 7                       | Columbia/ACSS/TW    | 1628-50S* |
| 1033.5 MCM     | 1.089" (27.66 mm)    | 30 x 7                       | Snowbird/ACSS/TW    | 1628-50S* |
| 1033.5 MCM     | 1.102" (27.99 mm)    | 32 x 7                       | Ortolan/ACSS/TW     | 1628-50S* |
| 1033.5 MCM     | 1.132" (28.75 mm)    | 22 x 7                       | Curlew/ACSS/TW      | 1628-50S* |
| 1113.0 MCM     | 1.129" (28.68 mm)    | 30 x 7                       | Avocet/ACSS/TW      | 1628-50S* |
| 1113.0 MCM     | 1.185" (30.10 mm)    | 38 x 19                      | Finch/ACSS/TW       | 1628-50T* |
| 1113.0 MCM     | 1.143" (29.03 mm)    | 33 x 7                       | Bluejay/ACSS/TW     | 1628-50T* |
| 1158 MCM       | 1.165" (29.59 mm)    | 34 x 7                       | Genesee/ACSS/TW     | 1628-50T* |
| 1158.4 MCM     | 1.196" (30.38 mm)    | 24 x 7                       | Hudson/ACSS/TW      | 1628-50T* |
| 1168.1 MCM     | 1.155" (29.34 mm)    | 30 x 7                       | Cheyenne/ACSS/TW    | 1628-50T* |
| 1192.5 MCM     | 1.170" (29.72 mm)    | 30 x 7                       | Oxbird/ACSS/TW      | 1628-50T* |
| 1192.5 MCM     | 1.181" (29.99 mm)    | 34 x 7                       | Bunting/ACSS/TW     | 1628-50T* |
| 1192.5 MCM     | 1.225" (31.12 mm)    | 38 x 19                      | Grackle/ACSS/TW     | 1628-50U* |
| 1233.6 MCM     | 1.245" (31.62 mm)    | 38 x 19                      | Yukon/ACSS/TW       | 1628-50U* |
| 1257.1 MCM     | 1.213" (30.81 mm)    | 35 x 7                       | Nelson/ACSS/TW      | 1628-50U* |
| 1272 MCM       | 1.203" (30.56 mm)    | 30 x 7                       | Scissortail/ACSS/TW | 1628-50T* |
| 1272 MCM       | 1.203" (30.56 mm)    | 30 x 7                       | Catawba/ACSS/TW     | 1628-50T* |
| 1272 MCM       | 1.264" (32.11 mm)    | 39 x 19                      | Pheasant/ACSS/TW    | 1628-50U* |
| 1272 MCM       | 1.220" (30.99 mm)    | 38 x 7                       | Bittern/ACSS/TW     | 1628-50U* |
| 1334.6 MCM     | 1.290" (32.77 mm)    | 39 x 19                      | Thames/ACSS/TW      | 1628-50W* |
| 1351.5 MCM     | 1.300" (33.02 mm)    | 42 x 19                      | Martin/ACSS/TW      | 1628-50W* |
| 1351.5 MCM     | 1.256" (31.90 mm)    | 35 x 7                       | Dipper/ACSS/TW      | 1628-50U* |
| 1359.7 MCM     | 1.259" (31.98 mm)    | 36 x 7                       | Mackenzie/ACSS/TW   | 1628-50W* |
| 1372.5 MCM     | 1.248" (31.70 mm)    | 30 x 7                       | Truckee/ACSS/TW     | 1628-50U* |
| 1431 MCM       | 1.291" (32.79 mm)    | 36 x 7                       | Bobolink/ACSS/TW    | 1628-50W* |
| 1431 MCM       | 1.337" (33.96 mm)    | 44 x 19                      | Plover/ACSS/TW      | 1628-50X* |
| 1433.6 MCM     | 1.340" (34.04 mm)    | 39 x 19                      | Merrimack/ACSS/TW   | 1628-50X* |
| 1455.3 MCM     | 1.302" (33.07 mm)    | 36 x 7                       | Miramichi/ACSS/TW   | 1628-50W* |
| 1467.8 MCM     | 1.292" (32.82 mm)    | 33 x 7                       | St. Croix/ACSS/TW   | 1628-50W* |
| 1533.3 MCM     | 1.380" (35.05 mm)    | 38 x 19                      | Rio Grande/ACSS/TW  | 1628-50X* |
| 1557.4 MCM     | 1.350" (34.29 mm)    | 36 x 7                       | Potomac/ACSS/TW     | 1628-50X* |
| 1569 MCM       | 1.334" (33.88 mm)    | 33 x 7                       | Platte/ACSS/TW      | 1628-50X* |
| 1590 MCM       | 1.358" (34.49 mm)    | 36 x 7                       | Lapwing/ACSS/TW     | 1628-50X* |
| 1590 MCM       | 1.410" (35.81 mm)    | 42 x 19                      | Falcon/ACSS/TW      | 1628-50Y* |
| 1657.4 MCM     | 1.386" (35.20 mm)    | 36 x 7                       | Schuylkill/ACSS/TW  | 1628-50X* |
| 1622 MCM       | 1.420" (36.07 mm)    | 39 x 19                      | Pecos/ACSS/TW       | 1628-50Y* |
| 1730.6 MCM     | 1.470" (37.34 mm)    | 34 x 19                      | James/ACSS/TW       | 1628-50Z* |
| 1758.6 MCM     | 1.427" (36.25 mm)    | 38 x 7                       | Pee Dee/ACSS/TW     | 1628-50Y* |
| 1780 MCM       | 1.445" (36.70 mm)    | 38 x 19                      | Chukar/ACSS/TW      | 1628-50Y* |
| 1949.6 MCM     | 1.504" (38.20 mm)    | 44 x 7                       | Athabaska/ASCC/TW   | 1628-50Z* |
| 1926.9 MCM     | 1.550" (39.37 mm)    | 42 x 19                      | Cumberland/ACSS/TW  | 1628-50A* |
| 2153.8 MCM     | 1.602" (40.69 mm)    | 64 x 19                      | Powder/ACSS/TW      | 1628-50B* |
| 2156 MCM       | 1.608" (40.84 mm)    | 64 x 19                      | Bluebird/ACSS/TW    | 1628-50B* |
| 2627.3 MCM     | 1.761" (44.73 mm)    | 64 x 19                      | Santee/ACSS/TW      | 1628-50D* |

Special order only. Application must be confirmed prior to ordering. Please allow 30 days for delivery

For grip details see pages 281 and 282.





## AAC (All Aluminum Conductor)

For Cable Diameter

**4 AWG - 650 MCM**

**.231" - .928" (5.87 mm - 23.57 mm)**

### MAXIMUM SAFE LOAD

| AWG or MCM<br>Cable Size | Diameter<br>inches (mm) | No. of Alum.<br>Strands | Code<br>Word | MAXIMUM SAFE LOAD                                             |                                    |                                     |                                     |
|--------------------------|-------------------------|-------------------------|--------------|---------------------------------------------------------------|------------------------------------|-------------------------------------|-------------------------------------|
|                          |                         |                         |              | <b>A</b><br>4,500 lbs<br>(2041 kg)                            | <b>B</b><br>8,000 lbs<br>(3629 kg) | <b>C</b><br>15,000 lbs<br>(6803 kg) | <b>D</b><br>20,000 lbs<br>(9072 kg) |
|                          |                         |                         |              | Cat. No.                                                      | Cat. No.                           | Cat. No.                            | Cat. No.                            |
| 4                        | .231" (5.87 mm)         | 7                       | Rose         | 1656-20, 1656-20H and S1656-20H                               |                                    |                                     |                                     |
| 2                        | .292" (7.42 mm)         | 7                       | Iris         | 1656-20, 1656-20H and S1656-20H                               |                                    |                                     |                                     |
| 1                        | .328" (8.33 mm)         | 7                       | Pansy        | 1656-20, 1656-20H, S1656-20H, 1656-30, 1656-30H and S1656-30H |                                    |                                     |                                     |
| 1/0                      | .369" (9.36 mm)         | 7                       | Poppy        | 1656-20, 1656-20H, S1656-20H, 1656-30, 1656-30H and S1656-30H |                                    |                                     |                                     |
| 2/0                      | .414" (10.51 mm)        | 7                       | Aster        | 1656-30, 1656-30H and S1656-30H                               |                                    |                                     |                                     |
| 3/0                      | .465" (11.81 mm)        | 7                       | Phlox        | 1656-30, 1656-30H and S1656-30H                               |                                    |                                     |                                     |
| 4/0                      | .522" (13.25 mm)        | 7                       | Oxlip        | 1656-30, 1656-30H and S1656-30H                               |                                    |                                     |                                     |
| 250 MCM                  | .567" (14.40 mm)        | 7                       | Sneezewort   |                                                               | 1656-40, 1656-40H and S1656-40H    | 1628-16PI*                          |                                     |
| 250 MCM                  | .574" (14.58 mm)        | 19                      | Valerian     |                                                               | 1656-40, 1656-40H and S1656-40H    | 1628-16PI*                          |                                     |
| 266.8 MCM                | .586" (14.88 mm)        | 7                       | Daisy        |                                                               | 1656-40, 1656-40H and S1656-40H    | 1628-16PJ*                          |                                     |
| 266.8 MCM                | .593" (15.05 mm)        | 19                      | Laurel       |                                                               | 1656-40, 1656-40H and S1656-40H    | 1628-16PJ*                          |                                     |
| 300 MCM                  | .628" (15.95 mm)        | 19                      | Peony        |                                                               | 1656-40, 1656-40H and S1656-40H    | 1628-16PJ*                          |                                     |
| 336.4 MCM                | .665" (16.90 mm)        | 19                      | Tulip        |                                                               | 1656-40, 1656-40H and S1656-40H    | 1628-16PK*                          |                                     |
| 350 MCM                  | .678" (17.22 mm)        | 19                      | Daffodil     |                                                               | 1656-40, 1656-40H and S1656-40H    | 1628-16PK*                          |                                     |
| 397.5 MCM                | .724" (18.38 mm)        | 19                      | Canna        |                                                               | 1656-40, 1656-40H and S1656-40H    | 1628-16PL*                          |                                     |
| 450 MCM                  | .769" (19.53 mm)        | 19                      | Goldentuft   |                                                               | 1656-50, 1656-50H and S1656-50H    | 1628-16PM*                          |                                     |
| 477 MCM                  | .792" (20.12 mm)        | 19                      | Cosmos       |                                                               |                                    | 1628-16PM*                          |                                     |
| 477 MCM                  | .794" (20.18 mm)        | 37                      | Syringa      |                                                               |                                    | 1628-16PM*                          |                                     |
| 500 MCM                  | .811" (20.60 mm)        | 19                      | Zinnia       |                                                               |                                    | 1628-16PM*                          |                                     |
| 500 MCM                  | .813" (20.65 mm)        | 37                      | Hyacinth     |                                                               |                                    | 1628-16PM*                          |                                     |
| 556.5 MCM                | .856" (21.73 mm)        | 19                      | Dahlia       |                                                               |                                    | 1628-16PN*                          | 1628-30N*                           |
| 556.5 MCM                | .858" (21.80 mm)        | 37                      | Mistletoe    |                                                               |                                    | 1628-16PN*                          | 1628-30N*                           |
| 600 MCM                  | .891" (22.63 mm)        | 37                      | Meadowsweet  |                                                               |                                    |                                     | 1628-300*                           |
| 636 MCM                  | .918" (23.31 mm)        | 37                      | Orchid       |                                                               |                                    |                                     | 1628-300*                           |
| 650 MCM                  | .928" (23.57 mm)        | 37                      | Heuchera     |                                                               |                                    |                                     | 1628-300*                           |

"S" is for spring. "H" is for hot latch.

\*Special order only. Please allow 30 days for delivery. These are not returnable.

For grip details  
See pages 281 and 282.

## AAC (All Aluminum Conductor)

For Cable Diameter

**700 - 2500 MCM**

**.963" - 1.823" (24.46 mm - 46.30 mm)**


### MAXIMUM SAFE LOAD

| MCM<br>Cable Size | Diameter<br>inches (mm) | No. of Alum. &<br>Steel Strands | Code<br>Word | <b>D</b>                 | <b>E</b>                  | <b>F</b>                                       |
|-------------------|-------------------------|---------------------------------|--------------|--------------------------|---------------------------|------------------------------------------------|
|                   |                         |                                 |              | 20,000 lbs<br>(9,072 kg) | 25,000 lbs<br>(11,340 kg) | 25,000 lbs.<br>(11,340 kg)<br>with bolt on jaw |
|                   |                         |                                 |              | Cat. No.                 | Cat. No.                  | Cat. No.                                       |
| 700 MCM           | .963" (24.46 mm)        | 37                              | Verbena      | 1628-30P*                |                           | 1628-50P*                                      |
| 700 MCM           | .964" (24.49 mm)        | 61                              | Flag         | 1628-30P*                |                           | 1628-50P*                                      |
| 715.5 MCM         | .974" (24.73 mm)        | 37                              | Violet       | 1628-30P*                |                           | 1628-50P*                                      |
| 715.5 MCM         | .975" (24.76 mm)        | 61                              | Nasturtium   | 1628-30P*                |                           | 1628-50P*                                      |
| 750 MCM           | .997" (25.32 mm)        | 37                              | Petunia      | 1628-30P*                |                           | 1628-50P*                                      |
| 750 MCM           | .998" (25.35 mm)        | 61                              | Cattail      | 1628-30P*                |                           | 1628-50P*                                      |
| 795 MCM           | 1.026" (26.07 mm)       | 37                              | Arbutus      | 1628-30R*                |                           | 1628-50R*                                      |
| 795 MCM           | 1.028" (26.11 mm)       | 61                              | Lilac        | 1628-30R*                |                           | 1628-50R*                                      |
| 800 MCM           | 1.029" (26.14 mm)       | 37                              | Fuchsia      | 1628-30R*                |                           | 1628-50R*                                      |
| 800 MCM           | 1.031" (26.19 mm)       | 61                              | Heliotrope   | 1628-30R*                |                           | 1628-50R*                                      |
| 874.5 MCM         | 1.076" (27.37 mm)       | 37                              | Anemone      | 1628-30R*                |                           | 1628-50R*                                      |
| 874.5 MCM         | 1.077" (27.36 mm)       | 61                              | Crocus       | 1628-30R*                |                           | 1628-50R*                                      |
| 900 MCM           | 1.092" (27.74 mm)       | 37                              | Cockscomb    | 1628-30S*                |                           | 1628-50S*                                      |
| 954 MCM           | 1.124" (28.55 mm)       | 37                              | Magnolia     | 1628-30S*                |                           | 1628-50S*                                      |
| 954 MCM           | 1.126" (28.60 mm)       | 61                              | Goldenrod    | 1628-30S*                |                           | 1628-50S*                                      |
| 1000 MCM          | 1.152" (29.26 mm)       | 61                              | Camellia     | 1628-30T*                |                           | 1628-50T                                       |
| 1000 MCM          | 1.152" (29.26 mm)       | 37                              | Hawkweed     | 1628-30T*                |                           | 1628-50T*                                      |
| 1033.5 MCM        | 1.170" (29.71 mm)       | 37                              | Bluebell     | 1628-30T*                |                           | 1628-50T*                                      |
| 1033.5 MCM        | 1.172" (29.76 mm)       | 61                              | Larkspur     | 1628-30T*                |                           | 1628-50T*                                      |
| 1113 MCM          | 1.216" (30.88 mm)       | 61                              | Marigold     | 1628-30U*                | 1628-40U*                 | 1628-50U*                                      |
| 1192.5 MCM        | 1.258" (31.96 mm)       | 61                              | Hawthorn     | 1628-30U*                | 1628-40U*                 | 1628-50U*                                      |
| 1272 MCM          | 1.297" (32.94 mm)       | 61                              | Narcissus    |                          | 1628-40W*                 | 1628-50W*                                      |
| 1351.5 MCM        | 1.339" (34.02 mm)       | 61                              | Columbine    |                          | 1628-40X*                 | 1628-50X*                                      |
| 1431 MCM          | 1.379" (35.02 mm)       | 61                              | Carnation    |                          | 1628-40X*                 | 1628-50X*                                      |
| 1510.5 MCM        | 1.417" (35.98 mm)       | 61                              | Gladolus     |                          | 1628-40Y*                 | 1628-50Y*                                      |
| 1590 MCM          | 1.454" (36.93 mm)       | 61                              | Coreopsis    |                          | 1628-40Z*                 | 1628-50Z*                                      |
| 1750 MCM          | 1.524" (38.72 mm)       | 61                              | Jessamine    |                          | 1628-40A*                 | 1628-50A*                                      |
| 2000 MCM          | 1.630" (41.41 mm)       | 91                              | Cowslip      |                          |                           | 1628-50B*                                      |
| 2250 MCM          | 1.729" (43.92 mm)       | 91                              | Sagebrush    |                          |                           | 1628-50D*                                      |
| 2500 MCM          | 1.823" (46.30 mm)       | 91                              | Lupine       |                          |                           | 1628-50E*                                      |

**Maximum safe stringing tension 12,500 lbs to minimize cable deformation.**

\* Special order. Please allow 30 days for delivery. These are not returnable.

For grip details  
See pages 281 and 282.




## Chicago™ Grips

### 1656 Series

- Round, smooth inside jaw contour on this series of grips is ideal for bare ACSR
- Smooth jawed grips with maximum contact are less likely to cause cable deformation



1656-30



1656-40

#### A 4,500 lbs. (2,041 kg) Maximum Safe Load

| Cat. No. | Hot Latch Model No. | Hot Latch/Spring Model No. | Cable Diameter                    | Jaw Length        | Weight             |
|----------|---------------------|----------------------------|-----------------------------------|-------------------|--------------------|
| 1656-20  | 1656-20H            | S1656-20H                  | 0.20" to 0.40" (5.08 to 10.16 mm) | 4" (101.6 mm)     | 3.0 lbs. (1.36 kg) |
| 1656-30  | 1656-30H            | S1656-30H                  | 0.31" to 0.53" (7.87 to 13.46 mm) | 4-3/4" (120.7 mm) | 3.8 lbs. (1.70 kg) |

#### B 8,000 lbs. (3,629 kg) Maximum Safe Load

| Cat. No. | Hot Latch Model No. | Hot Latch/Spring Model No. | Cable Diameter                        | Jaw Length        | Weight             |
|----------|---------------------|----------------------------|---------------------------------------|-------------------|--------------------|
| 1656-40  | 1656-40H            | S1656-40H                  | 0.53" to 0.74" (13.46 mm to 18.80 mm) | 5-1/2" (139.7 mm) | 8.3 lbs. (3.76 kg) |
| 1656-50  | 1656-50H            | S1656-50H                  | 0.74" to 0.86" (18.80 to 21.84 mm)    | 5-1/2" (139.7 mm) | 8.3 lbs. (3.76 kg) |
| 1656-60  | 1656-60H            | S1656-60H                  | 0.86" to 0.96" (21.84 to 24.38 mm)    | 5-1/2" (139.7 mm) | 8.3 lbs. (3.76 kg) |

### 1628-16P and 1628-30 Series

- Round jaws are shaped to provide maximum contact with the cable, virtually eliminating cable deformation
- Designed for large-diameter ACSR cables
- These grips are special order only; please allow 30 days for delivery; special order grips are not returnable

#### C 15,000 lbs. (6,803 kg) Maximum Safe Load

| Cat. No.   | Cable Diameter Range                | Jaw Length         | Weight              |
|------------|-------------------------------------|--------------------|---------------------|
| 162816PE   | 0.31" to 0.33" (7.87 to 8.38 mm)    | 7-1/4" (184.15 mm) | 17.0 lbs. (7.73 kg) |
| 162816PF   | 0.33" to 0.39" (8.38 to 9.90 mm)    | 7-1/4" (184.15 mm) | 17.0 lbs. (7.73 kg) |
| 162816PG   | 0.40" to 0.45" (9.93 to 11.50 mm)   | 7-1/4" (184.15 mm) | 17.0 lbs. (7.73 kg) |
| 162816PH ‡ | 0.46" to 0.52" (11.53 to 13.08 mm)  | 7-1/4" (184.15 mm) | 17.0 lbs. (7.73 kg) |
| 162816PI   | 0.52" to 0.58" (13.11 to 14.68 mm)  | 7-1/4" (184.15 mm) | 17.0 lbs. (7.73 kg) |
| 162816PJ   | 0.58" to 0.64" (14.71 to 16.25 mm)  | 7-1/4" (184.15 mm) | 17.0 lbs. (7.73 kg) |
| 162816K    | 0.64" to 0.70" (16.28 to 17.86 mm)  | 7-1/4" (184.15 mm) | 17.0 lbs. (7.73 kg) |
| 162816PL   | 0.71" to 0.76" (17.89 mm -19.43 mm) | 7-1/4" (184.15 mm) | 17.0 lbs. (7.73 kg) |
| 162816PM   | 0.77" to 0.82" (19.46 to 21.03 mm)  | 7-1/4" (184.15 mm) | 17.0 lbs. (7.73 kg) |
| 162816PN   | 0.83" to 0.89" (21.06 to 22.61 mm)  | 7-1/4" (184.15 mm) | 17.0 lbs. (7.73 kg) |

‡ The "H" suffix does not mean Hot Latch, this is only for Cat. No. 1628-16PH.



1628-16P



1628-30

#### D 20,000 lbs. (9,072 kg) Maximum Safe Load

| Cat. No. | Cable Diameter Range               | Jaw Length          | Weight               |
|----------|------------------------------------|---------------------|----------------------|
| 162930N  | 0.83" to 0.89" (21.06 to 22.61 mm) | 10-3/4" (273.05 mm) | 27.0 lbs. (12.27 kg) |
| 1628300  | 0.89" to 0.96" (22.63 to 24.21 mm) | 10-3/4" (273.05 mm) | 27.0 lbs. (12.27 kg) |

## Chicago™ Grips

### 1628 Series

- Round jaws are shaped to provide maximum contact with the cable, virtually eliminating cable deformation
- These grips are special order only; please allow 30 days for delivery; special order grips are not returnable

#### D 20,000 lbs. (9,072 kg) Maximum Safe Load

| Cat. No. | Cable Diameter Range               | Jaw Length          | Weight               |
|----------|------------------------------------|---------------------|----------------------|
| 162830P  | 0.95" to 1.02" (24.23 to 25.78 mm) | 10-3/4" (273.05 mm) | 27.0 lbs. (12.27 kg) |
| 162830R  | 1.02" to 1.08" (25.81 to 27.38 mm) | 10-3/4" (273.05 mm) | 27.0 lbs. (12.27 kg) |
| 162830S  | 1.08" to 1.14" (27.41 to 28.96 mm) | 10-3/4" (273.05 mm) | 27.0 lbs. (12.27 kg) |
| 162830T  | 1.14" to 1.20" (28.95 to 30.55 mm) | 10-3/4" (273.05 mm) | 27.0 lbs. (12.27 kg) |
| 162830U  | 1.21" to 1.26" (30.7 to 32 mm)     | 10-3/4" (273.05 mm) | 27.0 lbs. (12.27 kg) |

#### E 25,000 lbs. (11,340 kg) Maximum Safe Load

| Cat. No. | Cable Diameter Range               | Jaw Length          | Weight               |
|----------|------------------------------------|---------------------|----------------------|
| 162840U  | 1.20" to 1.26" (30.48 to 32 mm)    | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162840W  | 1.27" to 1.32" (32.25 to 33.52 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162840X  | 1.33" to 1.39" (33.78 to 35.30 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162840Y  | 1.39" to 1.45" (35.30 to 36.83 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162840Z  | 1.45" to 1.52" (36.83 to 38.6 mm)  | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162840A  | 1.52" to 1.58" (38.6 to 40.13 mm)  | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |

#### F 25,000 lbs. (11,340 kg) Maximum Safe Load with bolt on jaw


| Cat. No. | Cable Diameter Range               | Jaw Length          | Weight               |
|----------|------------------------------------|---------------------|----------------------|
| 1628-50P | 0.95" to 1.02" (24.23 to 25.78 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 1628-50R | 13.9 oz. (394 g)                   | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162850S  | 1.08" to 1.14" (27.41 to 28.96 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162850T  | 1.14" to 1.20" (28.95 to 30.55 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162850U  | 1.20" to 1.27" (30.48 to 32.25 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162850W  | 1.27" to 1.33" (32.25 to 33.78 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162850X  | 1.33" to 1.39" (33.78 to 35.30 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162850Y  | 1.39" to 1.45" (35.30 to 36.83 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162850Z  | 1.45" to 1.52" (36.83 to 38.6 mm)  | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162850A  | 1.52" to 1.58" (38.6 to 40.13 mm)  | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162850B  | 1.58" to 1.64" (40.13 to 41.65 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162850C  | 1.64" to 1.70" (41.65 to 43.18 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162850D  | 1.70" to 1.77" (43.18 to 44.95 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162850E  | 1.77" to 1.83" (44.95 to 46.48 mm) | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |
| 162850F  | 1.83" to 1.89" (46.48 to 48 mm)    | 10-3/4" (273.05 mm) | 34.0 lbs. (15.45 kg) |



1628-30



1628-40



1628-50

- Removable bolt on floating jaw, secured by a slotted nut and cotter pin. Jaw provides increased cable coverage
- Cat. No. 555 replacement bolt available
- NOTE: Jaw must be removed to insert cable
- These grips are special order only; please allow 30 days for delivery; special order grips are not returnable



### Chicago™ Grip-Dual Conductor

- Designed specifically for VR2® (vibration-resistant) and TransPowr® T-2® dual conductor twisted pair cables
- Machined upper and lower jaws eliminate scoring or damage to second conductor
- Currently available in U size. Made to order. Please call Klein Tools for expected delivery dates. These are not returnable

#### E 25,000 lbs. (11,340 kg) Maximum Safe Load

| Cat. No.  | Cable Diameter Range             | Jaw Length         | Weight             |
|-----------|----------------------------------|--------------------|--------------------|
| 162840VRU | 1.20" to 1.27" (30.5 to 32.3 mm) | 10-3/4" (273.1 mm) | 34 lbs. (15.45 kg) |


VR2 is a registered trademark of Southwire Company.

TransPowr and T-2 are registered trademarks of General Cable Technologies Corporation.




1628-40VRU





## Chicago™ Grips

### Aircraft Cable, EHS (Extra-High-Strength), Messenger and Guy Strand-1613, 1628, 1684 and 1692 Series



1613-40




1684-5C

- Sawtooth jaw profile provides extra gripping power.




- Designed for cable sizes from 0.12" (3.10 mm) to 1" (25.4 mm)
- Double V grooves provide four-point contact, reducing chance of slipping and providing proper alignment of wire and cable.
- Cat. No. 1684-5F is a Single V with file insert.
- Cat. No. 16845C is Aggressive jaw profile
- Sawtooth jaw profile provides extra gripping power
- Replacement parts available: Screws (Cat. No. 573) and file (Cat. No. 578)



1684-74



Milled curved jaw



1684-5F



With file insert



Replacement parts available: Screws (Cat. No. 573) and file (Cat. No. 578).

| Cat. No.                                                      | Hot Latch Model No. | Hot Latch/Spring Model No. | Cable Diameter                      | Jaw Length         | Weight              |
|---------------------------------------------------------------|---------------------|----------------------------|-------------------------------------|--------------------|---------------------|
| <b>4,500 lbs. (2,041 kg) Maximum Safe Load</b>                |                     |                            |                                     |                    |                     |
| 1613-40                                                       | 1613-40H            | S1613-40H                  | 0.12" to 0.37" (3.05 to 9.40 mm)    | 4-3/16" (106.4 mm) | 3.0 lbs. (1.36 kg)  |
| <b>8,000 lbs. (3,629 kg) Maximum Safe Load</b>                |                     |                            |                                     |                    |                     |
| 1684-5F                                                       | —                   | —                          | 0.16" to 0.55" (4.06 to 13.97 mm)   | 5" (127.0 mm)      | 6.3 lbs. (2.86 kg)  |
| 1684-5                                                        | 1684-5H             | S1684-5H                   | 0.218" to 0.550" (5.54 to 13.97 mm) | 5" (127.0 mm)      | 6.3 lbs. (2.86 kg)  |
| 1692-5                                                        | —                   | —                          | 0.218" to 0.550" (5.54 to 13.97 mm) | 5" (127.0 mm)      | 6.4 lbs. (2.90 kg)  |
| <b>8,000 lbs. (3,629 kg) Maximum Safe Load – EHS Specific</b> |                     |                            |                                     |                    |                     |
| 1684-5C                                                       | —                   | —                          | 0.16" to 0.55" (4.06 to 13.97 mm)   | 5" (127.0 mm)      | 6.3 lbs. (2.86 kg)  |
| 1684-74                                                       | —                   | S1684-5H                   | 0.218" to 0.550" (5.54 to 13.97 mm) | 5" (127.0 mm)      | 6.3 lbs. (2.86 kg)  |
| <b>15,000 lbs. (6,803 kg) Maximum Safe Load</b>               |                     |                            |                                     |                    |                     |
| 1628-16                                                       | —                   | —                          | 0.31" to 0.62" (7.87 to 15.75 mm)   | 7-1/4" (184.2 mm)  | 15.3 lbs. (6.94 kg) |
| 1628-17                                                       | —                   | —                          | 0.50" to 0.75" (12.70 to 19.05 mm)  | 7-1/4" (184.2 mm)  | 16.3 lbs. (7.39 kg) |
| 1628-18                                                       | —                   | —                          | 0.75" to 1.0" (19.05 to 25.40 mm)   | 7-1/4" (184.2 mm)  | 15.7 lbs. (7.12 kg) |

### Weatherproof Stranded and Solid Cable -1611 Series

- Round inside jaw contour for weatherproof coated wire
- Notches in jaw provide firm grip on insulation

| Cat. No.                                       | Cable Diameter                     | Jaw Length          | Weight             |
|------------------------------------------------|------------------------------------|---------------------|--------------------|
| <b>4,500 lbs. (2,041 kg) Maximum Safe Load</b> |                                    |                     |                    |
| 1611-20                                        | 0.20" to 0.40" (5.08 to 10.16 mm)  | 4-3/16" (106.4 mm)  | 3.0 lbs. (1.36 kg) |
| 1611-30                                        | 0.31" to 0.53" (7.87 to 13.46 mm)  | 4-3/4" (120.7 mm)   | 3.8 lbs. (1.72 kg) |
| <b>8,000 lbs. (3,629 kg) Maximum Safe Load</b> |                                    |                     |                    |
| 1611-40                                        | 0.53" to 0.70" (13.46 to 17.78 mm) | 5-11/16" (144.5 mm) | 7.8 lbs. (3.54 kg) |
| 1611-50                                        | 0.74" to 0.86" (18.80 to 21.84 mm) | 5-11/16" (144.5 mm) | 7.8 lbs. (3.54 kg) |



1611-30




Notched Jaw

## Chicago™ Grips

### Bare Wire-1613 Series

- Designed for working with solid and stranded bare wire from 0.08" (2 mm) to 0.20" (5.1 mm)
- Lightweight, cost-effective grip
- Single "V" groove jaw
- Cat. Nos. 1613-35 and 1613-35H pulls #6 and #8 bare copper wire without damaging or deforming the cable




1613-30



1613-35



| Cat. No.                                       | Latch Model | Minimum Cable                    | Maximum Cable                   | Jaw Length         | Weight             |
|------------------------------------------------|-------------|----------------------------------|---------------------------------|--------------------|--------------------|
| <b>1,500 lbs. (680 kg) Maximum Safe Load</b>   |             |                                  |                                 |                    |                    |
| 1613-30                                        | —           | 12 B and S solid 0.08" (2.03 mm) | 4 B and S solid 0.20" (5.08 mm) | 3" (76.2 mm)       | 1.5 lbs. (0.68 kg) |
| <b>4,500 lbs. (2,041 kg) Maximum Safe Load</b> |             |                                  |                                 |                    |                    |
| 1613-35                                        | 1613-35H    | #8 AWG Bare Copper               | #6 AWG Bare Copper              | 4-3/16" (106.4 mm) | 6.0 lbs. (2.72 kg) |



1613-35 and 1613-35H pulls #6 and #8 bare copper wire

### PVC-Covered Cable -1659 Series

- Specially machined serpentine jaws allow insulated conductor to be inserted through jaws
- Eliminates necessity of stripping insulation from conductor
- Round inside-jaw contour



| Cat. No.                                       | Cable Diameter                     | Jaw Length          | Weight             |
|------------------------------------------------|------------------------------------|---------------------|--------------------|
| <b>4,500 lbs. (2,041 kg) Maximum Safe Load</b> |                                    |                     |                    |
| 1659-20                                        | 0.20" to 0.42" (5.08 to 10.67 mm)  | 4-3/16" (106.4 mm)  | 3.0 lbs. (1.36 kg) |
| 1659-30                                        | 0.31" to 0.50" (7.87 to 12.70 mm)  | 4-3/4" (120.7 mm)   | 3.8 lbs. (1.72 kg) |
| <b>8,000 lbs. (3,629 kg) Maximum Safe Load</b> |                                    |                     |                    |
| 1659-40                                        | 0.49" to 0.79" (12.45 to 20.07 mm) | 5-11/16" (144.5 mm) | 7.8 lbs. (3.54 kg) |
| 1659-50                                        | 0.79" to 1.01" (20.07 to 25.65 mm) | 5-11/16" (144.5 mm) | 7.8 lbs. (3.54 kg) |



1659-30



Serpentine Jaw

### Bell System B, L, and H-1628, 1659, 1684 & 1692 Series

- All are equipped with chain, toggle and shackle - keeps the grip from falling off of cable
- 1659-5AT is similar to Bell-System type "B" Strand Puller. Designed to pull 1/4" (6.35 mm) figure-8 telephone cable. Also has serpentine jaw




Serpentine Jaw

| Cat. No.                                        | Type              | Cable Diameter                      | Jaw Length        | Weight              |
|-------------------------------------------------|-------------------|-------------------------------------|-------------------|---------------------|
| <b>5,000 lbs. (2,268 kg) Maximum Safe Load</b>  |                   |                                     |                   |                     |
| 1659-5AT                                        | "B" Strand Puller | 0.20" to 0.37" (5.08 to 9.4 mm)     | 5" (127.0 mm)     | 6.7 lbs. (3.04 kg)  |
| <b>8,000 lbs. (3,629 kg) Maximum Safe Load</b>  |                   |                                     |                   |                     |
| 1684-5AT                                        | "L" Strand Puller | 0.218" to 0.550" (5.54 to 13.97 mm) | 5" (127.0 mm)     | 6.9 lbs. (3.13 kg)  |
| 1692-5AT                                        | "L" Strand Puller | 0.218" to 0.550" (5.54 to 13.97 mm) | 5" (127.0 mm)     | 6.6 lbs. (2.99 kg)  |
| <b>15,000 lbs. (6,803 kg) Maximum Safe Load</b> |                   |                                     |                   |                     |
| 1628-16AT                                       | "H" Strand Puller | 0.31" to 0.62" (7.87 to 15.75 mm)   | 7-1/4" (184.2 mm) | 15.8 lbs. (7.17 kg) |

\*1692-5AT (larger clamping force than 1684-5AT)




1659-5AT



## Steel Strand – Haven's™ Grips

### Messenger and Guy Strand - 1604 Series

- Designed for use when light, compact grip is desired and where cable deformation is not a factor
- Gripping pressure of the knurled jaw is applied to 1/4" (6.35 mm) cable area
- Latch on Cat. No. 1604-20L helps hold cable in the jaw



1604-20



1604-20L



| Cat. No.                                       | Latch Model | Cable Diameter                      | Weight             |
|------------------------------------------------|-------------|-------------------------------------|--------------------|
| <b>2,500 lbs. (1,134 kg) Maximum Safe Load</b> |             |                                     |                    |
| 1604-10                                        | —           | 0.06" to 0.25" (1.52 to 6.35 mm)    | 4.0 lbs. (1.81 kg) |
| <b>5,000 lbs. (2,268 kg) Maximum Safe Load</b> |             |                                     |                    |
| 1604-20                                        | 1604-20L    | 0.125" to 0.500" (3.18 to 12.70 mm) | 2.1 lbs. (0.95 kg) |



### Wire Rope-1625 Series

- Designed for use when light, compact grip is desired and where cable deformation is not a factor
- Gripping pressure of the knurled jaw is applied to 1/4" (6.35 mm) cable area
- All 1625 series have a swing latch to help hold cable in the jaw



| Cat. No.                                       | Cable Diameter                     | Weight             |
|------------------------------------------------|------------------------------------|--------------------|
| <b>8,000 lbs. (3,629 kg) Maximum Safe Load</b> |                                    |                    |
| 1625-20                                        | 0.28" to 0.75" (7.11 to 19.05 mm)  | 4.0 lbs. (1.81 kg) |
| 162520-7/8                                     | 0.38" to 0.88" (9.65 to 22.35 mm)  | 4.0 lbs. (1.81 kg) |
| 162520-1                                       | 0.50" to 1.00" (12.70 to 25.40 mm) | 4.0 lbs. (1.81 kg) |



1625-20

## Parallel Jaw Grips

### Parallel Jaw Grip - Hendrix® Tree Wire

- Securely pulls HDPE-coated cable commonly known as "tree wire"
- Innovative high-traction surface grips the cable without damaging the outer jacket
- Tough carbide grit technology withstands even the harshest jobsite conditions
- The only grip solution specifically designed for Hendrix® Aerial Cable
- Spring-loaded for one-handed operation and easy placement on the conductor
- Hendrix® is a registered trademark of Marmon Utility LLC



**NEW!**



1716-60

| Cat. No.                                        | Cable Diameter                     | Jaw Length        | Weight             |
|-------------------------------------------------|------------------------------------|-------------------|--------------------|
| <b>12,000 lbs. (5,443 kg) Maximum Safe Load</b> |                                    |                   |                    |
| 1716-60 <b>NEW!</b>                             | 0.70" to 1.30" (17.78 to 33.02 mm) | 5-1/8" (130.2 mm) | 8.1 lbs. (3.67 kg) |




## Parallel Jaw Grips

### KT4500, KT4600 and KT4800 Series



KT4500



KT4650


KT4602

- The KT4500, KT4600 and KT4800 Series feature a round serrated jaw
- KT4501, KT4502, KT4601, KT4602, KT4801, KT4802 are supplied with hot latches
- Hot latch closes automatically to guard against grip accidentally disengaging from wire
- Large opening in the handle to accommodate a wide variety of hooks on hoists, winches and tackle blocks

| Cat. No.                                        | Cable Diameter                     | Hot Latch | Spring | Locking Handle | Jaw Length        | Weight             |
|-------------------------------------------------|------------------------------------|-----------|--------|----------------|-------------------|--------------------|
| <b>5,000 lbs. (2,268 kg) Maximum Safe Load</b>  |                                    |           |        |                |                   |                    |
| KT4500                                          | 0.18" to 0.60" (4.57 to 15.20 mm)  |           | •      |                | 4" (101.6 mm)     | 3.8 lbs. (1.72 kg) |
| KT4501                                          | 0.18" to 0.60" (4.57 to 15.20 mm)  | •         | •      | •              | 4" (101.6 mm)     | 3.8 lbs. (1.72 kg) |
| KT4502                                          | 0.18" to 0.60" (4.57 to 15.20 mm)  | •         |        |                | 4" (101.6 mm)     | 3.8 lbs. (1.72 kg) |
| KT4650                                          | 0.16" to 0.90" (4.06 to 22.86 mm)  |           | •      |                | 4-1/2" (114.3 mm) | 4.9 lbs. (2.22 kg) |
| KT4652                                          | 0.16" (4 mm) to 0.9" (23 mm)       | •         | •      |                | 4-1/2" (114.3 mm) | 4.9 lbs. (2.22 kg) |
| <b>10,000 lbs. (4,536 kg) Maximum Safe Load</b> |                                    |           |        |                |                   |                    |
| KT4600                                          | 0.3" to 0.8" (7.62 to 20.3 mm)     |           | •      |                | 5" (127.0 mm)     | 7.0 lbs. (3.18 kg) |
| KT4601                                          | 0.3" to 0.8" (7.62 to 20.3 mm)     | •         | •      | •              | 5" (127.0 mm)     | 7.0 lbs. (3.18 kg) |
| KT4602                                          | 0.3" to 0.8" (7.62 to 20.3 mm)     | •         |        |                | 5" (127.0 mm)     | 7.0 lbs. (3.18 kg) |
| <b>12,000 lbs. (5,443 kg) Maximum Safe Load</b> |                                    |           |        |                |                   |                    |
| KT4800                                          | 0.70" to 1.25" (17.78 to 31.75 mm) |           | •      |                | 5-1/8" (130.2 mm) | 9.0 lbs. (4.08 kg) |
| KT4801                                          | 0.70" to 1.25" (17.78 to 31.75 mm) | •         | •      | •              | 5-1/8" (130.2 mm) | 9.0 lbs. (4.08 kg) |
| KT4802                                          | 0.70" to 1.25" (17.78 to 31.75 mm) | •         |        |                | 5-1/8" (130.2 mm) | 9.0 lbs. (4.08 kg) |

### Parallel Jaw Grips-1685

- Lightweight, compact grips pull an exceptionally wide range of cable types and sizes
- Designed with a round inside-jaw contour for maximum contact to minimize cable deformation
- Lower jaw is serrated to firmly grip insulated cables and conductors
- Design includes a latch that prevents the grip from falling in case of jaw disengagement from the cable
- Large-diameter eye accommodates large hooks on hoists, winches and tackle blocks




1685-20



1685-31

| Cat. No.                                       | Cable Diameter                       | Jaw Length        | Weight             |
|------------------------------------------------|--------------------------------------|-------------------|--------------------|
| <b>4,500 lbs. (2,041 kg) Maximum Safe Load</b> |                                      |                   |                    |
| 1685-20                                        | 0.157" to 0.875" (3.98 to 22.22 mm)  | 2-1/2" (63.5 mm)  | 3.0 lbs. (1.36 kg) |
| <b>7,500 lbs. (3,400 kg) Maximum Safe Load</b> |                                      |                   |                    |
| 1685-31                                        | 0.625" to 1.250" (15.87 to 31.75 mm) | 4-1/2" (114.3 mm) | 5.0 lbs. (2.27 kg) |





## Parallel Jaw Grips

### Parallel Jaw Grips-1686-10, 1686-20, 1671-10 and 1672-10

- Longer jaws achieve a firm hold, reducing potential deformation to cable
- Designed with a Double V jaw contour, a latch, plus a large-diameter eye that accommodates large hooks on hoists, winches, and tackle blocks
- When latch is closed, it helps maintain cable position in grip jaws
- Cat. Nos. 1686-20 and 1672-10 have knurled jaws

| Cat. No.                                        | Cable Diameter                    | Jaw Length        | Weight             |
|-------------------------------------------------|-----------------------------------|-------------------|--------------------|
| <b>10,000 lbs. (4,536 kg) Maximum Safe Load</b> |                                   |                   |                    |
| 1686-10                                         | 0.20" to 0.40" (5.08 to 10.16 mm) | 4-3/8" (111.1 mm) | 5.0 lbs. (2.27 kg) |
| 1686-20                                         | 0.20" to 0.40" (5.08 to 10.16 mm) | 4-3/8" (111.1 mm) | 5.0 lbs. (2.27 kg) |
| 1671-10                                         | 0.37" to 0.75" (9.40 to 19.05 mm) | 4-3/8" (111.1 mm) | 5.0 lbs. (2.27 kg) |
| 1672-10                                         | 0.37" to 0.75" (9.40 to 19.05 mm) | 4-3/8" (111.1 mm) | 5.0 lbs. (2.27 kg) |




1672-10

## Interchangeable Jaw Grips & Liners

### OPGW Conductors - 1628-80 Series - Grip

- Suitable for Optical Ground Wire (OPGW) conductors 0.236" to 0.906" (6 mm - 23 mm)
- Constructed of high strength alloy steel, hot forged, heat treated, and galvanized for toughness, strength and corrosion resistance
- Offers a full range of interchangeable liners to be inserted between the upper and lower jaws of the grip



1628-80

| Cat. No.                                       | Cable Diameter                      | Weight              |
|------------------------------------------------|-------------------------------------|---------------------|
| <b>6,750 lbs. (3,062 kg) Maximum Safe Load</b> |                                     |                     |
| 1628-80                                        | 0.236" to 0.906" (5.99 to 23.01 mm) | 15.0 lbs. (6.80 kg) |

### OPGW Conductors - 1628-80 Series - Grip Liners

- **Lower liner** - Polyurethane (provides cushioning for the optical cable) **Upper liner** - Aluminum
- Liners are made to order. Call Customer Service with details of cable diameter, cable type and working load requirements for availability and lead time



1628-80AA


| Cat. No.  | Cable Diameter                       | Weight           |
|-----------|--------------------------------------|------------------|
| 1628-80AA | 0.236" to 0.314" (6.00 to 7.97 mm)   | 16.0 oz. (454 g) |
| 1628-80BB | 0.315" to 0.353" (8.00 to 8.96 mm)   | 16.0 oz. (454 g) |
| 1628-80E  | 0.354" to 0.432" (8.99 to 10.97 mm)  | 10.4 oz. (295 g) |
| 1628-80F  | 0.433" to 0.511" (10.99 to 12.97 mm) | 10.4 oz. (295 g) |
| 1628-80G  | 0.512" to 0.750" (13.00 to 19.05 mm) | 7.2 oz. (204 g)  |
| 1628-80H  | 0.591" to 0.740" (15.01 to 18.79 mm) | 8.8 oz. (249 g)  |
| 1628-80I  | 0.670" to 0.747" (17.01 to 18.97 mm) | 8.0 oz. (227 g)  |
| 1628-80J  | 0.748" to 0.787" (19.00 to 20.00 mm) | 16.0 oz. (454 g) |
| 1628-80K  | 0.788" to 0.826" (20.02 to 21.00 mm) | 16.0 oz. (454 g) |
| 1628-80L  | 0.827" to 0.866" (21.01 to 22.00 mm) | 16.0 oz. (454 g) |

Call Klein Tools for expected delivery dates. These are not returnable.

## Accessories

### Grip-Cleaning Brush Set

- Set of four wire-bristle brushes designed for cleaning Klein wire and cable-pulling grips
- Brushes have stiff wire bristles
- Includes round and square shapes in both 12" and 14" (304.8 and 355.6 mm) lengths for efficient cleaning of different jaw configurations
- Semi-flexible steel shafts set into comfortable wooden handles provide the necessary reach into grip jaws



25450

| Cat. No. | Weight             |
|----------|--------------------|
| 25450    | 1.0 lbs. (0.45 kg) |


## Introduction – Wire Mesh Grips

Klein mesh pulling-grips are used for pulling overhead or underground cable, for stringing service or communication lines into buildings, for pulling wire through conduit, and for general underground construction.

Klein grips may be used for pulling bare or insulated wires, and wire rope. They install quickly and easily, and are designed to pass readily through ducts, conduit, blocks, and sheaves.

Klein grips are reusable and do not damage the cable because pulling tension remains uniform along the length of the grip. The mesh will fit either a single cable, or a bundle of cables.

Klein pulling grips are woven of galvanized steel – strong and long lasting.



### General Application Information

**KPJ** junior-duty series is used for small-job requirements where pulling tensions are low. Typical uses are to connect insulated building wire bundles to pulling tape, and pull through conduit.

**KPL** light duty grips are economical for applications such as industrial plant wiring and rewiring jobs, and in underground electrical construction where pulling tensions are low.

**KSRK** light-duty, slack-pulling grips are split mesh, single-weave design with rod closure for quick installation. Application areas similar to KSSK series, except mesh lengths are shorter and for lower pulling loads.

**KPM** medium-duty grips are flexible and easily handled; ideal for use where the exceptional strength of heavy-duty grips is not required.

**KSCK** medium-duty slack-pulling grips with closed double-weave mesh are used for final placement of underground cable where cable end is available, or for removing cable. Standard lengths are used in restricted space for short pulls. Where space is not restricted, longer lengths are used for higher pulling loads.


**KSSK** medium-duty slack-pulling grip applications are similar to the KSCK series except they are used where cable end is not available. Double-weave split mesh has lace closure.

**KP** heavy-duty grip series are recommended for underground installations.

**KPS** heavy-duty grip series are also recommended for underground installations. An additional feature of the KPS includes "rotating eye" to allow twists in the cable to spin out during slack periods.

### Prefix Letter Code

|             |                                                                                         |
|-------------|-----------------------------------------------------------------------------------------|
| <b>KPJ</b>  | Pulling, Junior-Duty, Closed-Mesh, Single-Weave, Light Duty, Flexible Eye               |
| <b>KPL</b>  | Pulling, Closed-Mesh, Single-Weave, Flexible Eye                                        |
| <b>KSRK</b> | Slack-Pulling, Light-Duty, Split-Mesh, Single-Weave, Rod Closure, Offset Flexible Eye   |
| <b>KPM</b>  | Pulling, Medium-Duty, Closed-Mesh, Double-Weave, Flexible Eye                           |
| <b>KSCK</b> | Slack-Pulling, Medium Duty, Closed-Mesh, Double-Weave, Offset Flexible Eye              |
| <b>KSSK</b> | Slack-Pulling, Medium Duty, Split-Mesh, Double-Weave, Lace Closure, Offset Flexible Eye |
| <b>KP</b>   | Pulling, Heavy-Duty, Closed-Mesh, Double-Weave, Flexible Eye                            |
| <b>KPS</b>  | Pulling, Heavy-Duty, with Rotating Eye, Closed-Mesh, Double-Weave                       |



### Catalog Number Explanation


| KPS                 | — | 050                  | — | 2                                                                     |
|---------------------|---|----------------------|---|-----------------------------------------------------------------------|
| Grip Type* and Mesh |   | Cat. No.** Size Code |   | Final Digit, if any, refers to mesh length range or actual dimension. |


\* See Prefix Letter Code explanation.

\*\* On Junior-duty grips, initial digit "0" is omitted in Cat. No.

### Example:

Cat. No. KPS-050-2 is a heavy-duty pulling grip with a rotating eye, for use with cable diameters from .50" to .61", with medium-length mesh.





## Introduction – Wire Mesh Grips

### How to select proper grip eye and mesh type

There are three basic styles of pulling grips, together with a choice of wire mesh types and lengths to meet a wide variety of pulling requirements.

### Design Strength


Applications and conditions of use for Klein mesh pulling grips vary so widely that it is impossible to set any meaningful standard for "breaking strength."

With wire-mesh pulling grips, the holding power achieved is directly related to the length of mesh. The longer the mesh, the firmer the grip on the cable. For smaller-diameter cable, or where the weight to be pulled is less, short mesh grips will serve the purpose.

### 1. Flexible Eye: Closed Mesh

#### KPJ/KPL/KPM/KP

This pulling-grip eye allows maximum flexibility to follow the line of pull, and is used when the end of the cable is available. Mesh selection depends on the weight of the material being pulled. Closed-mesh, single weave, flexible-eye grips are offered in lengths for junior-duty and light-duty use; closed-mesh, double-weave, flexible-eye grips are offered for medium-duty and heavy-duty use.



### 2. Rotating Eye: Closed Mesh

#### KPS

Recommended for heavier pulling jobs and underground wiring, this pulling grip eye is furnished on double-weave mesh grips in a wide range of lengths. The rotating eye compensates for pulling torque, relieving strain on the cable. **Rotating-eye grips should not be used on rope or as a swivel.**



### 3. Offset Flexible Eye: Split and Closed Mesh


#### KSRK/KSCK/KSSK

These slack-pulling grips come in three styles:

**KSRK** single-weave split-mesh with rod closure (light duty, where cable end is not available),

**KSCK** double-weave closed-mesh (for medium duty, where the end of the cable is available),

**KSSK** double-weave split-mesh with lace closure (medium duty, where cable end is not available).



## How grips are attached to cable

**Closed-mesh grips** simply slip over the cable where the cable end is accessible.

**Split-mesh grips** are used when the end of the cable is not available.

The grip is folded around the cable, and secured with a wire lace or steel rod (supplied with the grip) as follows:

#### 1. Split mesh with lace closure

Start at the lead end of the grip, threading the lace through the first two loops of the split, then pulling it through until ends are centered evenly. Cross the lace ends and thread through next two loops, and so on down the grip. Do not pull lacing too tight. Spacing of laced closure should be about the same as the mesh weave. When the end of the grip is reached, twist lacing strands tightly together; wrap ends of lace around grip, and twist again to secure. Excess may be cut off.

#### 2. Split mesh with rod closure

Simply wrap the grip around the cable, then thread the rod through the loops, using a cork-screw motion.

To remove, pull the rod out, and the grip is ready for re-use.

## Wire-Mesh Grips Warnings

**⚠ WARNING:** Grips are to be used for temporary installation, not for permanent anchorage.

**⚠ WARNING:** When used on/or near energized lines, ground, insulate, or isolate grip before pulling.

**⚠ WARNING:** Do not exceed rated capacity.

**⚠ WARNING:** Always match proper size and type of grip to application.

**⚠ WARNING:** Before each use, clean jaw area and inspect grip for proper operation to avoid slippage.

## Introduction – Wire Mesh Grips

### How to select the proper pulling grip for your application

1. Select the proper pulling-grip series (Prefix Letter Code...e.g. KPS) based on the "General Application Information" descriptions in the Wire-Mesh Grips Introduction on preceding pages.
2. Select grip size based on the outside diameter or circumference of the cable(s) to be pulled. Refer to reference tables (on this and following page) for convenience in determining cable diameters.
3. Use Pulling-Grip Selection Tables (on this and following page) to determine the "Size" portion of the Catalog Number for the cable diameter required. In the ordering tables (see following pages) this "Size" code is incorporated within the catalog number under the various grip-type classifications.

**Table 1**

**Pulling Grip Selection Table for One or More Cables of Equal Diameter to Be Pulled in One Grip**

1. Read across on top line for number of cables in one grip.
2. Read down for diameter of each cable.
3. Use Cat. No. size code to select catalog number of the required size grip.

**Example:**

3 Cables, each with diameter of 1.31" use grip with Cat. No. Size Code 250.

**Cable Diameters in Decimal Inches**

| 1 Cable   | 2 Cables  | 3 Cables  | 4 Cables  | 5 Cables  | 6 & 7 Cables | 8 Cables  | 9 Cables  | Cat. No. Size Code | Grip Diam. Range |
|-----------|-----------|-----------|-----------|-----------|--------------|-----------|-----------|--------------------|------------------|
| 0.50-0.62 | 0.27-0.36 | 0.26-0.33 | 0.24-0.28 | 0.21-0.25 | 0.19-0.22    | 0.17-0.20 | 0.15-0.19 | 050                | 0.50-0.62        |
| 0.62-0.75 | 0.36-0.45 | 0.33-0.36 | 0.28-0.31 | 0.25-0.29 | 0.22-0.26    | 0.20-0.23 | 0.19-0.22 | 062                | 0.62-0.75        |
| 0.75-1.00 | 0.45-0.60 | 0.36-0.49 | 0.31-0.42 | 0.29-0.38 | 0.26-0.34    | 0.23-0.31 | 0.22-0.31 | 075                | 0.75-1.00        |
| 1.00-1.25 | 0.60-0.76 | 0.49-0.63 | 0.42-0.54 | 0.38-0.48 | 0.34-0.43    | 0.31-0.39 | 0.29-0.36 | 100                | 1.00-1.25        |
| 1.25-1.50 | 0.76-0.91 | 0.63-0.76 | 0.54-0.65 | 0.48-0.58 | 0.43-0.52    | 0.39-0.46 | 0.36-0.43 | 125                | 1.25-1.50        |
| 1.50-1.75 | 0.91-1.08 | 0.76-0.89 | 0.65-0.77 | 0.58-0.67 | 0.52-0.60    | 0.46-0.54 | 0.43-0.49 | 150                | 1.50-1.75        |
| 2.00-2.50 | 1.23-1.54 | 1.02-1.28 | 0.88-1.10 | 0.77-0.96 | 0.69-0.86    | 0.62-0.77 | 0.57-0.72 | 200                | 2.00-2.50        |
| 2.50-3.00 | 1.54-1.84 | 1.28-1.53 | 1.10-1.32 | 0.96-1.16 | 0.86-1.03    | 0.77-0.93 | 0.72-0.86 | 250                | 2.50-3.00        |
| 3.00-3.50 | 1.84-2.15 | 1.53-1.79 | 1.32-1.54 | 1.16-1.35 | 1.03-1.20    | 0.93-1.08 | 0.86-1.00 | 300                | 3.00-3.50        |
| 3.50-4.00 | 2.15-2.45 | 1.79-2.05 | 1.54-1.76 | 1.35-1.54 | 1.20-1.37    | 1.08-1.24 | 1.00-1.14 | 350                | 3.50-4.00        |


**Table 2**

**Pulling-Grip Selection Table for Cables of Different Diameters to Be Pulled in One Grip**

| Grip Circumference Range |                | Cat. No. Size Code | Grip Diameter Range |                |
|--------------------------|----------------|--------------------|---------------------|----------------|
| Fractional Inches        | Decimal Inches |                    | Fractional Inches   | Decimal Inches |
| 1-37/64-1-15/16          | 1.57-1.94      | 062                | 1/2-5/8             | .50-.62        |
| 1-37/64-2-3/8            | 1.57-2.37      | 050                | 5/8-3/4             | .62-.75        |
| 2-3/8-3-5/32             | 2.37-3.15      | 075                | 3/4-1               | .75-1.00       |
| 3-5/32-3-15/16           | 3.15-3.94      | 100                | 1-1-1/4             | 1.00-1.25      |
| 3-15/16-4-23/32          | 3.94-4.72      | 125                | 1-1/4-1-1/2         | 1.25-1.50      |
| 4-23/32-5-33/64          | 4.72-5.51      | 150                | 1-1/2-1-3/4         | 1.50-1.75      |
| 6-19/64-7-55/64          | 6.29-7.86      | 200                | 2-2-1/2             | 2.00-2.50      |
| 7-55/64-9-7/16           | 7.86-9.43      | 250                | 2-1/2-3             | 2.50-3.00      |
| 9-7/16-11-1/64           | 9.43-11.01     | 300                | 3-3-1/2             | 3.00-3.50      |
| 11-1/64-12-37/64         | 11.01-12.58    | 350                | 3-1/2-4             | 3.50-4.00      |

"Grip Circumference Range" refers to circumference of all cables held together.

1. Measure the circumference of bundle of cables to be held.
2. Read down to locate correct range.
3. Read across for catalog number size code.



**Table 3**


**Reference Table: Dimension Conversions for Ordering Tables**

| Decimal Inches | Fractional Inches | Metric Dimensions (mm) |
|----------------|-------------------|------------------------|
| 0.12-0.24      | 1/8-15/64         | 3.17-5.95              |
| 0.25-0.36      | 1/4-23/64         | 6.35-9.13              |
| 0.37-0.49      | 3/8-31/64         | 9.52-12.30             |
| 0.50-0.61      | 1/2-39/64         | 12.70-15.48            |
| 0.62-0.74      | 5/8-47/64         | 15.88-18.65            |
| 0.75-0.99      | 3/4-63/64         | 19.05-25.00            |
| 1.00-1.24      | 1-1-15/64         | 25.40-31.35            |
| 1.25-1.49      | 1-1/4-1-31/64     | 31.75-37.70            |
| 1.50-1.99      | 1-1/2-1-63/64     | 38.10-50.40            |
| 2.00-2.49      | 2-2-31/64         | 50.80-63.10            |
| 2.50-2.99      | 2-1/2-2-63/64     | 63.50-75.80            |
| 3.00-3.49      | 3-3-31/64         | 76.20-88.50            |
| 3.50-3.99      | 3-1/2-3-63/64     | 88.90-101.20           |

**Example:**

For four cables together with circumference of 6.35", use grip containing catalog number size code "200".





## Wire Mesh Grips

### Single-Weave, Flexible-Eye Pulling Grips



KPJ-50

| Cat. No. | Cable Diameter                     | Loaded/Compressed Mesh Length | Maximum Safe Load   | Weight           |
|----------|------------------------------------|-------------------------------|---------------------|------------------|
| KPJ50    | 0.50" to 0.61" (12.70 to 15.59 mm) | 8-1/2" (215.9 mm)             | 260 lbs. (118 kg)   | 0.8 oz. (23.0 g) |
| KPJ75    | 0.75" to 0.99" (19.05 to 25.15 mm) | 10" (254.0 mm)                | 560 lbs. (254 kg)   | 1.6 oz. (45 g)   |
| KPJ100   | 1.00" to 1.24" (25.4 to 31.50 mm)  | 11-1/2" (292.1 mm)            | 780 lbs. (354 kg)   | 4.5 oz. (128 g)  |
| KPL125-1 | 1.25" to 1.49" (31.75 to 37.85 mm) | 14" (355.6 mm)                | 1060 lbs. (481 kg.) | 6.4 oz. (181 g)  |
| KPL150-1 | 1.50" to 1.74" (38.10 to 44.20 mm) | 15" (381.0 mm)                | 1360 lbs. (617 kg)  | 6.4 oz. (181 g)  |
| KPL200-1 | 2.00" to 2.49" (50.80 to 63.25 mm) | 18" (457.2 mm)                | 1700 lbs. (771 kg)  | 10.4 oz. (295 g) |

### Double-Weave, Flexible-Eye Pulling Grips



KPM-075

| Cat. No. | Cable Diameter                     | Loaded/Compressed Mesh Length | Maximum Safe Load   | Weight             |
|----------|------------------------------------|-------------------------------|---------------------|--------------------|
| KPM050   | 0.50" to 0.61" (12.70 to 15.59 mm) | 13" (330.2 mm)                | 480 lbs. (218 kg)   | 1.6 oz. (45 g)     |
| KPM075   | 0.75" to 0.99" (19.05 to 25.15 mm) | 16" (406.4 mm)                | 1030 lbs. (467 kg)  | 3.2 oz. (91 g)     |
| KPM100   | 1.00" to 1.37" (25.4 to 34.80 mm)  | 18" (457.2 mm)                | 1420 lbs. (644 kg)  | 6.4 oz. (181 g)    |
| KP075-24 | 0.75" to 0.99" (19.05 to 25.15 mm) | 24" (609.6 mm)                | 1360 lbs. (617 kg)  | 8.0 oz. (227 g)    |
| KP100-24 | 1.00" to 1.49" (25.4 to 37.85 mm)  | 24" (609.6 mm)                | 1920 lbs. (871 kg)  | 1.1 lbs. (0.50 kg) |
| KP075-36 | 0.75" to 0.99" (19.05 to 25.15 mm) | 36" (914.4 mm)                | 1360 lbs. (617 kg)  | 11.8 oz. (335 g)   |
| KP100-36 | 1.00" to 1.49" (25.4 to 37.85 mm)  | 36" (914.4 mm)                | 1920 lbs. (871 kg)  | 1.0 lbs. (0.45 kg) |
| KP150-36 | 1.50" to 1.99" (38.10 to 50.55 mm) | 36" (914.4 mm)                | 3280 lbs. (1488 kg) | 1.6 lbs. (0.73 kg) |

### Double-Weave, Rotating-Eye Pulling Grips



KPS-062-1

| Cat. No. | Cable Diameter                       | Loaded/Compressed Mesh Length | Maximum Safe Load   | Weight             |
|----------|--------------------------------------|-------------------------------|---------------------|--------------------|
| KPS050-2 | 0.50" to 0.61" (12.70 to 15.59 mm)   | 16" (406.4 mm)                | 1120 lbs. (508 kg)  | 7.2 oz. (204 g)    |
| KPS062-2 | 0.620" to 0.740" (15.74 to 18.79 mm) | 16" (406.4 mm)                | 1360 lbs. (617 kg)  | 8.0 oz. (227 g)    |
| KPS075-2 | 0.75" to 0.99" (19.05 to 25.15 mm)   | 20" (508.0 mm)                | 1360 lbs. (617 kg)  | 13.6 oz. (386 g)   |
| KPS100-2 | 1.00" to 1.24" (25.4 to 31.50 mm)    | 20" (508.0 mm)                | 2560 lbs. (1161 kg) | 1.9 lbs. (0.86 kg) |
| KPS125-2 | 1.25" to 1.49" (31.75 to 37.85 mm)   | 21" (533.4 mm)                | 2560 lbs. (1161 kg) | 1.9 lbs. (0.86 kg) |
| KPS150-2 | 1.50" to 1.99" (38.10 to 50.55 mm)   | 25" (635.0 mm)                | 3280 lbs. (1488 kg) | 2.2 lbs. (1.00 kg) |
| KPS200-2 | 2.00" to 2.49" (50.80 to 63.25 mm)   | 26" (660.4 mm)                | 5440 lbs. (2468 kg) | 4.1 lbs. (1.86 kg) |
| KPS250-2 | 2.50" to 2.99" (63.50 to 75.95 mm)   | 28" (711.2 mm)                | 6600 lbs. (2994 kg) | 5.3 lbs. (2.40 kg) |
| KPS300-2 | 3.00" to 3.49" (76.20 to 88.65 mm)   | 30" (762.0 mm)                | 8200 lbs. (3720 kg) | 6.1 lbs. (2.77 kg) |
| KPS350-2 | 3.5" to 3.99" (88.90 to 101.35 mm)   | 32" (812.8 mm)                | 9600 lbs. (4354 kg) | 6.8 lbs. (3.08 kg) |
| KPS100-3 | 1.00" to 1.49" (25.4 to 37.85 mm)    | 33" (838.2 mm)                | 3280 lbs. (1488 kg) | 2.4 lbs. (1.09 kg) |
| KPS150-3 | 1.50" to 1.99" (38.10 to 50.55 mm)   | 34" (863.6 mm)                | 3280 lbs. (1488 kg) | 2.5 lbs. (1.13 kg) |
| KPS200-3 | 2.00" to 2.49" (50.80 to 63.25 mm)   | 36" (914.4 mm)                | 5440 lbs. (2468 kg) | 4.7 lbs. (2.13 kg) |

### Slack-Pulling, Offset Flexible-Eye Pulling Grips



KSKC-100-1

| Cat. No.  | Cable Diameter                     | Loaded/Compressed Mesh Length | Maximum Safe Load | Weight          |
|-----------|------------------------------------|-------------------------------|-------------------|-----------------|
| KSKC100-1 | 1.00" to 1.24" (25.4 to 31.50 mm)  | 15" (381.0 mm)                | 800 lbs. (363 kg) | 8.0 oz. (227 g) |
| KSSK125-1 | 1.25" to 1.49" (31.75 to 37.85 mm) | 16" (406.4 mm)                | 800 lbs. (363 kg) | 4.0 oz. (113 g) |