




ROHS COMPLIANT		PRODUCT DATA DRAWING		REVISION HISTORY									
				REV	DESCRIPTION	DATE	APPROVED						
				01	PRELIMINARY	07/12	FED						
				-	DCN 39315	08/12	STW						
													
MATERIAL:													
BODY, INSERT HEX NUT & CLAMP NUT:		STAINLESS STEEL PER AMS-5640, ALLOY UNS S30300, TYPE 1											
CONTACTS:		BERYLLIUM COPPER PER ASTM B196, ALLOY No. UNS C17300, TD04											
FERRULE:		BRASS PER ASTM B16, ALLOY UNS No. C36000											
BEAD:		ULTEM 1000 PER ASTM D5205											
													
FINISH:													
BODY, INSERT HEX NUT & CLAMP NUT:		PASSIVATED PER AMS-2700											
CONTACTS & FERRULE:		GOLD PER ASTM B488, TYPE II, CODE C, CLASS 1.27, OVER NICKEL PER AMS-QQ-N-290, CLASS 1, .00005" MIN.											
PERFORMANCE:													
IMPEDANCE:		50 OHMS											
FREQ. RANGE:		DC TO 40.0 GHz											
VSWR:		1.20:1 DC TO 40.0 GHz											