



Home: Crimp Housings >

Part Number: 48106-0714

2.00mm Pitch, Wire-to-Board, 7 Circuits, Crimp Housing, Yellow

Image not available

Status:	OBSOLETE
Replacement:	Contact Molex
Series:	48106
Category:	Crimp Housings

Go to [Part Detail](#) ▾ [CHECK DISTRIBUTOR INVENTORY](#) [Add to My Parts](#) [Email this page](#)

Series image - Reference only

Mates With Part(s):
[48107](#), [48148](#)**Use With Part(s):**
[48105](#)**Application Tooling****FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)**Product Environmental Compliance**[EU ELV](#): Product not active[EU RoHS](#): Product not active[EU RoHS Phthalates](#): Product not active[China RoHS](#):[REACH SVHC](#): Product not active[Low-Halogen Status](#): Product not active

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements

EU RoHS, REACH SVHC, & Low-Halogen

Multiple Part Industry Compliance Documents

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail****COLLAPSE ALL****General**

Status	Obsolete
Category	Crimp Housings
Series	48106
Application	Signal
Product Name	N/A
UPC	822348539208

Physical

Circuits (maximum)	7
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-25°C to +85°C

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	2.0A
-------------------------------	------

Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number.

[Click here to visit the UL Database](#)

CSA	LR19980
UL	E29179

PRODUCTS**QUICK LINKS****RESOURCES****STAY CONNECTED**

Antennas

Company Information

Supply Chain Transparency

Application Tooling

Contact Molex

Business Continuity

Cable Assemblies

Cross-Reference

Compliance

Connected Lighting

Koch Industries

ecocare

Connectors

Industries

Feedback | Help

Copper Flex

Investor Relations

Jobs

Electrical Products

Literature

Legal | Trademarks

Industrial Automation

Molex Racing

Mobile Site

Membrane Switches

Press Room / Press Releases

Supplier Portal

Optical Solutions

Product Index

Privacy Policy

Printed Electronic Solutions

Sitemap

Tradeshows

Terms & Conditions



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2017