

D

C

B


A

D



C

B


A





SINGLE POLARIZATION



PANEL CUTOUT



DOUBLE POLARIZATION



CAVITY IDENTIFICATION WHEN VIEWED FROM REAR OF CONNECTOR

1. DWV RATING: 725VAC @ SEA LEVEL
2. WIRE SIZE: 28 AWG MAX
3. WORKING TEMPERATURE: -55°C ~ +125°C

4 MATERIAL:

CONTACT : COPPER ALLOY

SHELL : COPPER ALLOY

INSULATOR : PEEK

O RING : SILICON RUBBER

5 FINISH

CONTACT: GOLD OVER NICKEL

SHELL : BLACK CHROMIUM

6. WATER PROOF: 1M IMMERSION

7 PART IS MARKED WITH TE PART NUMBER, CHINA, DATE CODE AND LOT ID

8 ALL TOLERANCES +/-0.20 UNLESS NOTED.

5	CHROMIUM-BLACK	DOUBLE	SOLDER CUP	2101677-2
5	CHROMIUM-BLACK	SINGLE	SOLDER CUP	2101677-1
SHELL SIZE	FINISH	POLARIZATION	TERMINATION	TE CONNECTIVITY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS	03MAR2010	TE Connectivity	
DIMENSIONS: mm		CHK R. GROSS	03MAR2010	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. GROSS	03MAR2010	PRODUCT SPEC	
0 PLC ± -		108-127005		APPLICATION SPEC	
1 PLC ± -		SIZE		CAGE CODE	
2 PLC ± 0.20		WEIGHT		DRAWING NO	
3 PLC ± -		CUSTOMER DRAWING		RESTRICTED TO	
4 PLC ± -		SCALE		SHEET	
ANGLES ± °		NTS		1 OF 1	
FINISH		REV		C	