

## KBPC2500W - KBPC2510W

**PRV : 50 - 1000 Volts**

**Io : 25 Amperes**


### FEATURES :

- \* High current capability
- \* High surge current capability
- \* High reliability
- \* Low reverse current
- \* Low forward voltage drop
- \* **Pb / RoHS Free**

### MECHANICAL DATA :

- \* Case : Metal Case
- \* Epoxy : UL94V-O rate flame retardant
- \* Terminals : plated .25" (6.35 mm). Faston
- \* Polarity : Polarity symbols marked on case
- \* Mounting position : Bolt down on heat-sink with silicone thermal compound between bridge and mounting surface for maximum heat transfer efficiency.
- \* Weight : 15.95 grams (approximately)

## SILICON BRIDGE RECTIFIERS



## MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25 °C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%.


| RATING                                                                                                        | SYMBOL          | KBPC 2500W    | KBPC 2501W | KBPC 2502W | KBPC 2504W | KBPC 2506W | KBPC 2508W | KBPC 2510W | UNIT               |
|---------------------------------------------------------------------------------------------------------------|-----------------|---------------|------------|------------|------------|------------|------------|------------|--------------------|
| Maximum Recurrent Peak Reverse Voltage                                                                        | $V_{RRM}$       | 50            | 100        | 200        | 400        | 600        | 800        | 1000       | V                  |
| Maximum RMS Voltage                                                                                           | $V_{RMS}$       | 35            | 70         | 140        | 280        | 420        | 560        | 700        | V                  |
| Maximum DC Blocking Voltage                                                                                   | $V_{DC}$        | 50            | 100        | 200        | 400        | 600        | 800        | 1000       | V                  |
| Maximum Average Forward Current $T_c = 55^\circ\text{C}$                                                      | $I_{F(AV)}$     | 25            |            |            |            |            |            |            | A                  |
| Peak Forward Surge Current Single half sine wave Superimposed on rated load (JEDEC Method)                    | $I_{FSM}$       | 300           |            |            |            |            |            |            | A                  |
| Current Squared Time at $t < 8.3$ ms.                                                                         | $I^2 t$         | 375           |            |            |            |            |            |            | A <sup>2</sup> S   |
| Maximum Forward Voltage per Diode at $I_F = 12.5$ A                                                           | $V_F$           | 1.1           |            |            |            |            |            |            | V                  |
| Maximum DC Reverse Current $T_a = 25^\circ\text{C}$<br>at Rated DC Blocking Voltage $T_a = 100^\circ\text{C}$ | $I_R$           | 10            |            |            |            |            |            |            | $\mu\text{A}$      |
|                                                                                                               | $I_{R(H)}$      | 200           |            |            |            |            |            |            | $\mu\text{A}$      |
| Typical Thermal Resistance (Note 1)                                                                           | $R_{\theta JC}$ | 1.45          |            |            |            |            |            |            | $^\circ\text{C/W}$ |
| Operating Junction Temperature Range                                                                          | $T_J$           | - 40 to + 150 |            |            |            |            |            |            | $^\circ\text{C}$   |
| Storage Temperature Range                                                                                     | $T_{STG}$       | - 40 to + 150 |            |            |            |            |            |            | $^\circ\text{C}$   |

### Note :


1. Thermal Resistance from junction to case with units mounted on a 5" x 6" x 4.9" (12.8cm.x 15.2cm.x 12.4cm.) Al.-Finned Plate

## RATING AND CHARACTERISTIC CURVES (KBPC2500W - KBPC2510W)


**FIG.1 - DERATING CURVE FOR OUTPUT RECTIFIED CURRENT**



**FIG.2 - MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT**



**FIG.3 - TYPICAL FORWARD CHARACTERISTICS PER DIODE**



**FIG.4 - TYPICAL REVERSE CHARACTERISTICS PER DIODE**

