


## NPN SILICON PLANAR TRANSISTOR

CD9011  
TO-92  
CBE





### ABSOLUTE MAXIMUM RATINGS

DESCRIPTION	SYMBOL	VALUE	UNIT
Collector -Emitter Voltage	VCEO	30	V
Collector -Base Voltage	VCBO	50	V
Emitter Base Voltage	VEBO	5.0	V
Collector Current	IC	100	mA
Power Dissipation	PD	400	mW
Operating And Storage Junction	T <sub>j</sub> , T <sub>stg</sub>	-55 to +125	deg C
Temperature Range			

### ELECTRICAL CHARACTERISTICS (Ta=25 deg C Unless Otherwise Specified)

DESCRIPTION	SYMBOL	TEST CONDITION	MIN	TYP	MAX	UNIT
Collector -Emitter Voltage	VCEO	IC=10mA, IB=0	30	-	-	V
Collector -Base Voltage	VCBO	IC=100uA, IE=0	50	-	-	V
Emitter Base Voltage	VEBO	IE=10uA, IC=0	5.0	-	-	V
Collector Cut off Current	ICBO	VCB=18V, IE=0	-	-	50	nA
Emitter Cut off Current	IEBO	VEB=3V, IC=0	-	-	100	nA
DC Current Gain	hFE	IC=1mA, VCE=5V	29	-	273	
Collector Emitter Saturation Voltage	VCE(Sat)	IC=10mA, IB=1mA	-	-	0.30	V
Dynamic Characteristics						
Output Capacitance	C <sub>ob</sub>	VCB=10V, f=1MHz	-	-	3.5	pF
Transition Frequency	f <sub>t</sub>	VCE=10V, IC=10mA, f=100MHz	250	-	-	MHz
Noise Figure	NF	VCE=5V, IC=100uA f=1KHz	-	-	4.0	dB
hFE CLASSIFICATION	D 29-44, E 40-59, F 54-80, G 72-108, H 97-146, I 132-198, J 182-273					

## TO-92 Plastic Package




**PIN CONFIGURATION**

1. COLLECTOR
2. BASE
3. Emitter

All dimensions in mm.

DIM	MIN.	MAX.
A	4.32	5.33
B	4.45	5.20
C	3.18	4.19
D	0.41	0.55
E	0.35	0.50
F	5 DEG	
G	1.14	1.40
H	1.14	1.53
K	12.70	—

## TO-92 Transistors on Tape and Ammo Pack



All dimensions in mm unless specified otherwise

ITEM	SYMBOL	SPECIFICATION				REMARKS
		MIN.	NOM.	MAX.	TOL.	
BODY WIDTH	A1	4.0		4.8		
BODY HEIGHT	A	4.8		5.2		
BODY THICKNESS	T	3.9		4.2		
PITCH OF COMPONENT	P					
FEED HOLE PITCH	Po					
FEED HOLE CENTRE TO						
COMPONENT CENTRE	P2					
DISTANCE BETWEEN OUTER						
LEADS	F	5.08				
COMPONENT ALIGNMENT	△h	0		1		
TAPE WIDTH	W	18				
HOLD-DOWN TAPE WIDTH	Wo	6				
HOLE POSITION	W1	9				
HOLD-DOWN TAPE POSITION	W2	0.5				
LEAD WIRE CLINCH HEIGHT	Ho	16				
COMPONENT HEIGHT	H1			23.25		
LENGTH OF SNIPPED LEADS	L			11.0		
FEED HOLE DIAMETER	Do	4				
TOTAL TAPE THICKNESS	t			1.2		
LEAD - TO - LEAD DISTANCE	F1	2.54				
CLINCH HEIGHT	H2			3		
PULL - OUT FORCE	(P)	6N				

### NOTES

1. MAXIMUM ALIGNMENT DEVIATION BETWEEN LEADS NOT TO BE GREATER THAN 0.2 mm.
2. MAXIMUM NON-CUMULATIVE VARIATION BETWEEN TAPE FEED HOLES SHALL NOT EXCEED 1 mm IN 20 PITCHES.
3. HOLDDOWN TAPE NOT TO EXCEED BEYOND THE EDGE(S) OF CARRIER TAPE AND THERE SHALL BE NO EXPOSURE OF ADHESIVE.
4. NO MORE THAN 3 CONSECUTIVE MISSING COMPONENTS ARE PERMITTED.
5. A TAPE TRAILER, HAVING AT LEAST THREE FEED HOLES ARE REQUIRED AFTER THE LAST COMPONENT.
6. SPLICES SHALL NOT INTERFERE WITH THE SPROCKET FEED HOLES.

## Packing Detail

PACKAGE	STANDARD PACK		INNER CARTON BOX		OUTER CARTON BOX		
	Details	Net Weight/Qty	Size	Qty	Size	Qty	Gr Wt
TO-92 Bulk	1K/polybag	200 gm/1K pcs	3" x 7.5" x 7.5"	5.0K	17" x 15" x 13.5"	80.0K	23 kgs
TO-92 T&A	2K/ammo box	645 gm/2K pcs	12.5" x 8" x 1.8"	2.0K	17" x 15" x 13.5"	32.0K	12.5 kgs

