

Shrink sleeve - WMS 2,4 (EX4)RL BK - 0800427

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, Roll, black, unlabeled, can be labeled with: THERMOMARK W, THERMOMARK ROLL, THERMOMARK X, Unperforated, Mounting type: slide on, Cable diameter: 0.8-2.4 mm, Lettering field: 4 x 120000 mm

The figure shows the WMS 12,7 (Ex20)R BK version

Product Features

- ✓ Available in the form of continuous rolls and can be printed on both sides using the THERMOMARK W2 printer
- ✓ The shrink sleeves are automatically perforated or cut to the required length during the printing process
- ✓ MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- ✓ CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)
- ✓ UL 224 (125°C, 600 V, all tubing)
- ✓ Individual markers can be cut to any length up to 1 m

Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	2000.0 GRM
Custom tariff number	39173200
Country of origin	China

Technical data

Dimensions

Length (b)	120 m
Width (a)	4 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

General

Color	black
Base element material	polyolefine
Components	Halogen-free
Material	Polyolefine

Shrink sleeve - WMS 2,4 (EX4)RL BK - 0800427

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	slide on

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27400401
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530
ETIM 4.0	EC000217
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410