



RECOMMENDED PCB LAYOUT




CIRCUIT: 2PDT

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 0.1A @30V DC
5. MATERIALS:

CONTACT/TERMINAL: SILVER PLATED COPPER ALLOY
HOUSING/PLUNGER: UL94HB

6. CONTACT RESISTANCE: 0.1 MAX.
7. TIMING: NON-SHORTING (BBM)
8. OPERATING FORCE: 170±100g
9. TRAVEL: 2mm (TRAVEL TO LOCK)
3mm (OVERALL)
10. ELECTRICAL LIFE: >10,000
11. DIELECTRIC STRENGTH: 250V RMS



TITLE			
MTH2U EE N AGX (LATCHING)			
E-SWITCH®			
C	11999	REVISED AND REDRAWN	CJB
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE		DATE	DR
1.5:1		3/14/02	CJB
		DWG	REV
		A960002	C