



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		A	INITIAL RELEASE	26NOV2013	GSK	BvH
			A1	ECR—14—011671	20AUG2014	GSK	BvH

NOTES:
Tolerances cable lengths:
0m to 0.5m +30mm
0.5m to 1.0m +50mm
1.0m to 3.0m +100mm
< 3.0m +1.5%



PVC CABLE	
No./diameter of wires	4 x 0.34 mm²
Wire isolation	PVC (br, wh, bl, bk)
C—track properties	
Jacket	PVC (UL/CSA)
Outer diameter	approx. 5.0 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	−30...+80 °C
Temperature range (mobile)	−5...+80 °C



TECHNICAL DATA	
Operating voltage	max. 250 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self—securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)

PUR CABLE	
No./diameter of wires	4 x 0.34 mm²
Wire isolation	PP (br, wh, bl, bk)
C—track properties	5 million
Jacket	PUR (UL/CSA)
Outer diameter	approx. 4.7 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	−40...+80 °C
Temperature range (mobile)	−25...+80 °C

4 pos	10mtr	PVC	Black	1—2273082—4	4x22AWG PVC 10.0m	8
	5mtr			1—2273082—3	4x22AWG PVC 5.0m	7
	3mtr			1—2273082—2	4x22AWG PVC 3.0m	6
	1.5mtr			1—2273082—1	4x22AWG PVC 1.5m	5
4 pos	10mtr	PUR	Black	2273082—4	4x22AWG PUR 10.0m	4
	5mtr			2273082—3	4x22AWG PUR 5.0m	3
	3mtr			2273082—2	4x22AWG PUR 3.0m	2
	1.5mtr			2273082—1	4x22AWG PUR 1.5m	1
LENGTH”L”		MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± −
1 PLC	± −
2 PLC	± −
3 PLC	± −
4 PLC	± −
ANGLES	± −
FINISH	—

MATERIAL

—

DWN
SATHISH KUMAR .G
26NOV2013

CHK
B.VELDHOVEN
26NOV2013

APVD
A.VAN ZANDVOORT
26NOV2013

PRODUCT SPEC
108—19483

APPLICATION SPEC
114—32127

WEIGHT
—

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
A1

TE Connectivity

NAME
M12 X 1.0 ANGLED PLUG PIGT A

SIZE
A3

CAGE CODE
00779

DRAWING NO
C=2273082

RESTRICTED TO
—