


BZT55C- Series



Features:

- Zener voltage range 2.0 to 75 volts.
- Mini-MELF package.
- Surface device type mounting.
- Hermetically sealed glass.
- Compression Bonded Construction.
- All external surfaces are corrosion resistant and terminals are readily solderable.
- RoHS compliant.
- Matte Tin (Sn) lead finish.
- Blue color band indicates negative polarity.


Maximum Ratings and Electrical Characteristics

Type Number	Symbol	Value	Units
Power Dissipation	P_D	500	mW
Operating and Storage Temperature Range	T_J, T_{STG}	-65 to + 200	$^{\circ}\text{C}$


Notes : These ratings are limiting values above which the serviceability of the diode may be impaired.

Ratings and Characteristic Curves


Total Power Dissipation vs. Ambient Temperature




Temperature Coefficient of V_Z vs. Z-Voltage




Typical Change of Working Voltage under Operating Conditions at $T_{amb} = 25^{\circ}\text{C}$




Diode Capacitance vs. Z - Voltage




Typical Change of Working Voltage vs. Junction Temperature




Forward Current vs. Forward Voltage




Z-Current vs. Z-Voltage




Differential Z - Resistance vs. Z-Voltage



Z-Current vs. Z-Voltage



Thermal Response



Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

V _Z at I _{ZT} (Volts)		I _{ZT} mA	Z _{ZT} at I _{ZT} Ohms Maximum	I _{ZK} mA	Z _{ZK} at I _{ZK} Ohms	I _R at V _R uA Maximum	V _R V	Part Number		
V _Z Minimum (V)	V _Z Maximum (V)									
9.4	10.6	5	15	1.0	70	0.1	7.5	BZT55C10		
10.4	11.6		20				8.2	BZT55C11		
11.4	12.7				90		9.1	BZT55C12		
12.4	14.1		26		110		10	BZT55C13		
13.8	15.6		30				11	BZT55C15		
15.3	17.1		40		170		12	BZT55C16		
16.8	19.1		50				13	BZT55C18		
18.8	21.1		55		220		15	BZT55C20		
20.8	23.3						16	BZT55C22		
22.8	25.6		80				18	BZT55C24		
25.1	28.9	2		20		BZT55C27				
1.88	2.11	5	100	600	50	1.0	BZT55C2V0			
2.08	2.33						BZT55C2V2			
2.28	2.56		85		10		BZT55C2V4			
2.51	2.89				BZT55C2V7					
28	32	2	80	220	0.1	22	BZT55C30			
31	35					24	BZT55C33			
34	38		90			0.5	500	27	BZT55C36	
37	41							28	BZT55C39	
2.8	3.2	5	85	1.0	600	4	1.0	BZT55C3V0		
3.1	3.5					2		0.1	35	BZT55C3V3
3.4	3.8									BZT55C3V6
3.7	4.1									BZT55C3V9
40	46	2	90	0.5	700	0.1	35	BZT55C43		
44	50		110					BZT55C47		
4.0	4.6	5	75	1.0	600	2	1.0	BZT55C4V3		
4.4	5.0		60			0.5		BZT55C4V7		
48	54	2	125	0.5	700	0.1	38	BZT55C51		
52	60		135		1000		42	BZT55C56		
4.8	5.4	5	35	1.0	550		1.0	BZT55C5V1		
5.2	6.0		25		450			BZT55C5V6		
58	66	2.5	150	0.5	1000			47	BZT55C62	

Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

V _Z at I _{ZT} (Volts)		I _{ZT} mA	Z _{ZT} at I _{ZT} Ohms Maximum	I _{ZK} mA	Z _{ZK} at I _{ZK} Ohms	I _R at V _R uA Maximum	V _R V	Part Number
V _Z Minimum (V)	V _Z Maximum (V)							
64	72	2.5	160	0.5	1000	0.1	51	BZT55C68
5.8	6.6	5	10	1.0	200		2.0	BZT55C6V2
6.4	7.2		8		150		3.0	BZT55C6V8
70	80	2.5	170	0.5	1000		56	BZT55C75
7.0	7.9	5	7	1.0	50		5.0	BZT55C7V5
7.7	8.7						6.2	BZT55C8V2
8.5	9.6		10				6.8	BZT55C9V1

V_F Forward Voltage = 1.0v Maximum at $I_F = 100\text{mA}$ for all types.

- Notes :
1. The type numbers listed have zener voltage min/max limits as shown.
 2. The zener impedance is derived from the 60-cycle ac voltage, which results when an ac current having an rms value equal to 10% of the dc zener current (I_{ZT} or I_{ZK}) is superimposed to I_{ZT} or I_{ZK} .

BZT55C- Series



Notes:

International Sales Offices:

 AUSTRALIA - Farnell Tel No: ++61 1300 361 005 Fax No: ++61 1300 361 225	 FINLAND - Farnell Tel No: ++ 358 9 560 7780 Fax No: ++ 358 9 345 5411	 ITALY - Farnell Tel No: ++ 39 02 93 995 200 Fax No: ++ 39 02 93 995 300	 SPAIN - Farnell Tel No: 901 20 20 80 Fax No: 901 20 20 90
 AUSTRIA - Farnell Tel No: ++ 43 662 2180 680 Fax No: ++ 43 662 2180 670	 FRANCE - Farnell Tel No: ++ 33 474 68 99 99 Fax No: ++ 33 474 68 99 90	 MALAYSIA - Farnell-Newark Tel No: ++ 60 3 7873 8000 Fax No: ++ 60 3 7873 7000	 SWEDEN - Farnell Tel No: ++ 46 8 730 50 00 Fax No: ++ 46 8 83 52 62
 BELGIUM - Farnell Tel No: ++ 32 3 475 2810 Fax No: ++ 32 3 227 3648	 GERMANY - Farnell Tel No: ++ 49 89 61 39 39 39 Fax No: ++ 49 89 613 59 01	 NETHERLANDS - Farnell Tel No: ++ 31 30 241 7373 Fax No: ++ 31 30 241 7333	 SWITZERLAND - Farnell Tel No: ++ 44 204 64 64 Fax No: ++ 44 204 64 54
 BRAZIL - Farnell-Newark Tel No: ++ 55 11 4066 9400 Fax No: ++ 55 11 4066 9410	 HONG KONG - Farnell-Newark Tel No: ++ 852 2268 9888 Fax No: ++ 852 2268 9899	 NEW ZEALAND - Farnell Tel No: 0800 90 80 80 Fax No: 0800 90 80 81	 UK - Farnell Tel No: ++ 44 8701 200 200 Fax No: ++ 44 8701 200 201
 CHINA - Farnell-Newark Tel No: ++86 10 6238 5152 Fax No: ++86 10 6238 5022	 HUNGARY - Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209	 NORWAY - Farnell Tel No: 800 146 70 Fax No: 800 146 76	 UK - CPC ++ 44 8701 202 530 ++ 44 8701 202 531
 CZECH REPUBLIC - Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209	 INDIA - Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209	 PORTUGAL - Farnell Tel No: ++ 34 93 475 8804 Fax No: ++ 34 93 474 5288	 USA - Newark Tel No: 800 463 9275
 DENMARK - Farnell Tel No: ++ 45 44 53 66 44 Fax No: ++ 45 44 53 66 06	 IRELAND - Farnell Tel No: ++ 353 1 830 9277 Fax No: ++ 353 1 830 9016	 RUSSIA - Farnell Tel No: ++ 44 870 1200 208 Fax No: ++ 44 870 1200 209	 EXPORT - Farnell Tel No: ++ 44 8701 200 208 Fax No: ++ 44 8701 200 209 For enquiries from all other markets
 ESTONIA - Farnell Tel No: ++ 358 9 560 7780 Fax No: ++ 358 9 345 5411	 ISRAEL - Farnell Tel No: ++ 180 937 0015 Fax No: ++ 180 937 0014	 SINGAPORE - Farnell-Newark Tel No: ++ 65 6788 0200 Fax No: ++ 65 6788 0300	http://www.farnell.com http://www.newark.com http://www.cpc.co.uk

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC Multicomp is the registered trademark of the Group. © Premier Farnell plc 2008.

