







- ① HOUSING MATERIAL: GLASS-FILLED POLYMER.
- ② CONTACT MATERIAL: COPPER ALLOY.
- ③ CONTACT FINISH: DIN 41612 CLASS 2 IN CONTACT AREA.
TIN PLATE ON POSTS.
- ④ CONTACT POINT.
- ⑤ RECOMMENDED HOLE SIZE FOR MANUAL APPLICATION OF
CONNECTOR ONTO PC BOARD.
- ⑥ PART NUMBER, DATE CODE IDENTIFICATION, CSA LOGO IN
THIS APPROXIMATE AREA ON REVERSE SIDE.



3	1 THRU 32	X	—	X	64	5650408-5
3	1 THRU 32	X	—	X	64	5650408-4
FINISH	POSITIONS LOADED	C	B	A	NO. OF LOADED POSITION	ASSY PART NUMBER
		ROWS LOADED				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. <u>1. POLIGNONE</u>	27MAY05	 TE Connectivity
		CHK. <u>A. SHARPE</u>	27MAY05	
DIMENSIONS: mm. [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: APD. <u>A. SHARPE</u>		NAME ASSEMBLY, RECEPTACLE, EUROCARD, TYPE C, LEAD-FREE, A and C, 64/96 POSITION, 4.57[.180] SOLDER POSTS
		PRODUCT SPEC APPLICATION SPEC		
MATERIAL		WEIGHT	—	SIZE A1
		CUSTOMER DRAWING	—	CAGE CODE 00779
				DRAWING NO. 5650408
				SCALE 4:1
				SHEET 1 OF 1
				REV P