

## NTE2349 (NPN) & NTE2350 (PNP) Silicon Darlington Transistors High Current, General Purpose

### **Description:**

The NTE2349 (NPN) and NTE2350 (PNP) are silicon complementary Darlington transistors in a TO3 type package designed for use as output devices in general purpose amplifier applications.

### **Features:**

- High DC Current Gain:  $h_{FE} = 1000$  (Min) @  $I_C = 25A$   
 $h_{FE} = 400$  (Min) @  $I_C = 50A$
- Diode Protection to Rated  $I_C$
- Monolithic Construction <sup>w</sup>/Built-In Base-Emitter Shunt Resistor
- Junction Temperature to +200°C

### **Absolute Maximum Ratings:**

|                                                              |                |
|--------------------------------------------------------------|----------------|
| Collector-Emitter Voltage, $V_{CEO}$ .....                   | 120V           |
| Collector-Base Voltage, $V_{CB}$ .....                       | 120V           |
| Emitter-Base Voltage, $V_{EB}$ .....                         | 5V             |
| Collector Current, $I_C$                                     |                |
| Continuous .....                                             | 50A            |
| Peak .....                                                   | 100A           |
| Continuous Base Current, $I_B$ .....                         | 2A             |
| Total Power Dissipation ( $T_C = +25^\circ C$ ), $P_D$ ..... | 300W           |
| Derate Above 25°C @ $T_C = +100^\circ C$ .....               | 1.71W/°C       |
| Operating Junction Temperature Range, $T_J$ .....            | -55° to +200°C |
| Storage Temperature Range, $T_{stg}$ .....                   | -55° to +200°C |
| Thermal Resistance, Junction-to-Case, $R_{thJC}$ .....       | 0.584°C        |
| Lead Temperature (During Soldering, 10sec Max), $T_L$ .....  | +275°C         |

### **Electrical Characteristics:** ( $T_C = +25^\circ C$ unless otherwise specified)

| Parameter                           | Symbol        | Test Conditions                                        | Min | Typ | Max | Unit |
|-------------------------------------|---------------|--------------------------------------------------------|-----|-----|-----|------|
| <b>OFF Characteristics</b>          |               |                                                        |     |     |     |      |
| Collector-Emitter Breakdown Voltage | $V_{(BR)CEO}$ | $I_C = 100mA, I_B = 0$                                 | 120 | —   | —   | V    |
| Collector-Emitter Leakage Current   | $I_{CER}$     | $V_{CE} = 120V, R_{BE} = 1k\Omega$                     | —   | —   | 2   | mA   |
|                                     |               | $V_{CE} = 120V, R_{BE} = 1k\Omega, T_C = +150^\circ C$ | —   | —   | 10  | mA   |
|                                     | $I_{CEO}$     | $V_{CE} = 50V, I_B = 0$                                | —   | —   | 2   | mA   |
| Emitter Cutoff Current              | $I_{EBO}$     | $V_{BE} = 5V, I_C = 0$                                 | —   | —   | 2   | mA   |

# **Electrical Characteristics (Cont'd):** ( $T_C = +25^{\circ}\text{C}$ unless otherwise specified)

| Parameter                            | Symbol        | Test Conditions                        | Min  | Typ | Max   | Unit |
|--------------------------------------|---------------|----------------------------------------|------|-----|-------|------|
| <b>ON Characteristics</b> (Note 1)   |               |                                        |      |     |       |      |
| DC Current Gain                      | $h_{FE}$      | $I_C = 25\text{A}, V_{CE} = 5\text{V}$ | 1000 | —   | 18000 |      |
|                                      |               | $I_C = 50\text{A}, V_{CE} = 5\text{V}$ | 400  | —   | —     |      |
| Collector–Emitter Saturation Voltage | $V_{CE(sat)}$ | $I_C = 25\text{A}, I_B = 250\text{mA}$ | —    | —   | 2.5   | V    |
|                                      |               | $I_C = 50\text{A}, I_B = 500\text{mA}$ | —    | —   | 3.5   | V    |
| Base–Emitter Saturation Voltage      | $V_{BE(sat)}$ | $I_C = 25\text{A}, I_B = 200\text{mA}$ | —    | —   | 3.0   | V    |
|                                      |               | $I_C = 50\text{A}, I_B = 300\text{mA}$ | —    | —   | 4.5   | V    |

**Note 1.** Pulse Test: Pulse Width  $\leq 300\mu\text{s}$ , Duty Cycle  $\leq 2\%$ .

## **Schematic Diagram**

