







LOC	DIST	REVISIONS				
DW	—	P	LTR	DESCRIPTION	DATE	APVD
			A	RELEASED	14JAN08	AW WK

NOTE:


1. MATERIAL:
HOUSING: LCP WITH 30% GF, UL 94V-0, BLACK COLOR.
CAP: PA9T WITH 45% GF, UL 94V-0, BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
2. FINISH:
CONTACTS: 0.762μm [30μ"] MIN. GOLD PLATED ON CONTACT AREA,
GOLD FLASH ON SOLDER TAIL, WITH ENTIRE CONTACT
UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.
3. REFLOW SOLDER CAPABLE TO 260°C PER TE TEST SPEC. 109-201,
CONDITION B.
4. NO DATE CODE & LOGO ON THE PRODUCT.



SOLDER AREA: , TOLERANCE: ±0.05
RECOMMENDED PCB LAYOUT
(TOP VIEW)



1.10	0.762μm [30μ"]	2041085-2
0.70	0.762μm [30μ"]	2041085-1
DIM. A	MIN. GOLD THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. WU 14JAN2009	 Tyco Electronics Corporation Taipei, Taiwan			
DIMENSIONS: MM		CHK S. CHIEN 14JAN2009	NAME BATTERY BLOCK CONNECTOR, PLUG WITH CAP, 2 MM PITCH, 3 POSITION			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD W. KODAMA 14JAN2009				
	0 PLC ± 0.5 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 0.15 4 PLC ± - ANGLES ± 3'	PRODUCT SPEC 108-57739				
		APPLICATION SPEC				
MATERIAL SEE NOTE	FINISH SEE NOTE	WEIGHT 0.41 GRAMS	SIZE A3	CAGE CODE 00779	DRAWING NO C=2041085	RESTRICTED TO -
CUSTOMER DRAWING			SCALE	SHEET	1 OF 3	REV A

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-.



COPYRIGHT

-

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

—

P

LTR

DESCRIPTION







DATE

DWN

APVD

SEE SHEET 1.


(WITHOUT CAP CONDITION)



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM



MATERIAL

SEE SHEET 1.

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.3
2 PLC ± 0.2
3 PLC ± 0.15
4 PLC ± —
ANGLES ± 3°

FINISH

SEE SHEET 1.

DWN

A. WU

14JAN2009

CHK

S. CHIEN

14JAN2009

APVD

W. KODAMA

14JAN2009

PRODUCT SPEC

SEE SHEET 1.

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



Tyco Electronics Corporation

Taipei, Taiwan

NAME

BATTERY BLOCK CONNECTOR, PLUG
WITH CAP, 2 MM PITCH, 3 POSITION

SIZE

A300779

CAGE CODE

DRAWING NO

C=2041085

RESTRICTED TO

—

SCALE

—

SHEET

2 OF 3

REV

A

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

--,--.



COPYRIGHT

-

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

—

P

LTR


DESCRIPTION

DATE



DWN

APVD

SEE SHEET 1.



USER DIRECTION OF UNREELING →



NOTE:

- MATERIAL:
BOX: FIBREBOARD, CORRUGATED, DOUBLE WALL.
TAPE: POLYSTYRENES, HEAT-RESISTANT TEMPERATURE: 120°C, TRANSPARENT COLOR.
REEL: POLYSTYRENES, HEAT-RESISTANT TEMPERATURE: 70°C, BLUE COLOR.
BAG: POLYETHYLENE, HEAT-RESISTANT TEMPERATURE: 100°C.
- PEELING STRENGTH: 0.1 ~ 1.3 N (10 ~ 130 GRAMS)
- PEELING SPEED: 300 mm/min.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
MATERIAL	FINISH
—	—

DWN	A. WU	14JAN2009
CHK	S. CHIEN	14JAN2009
APVD	W. KODAMA	14JAN2009
PRODUCT SPEC	—	—
APPLICATION SPEC	—	—
WEIGHT	—	—
CUSTOMER DRAWING		

 Tyco Electronics		Tyco Electronics Corporation Taipei, Taiwan	
NAME			
BATTERY BLOCK CONNECTOR, PLUG WITH CAP, 2 MM PITCH, 3 POSITION			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=2041085	—
		SCALE —	SHEET 3 OF 3
			REV A