

## Safety Limit Switch

### Positive Action Limit Switches with Direct Drive Contacts for Critical Switching Applications

- Snap-action contact for accurate switching with safe operation via direct drive positive opening mechanism
- Two sets of contacts: one (NC) for safety circuit and the other (NO) for control circuit
- Safety of lever settings ensured as a mechanism engages a gear between the operating position indicator plate and the lever
- Conforms to EN (TÜV) standards corresponding to the CE marking
- 3-conduit switches are available for easy wiring
- Conforms to these standards and EC Directives:  
Machinery Directive  
Low Voltage Directive  
EN1088  
EN50041

#### Approved Standards

##### Snap-Action Models

| Agency            | Standard     | File No.                                                                                             |
|-------------------|--------------|------------------------------------------------------------------------------------------------------|
| TÜV Rheinland     | EN60947-5-1  | R9851083 (Positive opening: approved)<br>R9151372 (Positive opening: approval pending) (See note 1.) |
| UL                | UL508        | E76675                                                                                               |
| CSA               | C22.2 No. 14 | LR45746                                                                                              |
| BIA (See note 2.) | GS-ET-15     | 1-conduit: 9202158<br>3-conduit: 9309655                                                             |

- Note: 1. Adjustable roller lever, adjustable rod lever, coil spring, and plastic rod models only.  
2. Not including adjustable roller lever, adjustable rod lever, coil spring, and plastic rod models.



##### Slow-Action Models

| Agency           | Standard     | File No.                                         |
|------------------|--------------|--------------------------------------------------|
| TÜV Rheinland    | EN60947-5-1  | R9151643 (Positive opening: approved) (See note) |
| UL               | UL508        | E76675                                           |
| CSA              | C22.2 No. 14 | LR45746                                          |
| BIA (See note.)  | GS-ET-15     | 1-conduit: 9202158<br>3-conduit: 9309655         |
| SUVA (See note.) | SUVA         | 1-conduit: E6188.d<br>3-conduit: E6189.d         |

- Note: Not including adjustable roller lever, adjustable rod lever, coil spring, and plastic rod models.

# Ordering Information

## ■ MODEL NUMBER LEGEND

D4B-□□□□N

1 2 3

### 1. Conduit

- 1: PG13.5 (1-conduit) European type
- 2: G1/2 (PF1/2) (1-conduit) Japanese type
- 3: 1/2-14NPT (1-conduit) North American type
- 5: PG13.5 (3-conduit) European type
- 6: G1/2 (PF1/2) (3-conduit) Japanese type
- 7: 1/2-14NPT (3-conduit) North American type

### 2. Built-in Switch

- 1: 1NC/1NO (Snap-action)
- A: 2NC (Slow-action)
- 5: 1NC/1NO (Slow-action) (See Note)

### 3. Actuator

- 00: Switch box (without head)
- 11: Roller lever (standard)
- 13: Adjustable rubber roller lever
- 16: Adjustable roller lever
- 17: Adjustable rod lever
- 1R: Roller lever (conventional D4B-compatible)
- 70: Top plunger
- 71: Top roller plunger
- 81: Coil spring
- 87: Plastic rod

Note: Excluding D4B-□□81N and D4B-□□87N models.

## ■ SWITCHES (EN50041)

| Description               |                                                                   | Part number                                                                                     |                       |                   |                                                                                                 |                       |                   |                                                                                                   |                       |                   |
|---------------------------|-------------------------------------------------------------------|-------------------------------------------------------------------------------------------------|-----------------------|-------------------|-------------------------------------------------------------------------------------------------|-----------------------|-------------------|---------------------------------------------------------------------------------------------------|-----------------------|-------------------|
| Actuator                  |                                                                   | Conduit size/type                                                                               |                       |                   |                                                                                                 |                       |                   |                                                                                                   |                       |                   |
|                           |                                                                   | PG13.5 (European)                                                                               |                       |                   | G1/2 (Japanese)                                                                                 |                       |                   | 1/2-14NPT (North American)                                                                        |                       |                   |
|                           |                                                                   | 1NC/1NO (Snap-action)                                                                           | 1NC/1NO (Slow-action) | 2NC (Slow-action) | 1NC/1NO (Snap-action)                                                                           | 1NC/1NO (Slow-action) | 2NC (Slow-action) | 1NC/1NO (Snap-action)                                                                             | 1NC/1NO (Slow-action) | 2NC (Slow-action) |
| Side rotary               | Roller lever (form A)                                             | D4B-1111N                                                                                       | D4B-1511N             | D4B-1A11N         | D4B-2111N                                                                                       | D4B-2511N             | D4B-2A11N         | D4B-3111N                                                                                         | D4B-3511N             | D4B-3A11N         |
|                           | Adjustable roller lever, rubber, 50.0 mm (1.97 in) dia. 1/2-14NPT | D4B-3113N                                                                                       | D4B-3513N             | D4B-3A13N         | —                                                                                               |                       |                   | —                                                                                                 |                       |                   |
|                           | Adjustable roller lever (See Note 1)                              | D4B-1116N                                                                                       | D4B-1516N             | D4B-1A16N         | D4B-2116N                                                                                       | D4B-2516N             | D4B-2A16N         | D4B-3116N                                                                                         | D4B-3516N             | D4B-3A16N         |
|                           | Adjustable rod lever (form D) (See Note 1)                        | D4B-1117N                                                                                       | D4B-1517N             | D4B-1A17N         | D4B-2117N                                                                                       | D4B-2517N             | D4B-2A17N         | D4B-3117N                                                                                         | D4B-3517N             | D4B-3A17N         |
| Top plunger               | Plain (form B)                                                    | D4B-1170N                                                                                       | D4B-1570N             | D4B-1A70N         | D4B-2170N                                                                                       | D4B-2570N             | D4B-2A70N         | D4B-3170N                                                                                         | D4B-3570N             | D4B-3A70N         |
|                           | Roller (form C)                                                   | D4B-1171N                                                                                       | D4B-1571N             | D4B-1A71N         | D4B-2171N                                                                                       | D4B-2571N             | D4B-2A71N         | D4B-3171N                                                                                         | D4B-3571N             | D4B-3A71N         |
| Wobble lever (See Note 2) | Coil spring                                                       | D4B-1181N                                                                                       | ---                   | D4B-1A81N         | D4B-2181N                                                                                       | ---                   | D4B-2A81N         | D4B-3181N                                                                                         | ---                   | D4B-3A81N         |
|                           | Plastic rod                                                       | D4B-1187N                                                                                       | ---                   | D4B-1A87N         | D4B-2187N                                                                                       | ---                   | D4B-2A87N         | D4B-3187N                                                                                         | ---                   | D4B-3A87N         |
| Standards                 |                                                                   | EN60947-5-1  |                       |                   | EN60947-5-1  |                       |                   | EN60947-5-1  |                       |                   |

- Note: 1. The slow-action models with adjustable roller levers or adjustable rod levers are approved under the Forced Opening Certificate (TÜV) of the EN standard, but they do not conform to the GS-ET-15 Standard (BIA) and SUVA.  
The snap-action models with adjustable roller levers or adjustable rod levers are not approved under the Forced Opening Certificate (TÜV) of the EN standard.
2. The wobble lever models are ordinary limit switches and are not approved under EN, GS, and SUVA's Forced Opening Certificate.

## 3-Conduit Switch

| Description               |                                                         | Part number                                                                                   |                          |                      |                                                                                               |                          |                      |                                                                                                 |                          |                      |
|---------------------------|---------------------------------------------------------|-----------------------------------------------------------------------------------------------|--------------------------|----------------------|-----------------------------------------------------------------------------------------------|--------------------------|----------------------|-------------------------------------------------------------------------------------------------|--------------------------|----------------------|
| Actuator                  |                                                         | Conduit size                                                                                  |                          |                      |                                                                                               |                          |                      |                                                                                                 |                          |                      |
|                           |                                                         | PG13.5 (European) See Note 2                                                                  |                          |                      | G1/2 (Japanese)                                                                               |                          |                      | 1/2-14NPT North American                                                                        |                          |                      |
|                           |                                                         | 1NC/1NO<br>(Snap-action)                                                                      | 1NC/1NO<br>(Slow-action) | 2NC<br>(Slow-action) | 1NC/1NO<br>(Snap-action)                                                                      | 1NC/1NO<br>(Slow-action) | 2NC<br>(Slow-action) | 1NC/1NO<br>(Snap-action)                                                                        | 1NC/1NO<br>(Slow-action) | 2NC<br>(Slow-action) |
| Side rotary               | Roller lever (form A)                                   | D4B-5111N                                                                                     | D4B-5511N                | D4B-5A11N            | D4B-6111N                                                                                     | D4B-6511N                | D4B-6A11N            | D4B-7111N                                                                                       | D4B-7511N                | D4B-7A11N            |
|                           | Adjustable roller lever, rubber, 50.0 mm (1.97 in) dia. | D4B-7113N                                                                                     | D4B-7513N                | D4B-7A13N            | —                                                                                             |                          |                      |                                                                                                 |                          |                      |
|                           | Adjustable roller lever (See Note 1)                    | D4B-5116N                                                                                     | D4B-5516N                | D4B-5A16N            | D4B-6116N                                                                                     | D4B-6516N                | D4B-6A16N            | D4B-7116N                                                                                       | D4B-7516N                | D4B-7A16N            |
|                           | Adjustable rod lever (form D) (See Note 1)              | D4B-5117N                                                                                     | D4B-5517N                | D4B-5A17N            | D4B-6117N                                                                                     | D4B-6517N                | D4B-6A17N            | D4B-7117N                                                                                       | D4B-7517N                | D4B-7A17N            |
| Top plunger               | Plain (form B)                                          | D4B-5170N                                                                                     | D4B-5570N                | D4B-5A70N            | D4B-6170N                                                                                     | D4B-6570N                | D4B-6A70N            | D4B-7170N                                                                                       | D4B-7570N                | D4B-7A70N            |
|                           | Roller (form C)                                         | D4B-5171N                                                                                     | D4B-5571N                | D4B-5A71N            | D4B-6171N                                                                                     | D4B-6571N                | D4B-6A71N            | D4B-7171N                                                                                       | D4B-7571N                | D4B-7A71N            |
| Wobble lever (See Note 2) | Coil spring                                             | D4B-5181N                                                                                     | ---                      | D4B-5A81N            | D4B-6181N                                                                                     | ---                      | D4B-6A81N            | D4B-7181N                                                                                       | ---                      | D4B-7A81N            |
|                           | Plastic rod                                             | D4B-5187N                                                                                     | ---                      | D4B-5A87N            | D4B-6187N                                                                                     | ---                      | D4B-6A87N            | D4B-7187N                                                                                       | ---                      | D4B-7A87N            |
| Standards                 |                                                         | EN60947-5-1  |                          |                      | EN60947-5-1  |                          |                      | EN60947-5-1  |                          |                      |

- Note: 1. The slow-action models with adjustable roller levers or adjustable rod levers are approved under the Forced Opening Certificate (TÜV) of the EN standard, but they do not conform to the GS-ET-15 Standard (BIA) and SUVA.  
The snap-action models with adjustable roller levers or adjustable rod levers are not approved under the Forced Opening Certificate (TÜV) of the EN standard.
2. The D4B-□N is a Limit Switch conforming to European standards, and PG13.5 is commonly used in Europe.
3. The wobble lever models are ordinary limit switches and are not approved under EN, GS, and SUVA's Forced Opening Certificate.

## LEVERS (FOR SIDE ROTARY SWITCHES)

| Description                   |          |                    | Part number |
|-------------------------------|----------|--------------------|-------------|
| Actuator                      | Length   | Diameter of roller |             |
| Standard                      | 31.5     | 17.5 dia.          | D4B-0001N   |
| Adjustable roller lever       | 25 to 89 | 19 dia.            | D4B-0006N   |
| Adjustable rod lever          | 145 max. | ---                | D4B-0007N   |
| Interchangeable with D4B-0001 | 33.7     | 19 dia.            | D4B-000RN   |

Note: Other lever types are also available.

## Specifications

### APPROVED STANDARD RATINGS

TÜV Rheinland: EN60947-5-1

|                                   |       |
|-----------------------------------|-------|
| Utilization category              | AC-15 |
| Rated operating current ( $I_e$ ) | 2 A   |
| Rated operating voltage ( $U_e$ ) | 400 V |

Note: As protection against short-circuiting, use either a gl-type or gG-type 10-A fuse that conforms to IEC269.

## ■ UL/CSA: (UL508, CSA C22.2 NO. 14)

### A600

| Rated voltage                            | Carry current | Current                      |                              | Volt-amperes |        |
|------------------------------------------|---------------|------------------------------|------------------------------|--------------|--------|
|                                          |               | Make                         | Break                        | Make         | Break  |
| 120 VAC<br>240 VAC<br>480 VAC<br>600 VAC | 10 A          | 60 A<br>30 A<br>15 A<br>12 A | 6 A<br>3 A<br>1.5 A<br>1.2 A | 7,200 VA     | 720 VA |

### Q150

#### Rating Codes for DC Control-Circuit Contacts

| Thermal continuous test current, amperes | Maximum make or break current, amperes |          |                 | Maximum make or break volt-amperes at 300 volts or less |
|------------------------------------------|----------------------------------------|----------|-----------------|---------------------------------------------------------|
|                                          | 125 Volt                               | 250 Volt | 301 to 600 Volt |                                                         |
| 2.5                                      | 0.55                                   | —        | —               | 69                                                      |

## ■ CHARACTERISTICS

| Item                                                      |                                                      | Snap-action                                                                                                             | Slow-action                |
|-----------------------------------------------------------|------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------|----------------------------|
| Life expectancy<br>(see note 2)                           | Mechanical                                           | 30,000,000 operations min.                                                                                              | 10,000,000 operations min. |
|                                                           | Electrical                                           | 500,000 operations min. (at a 250 VAC, 10-A resistive load)                                                             |                            |
| Operating speed                                           |                                                      | 1 mm/s to 0.5 m/s                                                                                                       |                            |
| Operating frequency                                       |                                                      | Mechanical: 120 operations/min<br>Electrical: 30 operations/min                                                         |                            |
| Rated frequency                                           |                                                      | 50/60 Hz                                                                                                                |                            |
| Insulation resistance                                     |                                                      | 100 MΩ min. (at 500 VDC) between terminals of the same polarity and between each terminal and non-current-carrying part |                            |
| Contact resistance                                        |                                                      | 25 mΩ max. (initial value)                                                                                              |                            |
| Dielectric strength                                       |                                                      |                                                                                                                         |                            |
|                                                           | Between terminals of same polarity                   | U <sub>imp</sub> 2.5 kV                                                                                                 | U <sub>imp</sub> 4 kV      |
|                                                           | Between terminals of different polarity              | ---                                                                                                                     | U <sub>imp</sub> 4 kV      |
|                                                           | Between current-carrying metal parts and ground      | U <sub>imp</sub> 4 kV                                                                                                   | U <sub>imp</sub> 4 kV      |
|                                                           | Between each terminal and non-current-carrying parts | U <sub>imp</sub> 4 kV                                                                                                   | U <sub>imp</sub> 4 kV      |
| Rated insulation voltage (U <sub>i</sub> )                |                                                      | 600 VAC (EN60947-5-1)                                                                                                   |                            |
| Counter electromotive voltage at switching                |                                                      | 1,500 VAC max. (EN60947-5-1)                                                                                            |                            |
| Operating environmental pollution level                   |                                                      | 3 (EN60947-5-1)                                                                                                         |                            |
| Conditional short-circuit current                         |                                                      | 100 A (EN60947-5-1)                                                                                                     |                            |
| Conventional enclosed thermal current (I <sub>the</sub> ) |                                                      | 20 A (EN60947-5-1)                                                                                                      |                            |
| Electric shock protection class                           |                                                      | Class I (with grounding terminal)                                                                                       |                            |
| Vibration resistance                                      |                                                      | Malfunction: 10 to 55 Hz, 0.75 mm single amplitude                                                                      |                            |
| Shock resistance                                          |                                                      | Destruction: 1,000 m/s <sup>2</sup> min.<br>Malfunction: 300 m/s <sup>2</sup> min.                                      |                            |
| Ambient temperature                                       |                                                      | Operating: -40°C to 80°C, with no icing (-25°C to 80°C for the flexible-rod type)                                       |                            |
| Ambient humidity                                          |                                                      | Operating: 95% max.                                                                                                     |                            |
| Degree of protection                                      |                                                      | IP67 (EN60947-5-1)                                                                                                      |                            |
| Weight                                                    |                                                      | Approx. 250 g                                                                                                           |                            |

Note: 1. The above values are for initial operation.

2. The life expectancy is for an ambient temperature of 5°C to 35°C and ambient humidity of 40% to 70%. For further conditions, consult your OMRON sales representative.

3. The values in this table are for an ambient temperature of 5°C to 35°C and ambient humidity of 40% to 70%. For further conditions, consult your OMRON sales representative.

## ■ OPERATING CHARACTERISTICS

| Model                    | D4B-□□11N                                            | D4B-□□16N<br>(see note 1) | D4B-□□17N<br>(see note 2) | D4B-□□70N   | D4B-□□71N | D4B-□□81N | D4B-□□87N |
|--------------------------|------------------------------------------------------|---------------------------|---------------------------|-------------|-----------|-----------|-----------|
| OF max.                  | 9.41 N                                               |                           | 2.12 N                    | 18.63 N     |           | 1.47 N    |           |
| RF min.                  | 1.47 N                                               |                           | 0.29 N                    | 1.96 N      |           | ---       |           |
| PT                       | 21±3°                                                |                           |                           | 2.0 mm max. |           | 15° max.  |           |
| PT (2nd)<br>(see note 3) | 45°                                                  |                           |                           | 3.0 mm      |           | ---       |           |
| OT min.                  | 50°                                                  |                           |                           | 5.0 mm      |           | ---       |           |
| MD max.<br>(see note 4)  | 12°                                                  |                           |                           | 1.0 mm      |           | ---       |           |
| POT min.                 | 35° (Slow-action models)<br>55° (Snap-action models) |                           |                           | 3.2 mm      |           | ---       |           |
| POF min.                 | 19.61 N                                              |                           |                           | 49.03 N     |           | ---       |           |
| TT                       | 75°                                                  |                           |                           | 7.0 mm      |           | ---       |           |
| FP max.                  | ---                                                  |                           |                           | 38 mm       | 51 mm     | ---       |           |
| OP                       | ---                                                  |                           |                           | 35±1 mm     | 48±1 mm   | ---       |           |

Note: 1. The operating characteristics of these Switches were measured with the roller lever set at 31.5 mm.

2. The operating characteristics of these Switches were measured with the rod lever set at 140 mm.


3. Only for slow-action models.

4. Only for snap-action models.


## Engineering Data

### ■ ELECTRICAL LIFE EXPECTANCY SNAP-ACTION MODELS

( $\cos\phi = 1$ )




( $\cos\phi = 0.4$ )



# Nomenclature

## Head

With roller lever models, the direction of the switch head can be varied to any of the four directions by loosening the roller lever switch screws at the four corners of the head.



Operating Position Mark  
(arrow)


The roller lever switch employs a system which allows selection of operation on only one side (left or right) or both sides without the use of any tools.

Push and rotate

Switch Box Material  
Aluminum die-cast

## Conduit Opening

Available in three different types of conduit threads:  
Pg 13.5, G1/2 or 1/2-14NPT



## Safety-Oriented Lever Setting

Grooves which engage the lever every 90° are cut in the operating position indicator plate to prevent the lever from slipping against the rotary shaft.

## Equipped with Operating Position Indicator Plate

An optimum overtravel (OT) value may be secured by setting a desired OT value with a projection.

## Shearing Force Contact Separating Mechanism (NC Contact Section Only)

Should any abnormality occur in the contact area, the contacts are positively pulled apart from each other by shearing force.

## Ground Terminal Screw

A ground terminal is provided to improve safety.

## Contact Material

Ag alloy

# Operation

## CONTACT FORM (EN50013)


| Model    | Contact                  | Diagrams | Explanation                                                                                                                                                 |
|----------|--------------------------|----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|
| D4B-□1□N | 1NC/1NO<br>(Snap-action) |          | <p>Only NC contact 11-12 has an approved positive opening mechanism. →</p> <p>Terminal numbers 11-12 and 13-14 cannot be used as unlike poles.</p>          |
| D4B-□5□N | 1NC/1NO<br>(Slow-action) |          | <p>Only NC contact 11-12 has an approved positive opening mechanism. →</p> <p>Terminal numbers 11-12 or 23-24 can be used as unlike poles.</p>              |
| D4B-□A□N | 2NC<br>(Slow-action)     |          | <p>Both NC contacts 11-12 and 21-22 have an approved positive opening mechanism. →</p> <p>Terminal numbers 11-12 and 21-22 can be used as unlike poles.</p> |

## POSITIVE CONTACT OPENING MECHANISM


### 1NO/1NC Contact (Snap-action)

If metal deposition between mating contacts occurs on the NC contact side, they can be pulled apart by the shearing force and tensile force generated when part B of the safety cam or plunger engages part A of the movable contact blade. When the safety cam or plunger is moved in the direction of the arrow, the Limit Switch releases.


1. When metal deposition occurs.




2. When contacts are being pulled apart.




3. When contacts are completely pulled apart.



**1NC/1NO Contact (Slow-Action)**

Conforms to IEC 947-5-1 Positive Opening

When metal deposition occurs, the contacts are separated from each other by the plunger being pushed in.

**2NC Contact (Slow-Action)**

Conforms to EN60947-5-1

When metal deposition occurs, the contacts are separated from each other by the plunger being pushed in.

is marked on the product to indicate approval of positive opening.

## Dimensions

Unit: mm (inch)

Note: 1. Unless otherwise specified, a tolerance of  $\pm 0.4$  mm applies to all dimensions shown in this section.

2. When placing your order, specify the conduit type by adding a code (see below) to the first blank box in the model number of the selected switch. (For more ordering information, refer to the Model Number Legend, found in the *Ordering Information* of this data sheet.)

Key for Part No. Code:

Conduit type for standard switches

1: PG 13.5 (European)

2: G 1/2 (Japanese)

3: 1/2-14NPT (North American)

Conduit type for 3-conduit switches


5: PG 13.5 (European)

6: G 1/2 (Japanese)


7: 1/2-14NPT (North American)

## SWITCHES


### Roller Lever D4B-□□11N




### Adjustable Roller Lever Switch, Rubber Roller D4B-3113N, D4B-3513N, D4B-3A13N



### Adjustable Roller Lever D4B-□□16N




### Adjustable Rod Lever D4B-□□17N




### Top Plunger

#### D4B-□□70N





### Top Roller Plunger

#### D4B-□□71N



### Coil Spring



#### D4B-□□81N



- Note:
1. The coil spring may be operated from any directions except axial directions (↓).
  2. Be sure to adjust the dog to within 40 mm from the top end of the coil spring.

### Plastic Rod

#### D4B-□□87N









- Note:
- Be sure to adjust the dog to within 40 mm from the top end of the plastic rod.



## 3-Conduit Switches

## Roller Lever



D4B-□□11N

Adjustable Roller Lever Switch, Rubber Roller  
D4B-7113N, D4B-7513N, D4B-7A13NAdjustable Roller Lever  
D4B-□□16N



### Adjustable Rod Lever D4B-□□17N





### Top Plunger D4B-□□70N





### Top Roller Plunger D4B-□□71N



### Coil Spring D4B-□□81N




### Plastic Rod D4B-□□87N




# ROLLER LEVERS


D4B-0001N




D4B-0002N




D4B-0003N




D4B-0004N




D4B-0005N




D4B-0006N



D4B-000RN




D4B-0007N



## CW, CCW or Two-way Operation

The head of Side Rotary Switches can be converted in seconds to CW, CCW, or two-way operation. The conversion procedure follows.



### Procedure

1. Remove the head by loosening the four screws that secure it.
2. Turn over the head to set the desired operation (CW, CCW, or both). The desired operation can be selected by setting the mode selector knob shown in the figure. This knob is factory set to the "CW + CCW" (two-way operation) position.
3. Set the CW hole on the head at the operation position mark (arrow) for clockwise operation or set the CCW hole right at the arrow for counterclockwise operation. In either case, be sure to set the hole position exactly at the arrow point.

## Precautions

If the D4B-□N is applied to an emergency stop circuit or safety circuit for prevention of injury, use the D4B-□N model that has an NC contact equipped with a force-separation mechanism, and make sure that the D4B-□N operates in the positive mode. In addition, secure the D4B-□N with screws that are tightened in a single direction so that the D4B-□N cannot be easily removed. Then provide a protection cover for the D4B-□N and post a warning label near the D4B-□N.


In order to protect the D4B-□N from damage due to short-circuiting, connect a fuse breaking a current 1.5 to 2 times higher than the rated current in parallel with the D4B-□N.

If an application satisfying EN standards is to employ the D4BL, apply the 10-A gI or gG fuse approved by IEC269.

Do not apply the D4B-□N to the door without applying a stopper to the door.

If the D4B-□N is used with the actuator normally pressed, the D4B-□N may malfunction or may soon have reset failures. Be sure to check and replace the D4B-□N regularly.

## Tightening Torque



|   | Type                                 | Proper tightening torque |
|---|--------------------------------------|--------------------------|
| 1 | Terminal screw (M3.5)                | 0.59 to 0.78 N • m       |
| 2 | Cover-mounting screw (see note)      | 1.18 to 1.37 N • m       |
| 3 | Head-mounting screw                  | 0.78 to 0.98 N • m       |
| 4 | Switch-mounting screw (M5)           | 4.90 to 5.88 N • m       |
| 5 | Connector                            | 1.77 to 2.16 N • m       |
| 6 | Cap screw (for three-conduit models) | 1.27 to 1.67 N • m       |

Note: Apply a tightening torque of 0.78 to 0.88 N • m to conduit models.

## ■ CORRECT USE

### Operating Environment

The D4B-□N is for indoor use. The D4B-□N may malfunction if the D4B-□N is used outdoors. Be sure to use a model with a lever-type actuator for outdoor use instead.


Do not use the D4B-□N in the following places:

- Places with radical temperature changes.
- Places with excessive humidity that may cause condensation.
- Places with excessive vibration.
- Places where metal dust, oil, or chemical may be sprayed to the D4B-□N.

### Mounting

Use four M5 screws with washers to mount the standard model. Be sure to apply the proper torque to tighten each screw. The D4B-□N can be mounted more securely by using the four screws plus two  $5^{-0.05}_{-0.15}$ -mm protruding parts, each of which has a maximum height of 4.8 mm as shown below.

### Mounting Dimensions (M5)



### Changes in Actuator Mounting Position

To change the angle of the lever, loosen the Allen-head bolts on the side of the lever.

The operating position indicator plate has protruding parts which engage with the lever, thus allowing changes to the lever position by 90°.

The back of the operating position indicator plate has no protruding parts. The lever can be set at any angle by attaching the operating position indicator plate to the Switch so that this side will face the lever. In this case, however, the D4B-□N will not be approved by SUVA or BIA. Make sure that the lever engages with the operating position indicator plate securely so that the lever will not slip.


### Changes in Head Mounting Position

By removing the screws on the four corners of the head, the head can be reset in any of four directions. Make sure that no foreign materials will penetrate through the head.


### Wiring

Do not connect the bare lead wires directly to the terminals but be sure to connect each of them by using an insulation tube and M3.5 round solderless terminals and tighten each terminal screw within the specified torque range.

The proper lead wire is 20 to 14 AWG (0.5 to 2.5 mm<sup>2</sup>) in size.



Make sure that all solderless terminals come into contact with the casing or cover as shown below, or the cover may not be mounted properly or the D4B-□N may malfunction.



### Connector

Make sure that each connector is tightened within the specified torque range. The casing may be damaged if the connector is tightened excessively.

If the 1/2-14NPT is used, cover the cable and conduit end with sealing tape in order to ensure IP67.


The Pg13.5 connector must be Nippon Flex's ABS-08Pg13.5 or ABS-12 Pg13.5.

Use OMRON's SC-series connector which is suited to the cable in diameter.

Properly attach the provided conduit cap to the unused conduit opening and securely tighten the cap screw within the specified torque when wiring the D4B-□N.


### Actuator Load

The load for the actuator (roller) of the Switch must be imposed on the actuator in the horizontal direction, or the actuator or the rotating axis may be deformed or damaged.



When using a long lever model like the D4B-□□16N or D4B-□□17N, the Switch may telegraph. To avoid telegraphing, take the following precautions.

1. Set the lever to operate in one direction. (For details, see the data sheet section: *CW, CCW or Two-way Operation*.)
2. Modify the rear end of the dog to an angle of 15° to 30° as shown below or to a secondary-degree curve.



3. Modify the circuit so as not to detect the wrong operating signals.

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS. To convert millimeters into inches, divide by 25.4

**OMRON**

**OMRON ELECTRONICS LLC**

One Commerce Drive  
Schaumburg, IL 60173

**847-843-7900**

For US technical support or other inquiries:

**800-556-6766**

**OMRON CANADA, INC.**

885 Milner Avenue  
Toronto, Ontario M1B 5V8

**416-286-6465**

**OMRON ON-LINE**

Global - <http://www.omron.com>

USA - <http://www.omron.com/oei>

Canada - <http://www.omron.ca>