



Lithium/Manganese Dioxide Battery



Inches	mm
.965	24.50
.118	3.00




Dimensions shown are maximum.

SPECIFICATIONS

Nominal Voltage:	3.0 V
Typical Voltage:	3.1 – 3.3 V
Rated Capacity:	300 mAh on 15 kΩ to 2.0 V at 20°C (68°F)
Average Weight:	0.141 oz. (4.0 g)
Volume:	0.086 in. ³ (1.41 cm ³)
Terminals:	Flat, PC Pins
Operating Temp. Range:	-40°C to 60°C (-40°F to 140°F)
NEDA/ANSI:	5011LC
IEC:	—

CONTINUOUS DISCHARGE AT 20°C (68°F)



TEST CONDITIONS



LOAD	DRAIN
2.7 kΩ	≈ 1 mA
6.8 kΩ	≈ 410 μA
12.0 kΩ	≈ 240 μA

DURACELL INC.

New Products and Technology Division
Berkshire Corporate Park
Bethel, CT 06801 U.S.A.
Telephone: Toll-free 1-800-431-2656
Outside North America: 203-791-3274
Facsimile: 203-791-3273
Internet: www.duracellnpt.com



Printed in U.S.A. on recycled paper, please recycle after use.

CONTINUOUS DISCHARGE AT 20°C (68°F)**EFFECT OF TEMPERATURE ON PERFORMANCE****INTERNAL RESISTANCE vs DISCHARGE VOLTAGE**