



PRT4H-TL0




- Greater resistance to damage caused by ultraviolet light – indoor or outdoor use
- Extended release tab permits easy release and re-use where changes are anticipated during development, production or servicing in the field
- One-piece construction for consistent performance and reliability
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation (Light-Heavy cross section ties have a straight tip)

▪ Part Number	PRT4H-TL0
▪ RoHS Compliance Status	Compliant
▪ Part Description	Cable Tie, Releasable, 14.5", Light-Heavy cross section
▪ Product Type	Cable Ties
▪ Material	Weather Resistant Nylon 6.6
▪ Color	Black
▪ CSA Certified	No
▪ UL Listed (File #E56854)	No
▪ UL Recognized (File #E56854)	No
▪ Length (In.)	14.5
▪ Length (mm)	368
▪ Width (In.)	.300
▪ Width (mm)	7.6
▪ CE Compliant	Yes
▪ Cross Section	Light-Heavy
▪ Head Height (In.)	.300
▪ Head Height (mm)	7.6
▪ Head Width (In.)	.480
▪ Head Width (mm)	12.2
▪ Locking Style	Releasable
▪ Material Flammability Rating	UL 94-HB
▪ Max. Bundle Diameter (In.)	4.00
▪ Max. Bundle Diameter (mm)	102
▪ Max. Continuous Use Temperature	185°F (85°C)
▪ Min. Loop Tensile Strength (Lbs.)	80
▪ Min. Loop Tensile Strength (N)	356

▪ Pricing Description	Cable Tie, Releasable, 14.5" L (368mm), Light-Heavy, Weather Resistant, Black
▪ Thickness (In.)	.075
▪ Thickness (mm)	1.9
▪ Tool	Hand install only
▪ Min. Order UOM	PC
▪ Min. Order Qty.	250
▪ BOM Qty. (# of Pkgs.)	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	G in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS- SECTION	TIP STYLE	WEIGHT lbs/100pcs (g)
	MIN in (mm)	MAX in (mm)											
PRT2H	.188 (4.8)	2.00 (51)	.075 (1.9)	.300 (7.6)	.413 (10.5)	.300 (7.6)	.480 (12.2)	8.4 (213)	.430 (10.9)	80 (356)	HEAVY	STRAIGHT	.76 (346)
PRT3H	.188 (4.8)	3.00 (76)	.075 (1.9)	.300 (7.6)	.413 (10.5)	.300 (7.6)	.480 (12.2)	11.4 (290)	.430 (10.9)	80 (356)	HEAVY	STRAIGHT	1.04 (473)
PRT4H	.188 (4.8)	4.00 (102)	.075 (1.9)	.300 (7.6)	.413 (10.5)	.300 (7.6)	.480 (12.2)	14.5 (368)	.430 (10.9)	80 (356)	HEAVY	STRAIGHT	1.28 (581)

NOTES:

* 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

PANDUIT
CORP. TINLEY PARK, ILLINOIS
PAN-TY CABLE TIES
RELEASEABLE SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± ----- (.XXX) ± .020 (.51)
(.XX) ± .02 (.5) ANGLES ± -----
UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

--	----	---	CORRECTED MATERIAL NAME			----	--				DRAWN BY CEW	MAT'L: NYLON 6.6	SCALE NONE
6	6/22/05	ERW	ADDED TOLERANCES TO DIMENSIONS 'A' & 'B'	4472	6					DATE 12-7-83	CHK'D HVP	DRAWING NO. SS-4472	DWG A
REV	DATE	BY	CHK	DESCRIPTION			ECN - R	CUST	SUP			SHEET 2 OF 2	SIZE