



**SQUARE D** **SQUARE D**

by Schneider Electric

List Price \$39.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

### Technical Characteristics

RoHS Compliant	Yes
Ampere Rating (Resistive)	12A
Application	Designed for multipole switching applications at 240 volts or lower
Approvals	UL Listed (with 8501NR socket) - UL Recognized Component - CSA Certified - CE Marked
Contact Material	Silver Tin Oxide
Coil Voltage	120Vac
Snapmount Socket	8501NR51 or 8501NR52
Mounting Type	Socket
Manual Operator	No
Horsepower Rating	1/3HP@120Vac - 1/2HP@240Vac
Type of Pins	Tubular Terminals
Pilot Light	No
Contact Arrangement	DPDT
Operating Temperature Range	-40°F to 131°F
Relay Type	Standard
Operating Times	Pick-Up: 12ms - Drop-Out: 12ms
Type	K

### Shipping and Ordering

Category	21141 - Relays, General Purpose, Plug-In, Tubular Terminals, Type KP
Discount Schedule	CP2
GTIN	00785901480747
Package Quantity	1
Weight	0.2 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	CN

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.